

CABLE AND WIRE CUTTERS

W355

CC10

CC21

CC325

WC6

CIRCLIP PLIERS

2195

2295

2105

2205

W355 The scissor action cuts stranded copper and aluminium cable up to 19 strands of 0.064ins diameter without fraying. The parrot beak blade holds the cable firmly without distorting its shape. Ideal for cutting domestic cooker cable.

Cat No	Overall Length	Unit/ Pack
--------	----------------	------------

W355/10	10" 250mm	5
----------------	------------------	----------

CC10 Drop forged steel handles and head joined by a hardened rivet. The head has two cutting stations, hardened and tempered to cut a maximum 9.2mm O/D copper cable.

Cat No	Overall Length	Unit/ Pack
--------	----------------	------------

CC10	6 1/4" 164mm	10
-------------	---------------------	-----------

CC21 Drop forged steel handles and head joined by a hardened rivet. The head is hardened and tempered to cut a maximum 17mm O/D copper cable.

Cat No	Overall Length	Unit/ Pack
--------	----------------	------------

CC21	9 3/8" 238mm	6
-------------	---------------------	----------

CC325 These powerful yet compact cutters feature a ratchet action, which with a series of small following cuts will shear up to a maximum 32mm O/D copper cable.

The pressed steel handles are spring loaded for single handed operation with a finger lock to hold them in a closed position.

Cat No	Overall Length	Unit/ Pack
--------	----------------	------------

CC325	11" 280mm	1
--------------	------------------	----------

457-346

WC6 The special cutting action of the head allows materials such as wire strand, electric cable and metal to be cut without distorting the end profile of the material. The pressed aluminium handles are spring loaded for single handed operation with a thumb lock to hold them in the closed position.

Maximum capacities:-

6.5mm mild steel strand-85 ton/inch²

6.5mm unarmoured electric cable

5.0mm high tensile steel rope-115 ton/inch²

5.0mm steel wire -21 ton/inch²

5.0mm copper and aluminium rod

4.0mm steel rod-42 ton/inch²

2.5mm spring steel wire-115 ton/inch²

Cat No	Overall Length	Unit/ Pack
--------	----------------	------------

WC6	7 3/4" 195mm	6
------------	---------------------	----------

CIRCLIP PLIERS

A quality range of drop forged circlip pliers with PVC sleeves available for fitting internal and external circlips in capacities as Table 1. Tips are manufactured to close limits and are angled and serrated to ensure retention of the clip when expanded or compressed.

TABLE 1

Cat No	Description	Length MM	Capacity OMM	Point OMM
W2105/5	External Straight Circlip Pliers	5"	125	10-25
W2105/7	External Straight Circlip Pliers	7"	175	19-40
W2105/9	External Straight Circlip Pliers	9"	230	32-80
W2195/5	External Bent Circlip Pliers	5"	125	10-25
W2195/7	External Bent Circlip Pliers	7"	175	19-40
W2195/9	External Bent Circlip Pliers	9"	230	32-80
W2205/5	Internal Straight Circlip Pliers	5"	125	12-25
W2205/7	Internal Straight Circlip Pliers	7"	175	19-65
W2205/9	Internal Straight Circlip Pliers	9"	230	32-80
W2295/5	Internal Bent Circlip Pliers	5"	125	12-25
W2295/7	Internal Bent Circlip Pliers	7"	175	19-65
W2295/9	Internal Bent Circlip Pliers	9"	230	32-80