

ZL series

Tiny toggle switches - metal bushing

Distinctive features - Specifications - Overview

UG1410A



☐ Ø 4,83 mm threaded bushing

☐ Solder lug and straight PC terminals

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
 - gold plated contacts : 0,4VA 20V max. AC or DC
 - silver plated contacts : 0,5A 48V max. AC or DC
- Minimum load : 10mA 50mV - 10µA 5VDC
- Contact resistance : 20 mΩ max.
- Insulation resistance : 1.000 MΩ min. at 500VDC
- Dielectric strength: 1.000 Vrms 50 Hz min. between terminals and frame
500 Vrms 50 Hz min. between terminals
- Electrical life at full load :

Contacts	Number of cycles	
	2 positions	3 positions
Gold plated	60.000	30.000
Silver plated	20.000	10.000

GENERAL SPECIFICATIONS

- Strength of terminals : pull-out force 10N max.
- Torque : 1 Nm max. applied between the 2 nuts
- Max. panel thickness : 1,5 mm (.059) with 2 nuts
- Operating temperature : -30°C to +85°C
- Moisture : 21 days 95 % (NFC 20-603 - IEC 8-2-3)

MATERIALS

- Case : thermoplastic UL94-V0
- Actuator : brass, nickel plated
- Bushing : zamac, tin plated
- Contacts and terminals :
 - 0 : brass, gold plated (standard)
 - 1 : brass, silver plated
 - 3 : brass, gold plated (1,27 micron gold)
- Terminal seal : epoxy

SOLDERING

- Hand soldering : 280°C max. for 5 seconds max.
- Wave soldering : 260°C max. for 5 seconds max.

ZL																																														
SERIES	Number of poles	Electrical functions	Terminals	Contact and terminal materials	Bushings	Models																																								
3	Single pole	<table><tr><td>1</td><td>ON</td><td>-</td><td>OFF</td></tr><tr><td>6</td><td>ON</td><td>-</td><td>ON</td></tr><tr><td>9</td><td>ON</td><td>OFF</td><td>ON</td></tr><tr><td>7</td><td>MOM</td><td>OFF</td><td>MOM</td></tr><tr><td>8</td><td>ON</td><td>OFF</td><td>MOM</td></tr><tr><td>2</td><td>ON</td><td>-</td><td>MOM</td></tr></table>	1	ON	-	OFF	6	ON	-	ON	9	ON	OFF	ON	7	MOM	OFF	MOM	8	ON	OFF	MOM	2	ON	-	MOM	<table><tr><td>SO</td><td>Solder lug</td></tr><tr><td>PO</td><td>Straight PC</td></tr></table>	SO	Solder lug	PO	Straight PC	<table><tr><td>0</td><td>Brass, gold plated</td></tr><tr><td>1</td><td>Brass, silver plated</td></tr><tr><td>3</td><td>Brass, gold plated (1,27 micron gold)</td></tr></table>	0	Brass, gold plated	1	Brass, silver plated	3	Brass, gold plated (1,27 micron gold)	<table><tr><td>01</td><td>Threaded, with flat</td></tr><tr><td>02</td><td>Threaded, with keyway</td></tr></table>	01	Threaded, with flat	02	Threaded, with keyway	<table><tr><td>00</td><td>Standard model</td></tr></table>	00	Standard model
1	ON	-	OFF																																											
6	ON	-	ON																																											
9	ON	OFF	ON																																											
7	MOM	OFF	MOM																																											
8	ON	OFF	MOM																																											
2	ON	-	MOM																																											
SO	Solder lug																																													
PO	Straight PC																																													
0	Brass, gold plated																																													
1	Brass, silver plated																																													
3	Brass, gold plated (1,27 micron gold)																																													
01	Threaded, with flat																																													
02	Threaded, with keyway																																													
00	Standard model																																													

Dimensions : First dimensions are in mm while inches are shown as bracketed numbers.



Packaging unit : 100 pieces




Mounting accessories : Standard hardware supplied with all models : 2 hex nuts 7 mm (.275) across flats P/N U5731, 1 locking ring P/N U5821 (with keyway) or U5831 (with flat) and 1 lockwasher P/N U5841.

The company reserves the right to change specifications without notice.



ZL series

Tiny toggle switches - metal bushing




- Single pole
- Gold plated or silver plated contacts
- Epoxy sealed terminals

Other actuator lengths available on request.



MODEL STRUCTURE




Shown with threaded bushing code 01

Solder lug terminals : ZL..S0



ZL31S0
ZL36S0
ZL39S0
ZL37S0
ZL38S0
ZL32S0

III	II	I
ON	-	OFF
ON	-	ON
ON	OFF	ON
MOM	OFF	MOM
MOM	OFF	ON
MOM	-	ON




→ Flat

Straight PC terminals : ZL..P0



ZL31P0
ZL36P0
ZL39P0
ZL37P0
ZL38P0
ZL32P0

III	II	I
ON	-	OFF
ON	-	ON
ON	OFF	ON
MOM	OFF	MOM
MOM	OFF	ON
MOM	-	ON



→ Flat

CONTACT & TERMINAL MATERIALS



0 : Brass, gold plated (standard) - 1 : Brass, silver plated
3 : Brass, gold plated (1,27µ gold)

BUSHINGS

