

Transfer or duplication of this document as well as the utilisation or communication of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved in case of patent, utility model or design patent registrations.



Ratings

Use Group	B	D
Rated Voltage	300V	300V
Rated Current	20A	10A
Rated Wire Size		
solid	AWG 30-12	AWG 30-12
flexible	AWG 30-12	AWG 30-12
Screw Size	M3	

Insulating Material


Material	PA 6.6
Flammability Class	UL 94 V-0

Materials

Clamp	Brass
Screw	Stainless Steel
Solder Tag	Copper Alloy
Temperature Range	-40° C ~ 105° C
RoHS Compliant	

Part No.: **ED790/X**

No. of Poles
02 2 Poles
03 3 Poles
...
12 12 Poles



△			
SIGN	DESCRIPTION	CHK.	DATE

DWG	WF. Zhang	DATE	2017.09.11	UNITS:	MM	SHEET:	1 OF 1	Tolerance
CHK.	WF. Zhang	DATE	2017.09.11	SCALE:	NONE 5:1 (:)	REV:	A	X. ±0.50
APP.		DATE		TITLE:	ED790 series 5.00 mm, one piece double level			X.X ±0.30
				PART NO.	ED790/X			X° ±1°
				DWG NO.	ED790/X.DWG			⊙



ON-SHORE TECHNOLOGY, INC.