


# POWER HEADERS, STACKERS & SOCKETS

MAX  
13.1  
A m p s



(3.96 mm) .156" PITCH • FWJ, HFWJ, JW, FHP SERIES

**FWJ, HFWJ, JW**  
Board Mates:  
FHP

**FHP**  
Board Mates:  
FWJ, HFWJ, JW

## SPECIFICATIONS

**Insulator Material:**  
FWJ = Black Glass Filled Polyester  
HFWJ, JW = Natural Liquid Crystal Polymer  
FHP = Black LCP

**Terminal Material (FWJ, HFWJ, JW):**  
Phosphor Bronze

**Contact Material (FHP):**  
BeCu

**Plating:**  
Sn over 50 μ" (1.27 μm) Ni

**Operating Temp Range:**  
-55 °C to +105 °C

**Voltage Rating:**  
600 VAC/849 VDC

**Insertion Depth (FHP):**  
(3.57 mm) .140" to (8.76 mm) .345" or pass-through from top

**Wiping Distance (FHP):**  
(0.38 mm) .015"

## PROCESSING

**Lead-Free Solderable:**  
FWJ = No, Lead Wave only  
HFWJ, JW, FHP = Yes

**SMT Lead Coplanarity:**  
HFWJ, FWJ, JW = (0.20 mm) .008" max (02-16)\*  
(0.25 mm) .010" max (17-24)\*  
FHP = (0.15 mm) .006" max\*  
\*(.004" stencil solution may be available; contact IPG@samtec.com)

**Note:**  
Some lengths, styles and options are non-standard, non-returnable.

SERIES	NO. OF PINS	LEAD STYLE	PLATING OPTION	S	OTHER OPTIONS
--------	-------------	------------	----------------	---	---------------

**FWJ**  
Standard Header

**HFWJ**  
High Temp Header

01 thru 24

Specify LEAD STYLE from chart below



-T = Matte Tin

Leave blank for Through-hole

-RA = Right-angle (Style -02 & -04 only)

-VS = Surface Mount Requires HFWJ (2 pins/row minimum) Style -05 not available.

-P = Pick & Place Pad (3 Pos. min.) (6.98 mm) .275" min. post height (-VS only)



LEAD STYLE	A	B	C	D	E	F
-01	(11.43) .450	(4.45) .175	(10.46) .412	-	-	-
-02	(12.70) .500	(11.73) .462	(4.45) .175	(8.13) .320	(2.54) .100	
-04	(20.55) .809	(3.96) .156	(19.10) .752	(3.96) .156	(13.56) .534	(4.95) .195
-05*	(3.81) .150	(12.07) .475	-	-	-	-

\*FWJ Only

JW	NO. OF PINS	04	PLATING OPTION	S	STACK HEIGHT	POST HEIGHT	OTHER OPTIONS
----	-------------	----	----------------	---	--------------	-------------	---------------

02 thru 24

-T = Matte Tin


- "XXX"  
= Stacker Height (in inches) (0.13 mm) .005" increments

- "XXX"  
= Post Height (in inches)

Leave blank for Through-hole

-VS = Surface Mount (2 pins/row minimum)

-P = Pick & Place Pad (3 Pos. min.) (6.98 mm) .275" min. post height (-VS only)



Example: -250 = (6.35 mm) .250"

FHP	NO. OF PINS	LEAD STYLE	PLATING OPTION	S	OTHER OPTIONS
-----	-------------	------------	----------------	---	---------------

02 thru 24

-01 = Through-hole

-T = Matte Tin


-02 = Surface Mount

-LC = Locking Clip (Manual placement required) (-02 lead style only)

-TR = Tape & Reel Packaging (Available on positions 2-18) (-02 lead style only)

-K = (6.50 mm) .256" DIA Polyimide film Pick & Place Pad (2-4 positions require -"X"R) (-02 lead style only)

-FR = Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (Available on positions 2-18) (-02 lead style only)



-01 -02