

4

3


2

1

THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
CE	16	F		REVISED PER 0A00-0308-00	31MAY00	TA	SB

- 1 MATERIAL:
BODY: THERMOPLASTIC
CAPILLARY: ZrO
CRIMP EYELET: COPPER
STRAIN RELIEF: THERMOPLASTIC ELASTOMER, V-0
- 2 FINISH:
CRIMP EYELET: TIN
- 3 BULK PACKAGE, 500 PIECES.
4. FOR USE WITH 3.0mm "LOOSE-JACKETED" CABLE.
- 5 CONTAINS NO STRAIN RELIEFS OR BARE BUFFER BOOTS.
- 6 FOR USE WITH 900µm BUFFERED FIBER.
- 7 NO AMP LOGO



- 7 3
- 7 5 3
- 6
- 5 3
- 3

—	BLACK/WHITE	126µm FERRULE	504655-6
—	—	126µm FERRULE	504655-5
BLUE	—	126µm FERRULE	504655-4
—	—	126µm FERRULE	504655-3
—	BLUE	126µm FERRULE	504655-2
—	BLUE	126µm FERRULE	504655-1
BUFFER BOOT COLOR		STRAIN RELIEF COLOR	DESCRIPTION
			PART NUMBER

DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN B BRIGGS 7-21-95		AMP Incorporated Harrisburg, PA 17105-3608	
				CHK T.FAWCETT 7-21-95		NAME AMP SC DUPLEX CONNECTOR KIT, SINGLEMODE, ONE PIECE, 3.0mm	
				APVD D.STAKEM 7-21-95		SIZE A3	
				PRODUCT SPEC —		CAGE CODE 00779	
				APPLICATION SPEC —		DRAWING NO C-504655	
				WEIGHT —		SCALE 2:1	
MATERIAL 1		FINISH 2		CUSTOMER DRAWING		SHEET 1 OF 1	
						REV F	