

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

NOTES:

1 MATERIAL: POLYAMIDE GLASS FILLED
COLOUR NATURAL

2 MATERIAL: POLYAMIDE GLASS FILLED
COLOUR BLACK

3) PACKAGING: SEE TE PACKAGING
SPECIFICATION 107-20294

4 TE LOGO

5 N CODE

6 L CODE

7 PE CODE

8 RATED VOLTAGE

9 WIRE SIZE & RATED CURRENT






10 AREA FOR AGENCY APPROVAL LOGO

11 IP CODE


12) SOCKET CAP P/N 293596-1 (SEE DRAWING 293596
FOR REFERENCE) HAS TO BE ASSEMBLED TO GUARANTEE
IP40 DEGREE OF PROTECTION WHEN CONNECTOR HOUSING IS NOT MATTED WITH
COUNTERPART

13 NOT YET RELEASED FOR PRODUCTION

14 DATA CODE




SCALE 1:1



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.3
2 PLC ±0.20
3 PLC ±
4 PLC ±
ANGLES ±3°

FINISH

-

DWN M. ZUCCA 06OCT2009

CHK U. AIME 06OCT2009

APVD G. TURCO 06OCT2009

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

Customer Drawing



TE Connectivity

NAME
T-SPLITTER CONNECTOR* M-LINE
3 POLES UNSEALED VERSION

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-293611

-

SCALE 2:1

SHEET 1 OF 2

REV E

