


## Dimensions: mm (in.)

**Electrical Specifications:**

- Rating: 50mA/12VDC
- Dielectric Strength: 300 V AC(50Hz or 60Hz) for 1 minute
- Contact Resistance: 100m $\Omega$  max.
- Insulation Resistance: 500VDC 100M $\Omega$  min.

**Note:**

- RoHS Compliant

**Mechanical Specifications:**

- Operating Temperature: -40° C to +85° C
- Storage Temperature: -40° C to +85° C
- Stroke: 1.30  $\pm$  .30mm

| Mouser Stock No. | Mechanical Life (cycles) | Operating Force |
|------------------|--------------------------|-----------------|
| 101-L613R-EV     | 100,000                  | 200 $\pm$ 50gf  |
| 101-L613S-EV     | 30,000                   | 350 $\pm$ 100gf |

**Tactile Switches**  
101-L613R-EV, 101-L613S-EV

**Mountain Switch**