

C-15-CPUSE-N-A

15 dB, Air Directional Coupler, 698–2700 MHz



OBSOLETE

This product was discontinued on: July 31, 2014

Replaced By:

C-15-CPUSE-N-AI6	15 dB, Air Directional Coupler, 555–2700 MHz
C-15-CPUSE-N-AI6X	15 dB, Air Directional Coupler, 578–2700 MHz

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Directional coupler

General Specifications

Device Type	Coupler
Application	Indoor/Outdoor
Color	Black
Inner Contact Plating	Silver
Interface	N Female
Outer Contact Plating	Trimetal

Dimensions

Height	22 mm 0.866 in
Width	75 mm 2.953 in
Length	155 mm 6.102 in

Electrical Specifications

3rd Order IMD	-150 dBc
3rd Order IMD Test Method	Two +43 dBm carriers

C-15-CPUSE-N-A

Insertion Loss at Frequency Band	0.4 dB @ 698–2700 MHz
Return Loss, minimum	20.8 dB
Average Power, maximum	200 W
Coupling	15 dB
Coupling Tolerance	±1.0dB
Impedance	50 ohm
Isolation at Frequency Band	35 dB @ 698–2700 MHz
Operating Frequency Band	698 – 2700 MHz
Peak Power, maximum	1 kW
Reflected Power, maximum	200 W
VSWR	1.2

Environmental Specifications

Operating Temperature	-35 °C to +85 °C (-31 °F to +185 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP65

Packaging and Weights

Height, packed	40 mm 1.575 in
Width, packed	90 mm 3.543 in
Length, packed	180 mm 7.087 in
Volume	648 cc 39.543 in ³
Weight, gross	0.42 kg 0.926 lb
Weight, net	0.38 kg 0.838 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

