

MA15 Series
OVP 120V 15A w. Filter,LED

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**General ordering data**

Type	OVP 120V 15A w. Filter,LED
Order No.	7940084772
US order No.	MA15D1SI
Version	Surge protection, MA15 Series
GTIN (EAN)	

MA15 Series OVP 120V 15A w. Filter,LED

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Weight	100 g
--------	-------

Temperatures

Humidity	Note: room temperature (service)	All values are typical at 25 °C, unless otherwise specified
95 %, no condensation		

Approvals

Approval for	AC Power Product, Hazardous Locations Class 1, Division 2 Groups A,B,C,D T4	Approvals
Approvals	UL 1449 Recognised Component, UL 1604, Hazardous Locations Class 1 Division 2 Groups A, B, C and D	

Rated data

Leakage current, max.	0.3 mA
-----------------------	--------

Surge Protection

Attenuation	-55dB @ 100 MHz max, typical	Continuous operating current, max.	15 A
EMC standards	BS EN 60950: 1992, BS EN 61000-6-2: 1999	Humidity	95 %, no condensation
Indication	Green LED for protection available, Green LED off - internal error	Leakage current, max.	0.3 mA
Limiting voltage	295V @ 500A ring, 320V @ 500A 8/20 µs, 396V @ 3kA 8/20 µs, 595V @ 10kA 8/20 µs	Modes protected	L-N, L-G, N-G
Mounting rail	TS 32, TS 35	Terminals	2.5 mm ² (12 AWG)
Type of connection	Screw connection		

Classifications

eClass 6.2
