

GNM0M2R61A104ME17#

“ # ” indicates a package specification code.

To be discontinued

General



85℃

Reflow OK

RoHS

< List of part numbers with package codes >
GNM0M2R61A104ME17D , GNM0M2R61A104ME17J

Shape



L size	0.9 ± 0.05mm
W size	0.6 ± 0.05mm
T size	0.45 ± 0.05mm
Distance between external terminals P	0.45 ± 0.05mm
Size code in inch(mm)	0302 (0906)

References

Packaging	Specifications	Minimum quantity
D	180mm Paper taping	10000
J	330mm Paper taping	40000

Mass (typ.)	
1 piece	1.4mg
180mm Reel	114g

Specifications

Capacitance	0.10μF ± 20%
Rated voltage	10Vdc
Temperature characteristics (complied standard)	X5R(EIA)
Capacitance change rate	± 15.0%
Temperature range of temperature characteristics	-55 to 85
Operating temperature range	-55 to 85

⚠ Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ’ s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.