


SBP200375WE2.5 Product Details



SBP200375WE2.5

TE Internal Number: CN9936-000
✔ Active

Label ID Products

✔ Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Labels
- Region = Not Specified
- Printer Type = Thermal Transfer
- Label Height = 95.30 mm
- Label Width = 50.80 mm

Documentation & Additional Information	
Product Drawings: • None Available Catalog Pages/Data Sheets: • None Available Product Specifications: • None Available Application Specifications: • None Available Instruction Sheets: • None Available CAD Files: • None Available	Additional Information: • Product Line Information Related Products: • Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: • Product Type = Labels • Series = SBP • Color = Clear (White Printable Area) Electrical Characteristics: • Printer Type = Thermal Transfer • Web Width (mm [in]) = 111.40 [4.386] Body Features: • Material = Translucent Vinyl • Horizontal Repeat (mm [in]) = 50.8 [2] • Recommended Printer = TE 3000 Series, T200 • Recommended Ribbon = TMS-RJS-RIBBON-4RPSCE Configuration Features: • Number of Labels Across = 2 Industry Standards: • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not reviewed for lead free solder process • RoHS/ELV Compliance History = Always was RoHS compliant	Printer/Label Features: • Label Height (mm [in]) = 95.30 [3.750] • Label Width (mm [in]) = 50.80 [2.000] • Label Finish = Gloss/Matte • Tamper Evident = No • Label Type = Die-Cut • Adhesive Type = Permanent Acrylic • Vertical Repeat (mm [in]) = 101.60 [4.000] • Printable Height (mm [in]) = 25.40 [1.000] Environmental: • Operating Temperature (°C [°F]) = -51 - +93 [-60 - +200] Conditions for Usage: • Energy Product = No Packaging Features: • Packaging Quantity = 2,500 Product Availability: • Region = Not Specified Other: • Brand = Raychem