


STANLEY

THE SCREWDRIVER REDEFINED

Provides Optimum
Torque, Performance
& Comfort under all
conditions.



266 577 to 266 802,
267-028 to 267-168,
MAGNUM

■ Chrome vanadium hardened and tempered blades – **Maximum strength and long life**

■ Innovative "Polinox" blade treatment – **Flake-free finish**

■ Lacquered blade – **Resists corrosion**

■ Winged bar set deep into handle – **Solid permanent joint**

■ Moulded polypropylene body – **Virtually unbreakable**

■ Integrally moulded thermo-plastic elastomer inserts – **Improved grip and comfort in use even in 'wet' conditions**

■ Innovative manufacturing technology pioneered by Stanley enables molecular bonding of the hard and soft materials in this unique handle, providing strength, durability and comfort to produce high torque performance.

■ Wide range of slotted cross-point and torx drivers available – **Covers virtually every requirement**

■ Moulding eliminates usual seam line over the end of handle – **Increased comfort**

**SLOTTED
PHILLIPS
TORX**

THE RANGE IN FULL

Product No	Blade Length mm/ins	Tip Width mm	Tip Thickness mm	Bar Diameter mm	Overall Length mm	No per Box
------------	------------------------	-----------------	---------------------	--------------------	----------------------	------------

FLARED

67-405	75/3"	4.0	0.8	4.0	162	6
67-406	100/4"	5.5	1.0	5.0	199	6
67-408	150/6"	6.5	1.2	6.0	249	6
67-409	150/6"	8.0	1.2	7.0	262	6
67-410	200/8"	8.0	1.2	7.0	312	6
67-411	200/8"	10.0	1.6	9.0	324	6
67-413	250/10"	10.0	1.6	9.0	374	6
67-414	300/12"	12.0	2.0	10.0	424	6
67-437	40/1 1/2"	6.5	1.2	6.0	97	6

PARALLEL

67-419	75/3"	3.5	0.6	3.5	165	6
67-421	100/4"	4.0	0.8	5.5	199	6
67-424	150/6"	5.5	1.0	5.5	249	6
67-425	200/8"	5.5	1.0	5.5	299	6
67-427	250/10"	6.5	1.2	6.5	349	6

INSTRUMENT

67-416	75/3"	3.0	0.5	3.0	145	6
67-417	100/4"	3.0	0.5	3.0	170	6
67-418	150/6"	3.0	0.5	3.0	220	6

SQUARE BAR

67-431	100/4"	6.5	1.2	6.0	199	6
67-432	150/6"	8.0	1.2	7.0	262	6
67-433	200/8"	10.0	1.6	9.0	324	6
67-434	250/10"	10.0	1.6	9.0	374	6

Product No	Blade Length mm/ins	Point Size	Bar Diameter mm	Overall Length mm	No per Box
------------	------------------------	------------	--------------------	----------------------	------------

POZIDRIV

67-474	60/2 3/8"	0	3.18	130	6
67-475	75/3"	1	5.0	162	6
67-476	100/4"	2	6.0	199	6
67-477	150/6"	3	8.0	262	6
67-478	200/8"	4	9.5	324	6
67-479	250/10"	1	5.0	337	6
67-480	250/10"	2	6.0	349	6
67-481	30/1 1/4"	1	5.0	87	6
67-482	30/1 1/4"	2	6.0	87	6

PHILLIPS

67-454	60/2 3/8"	0	3.18	130	6
67-455	75/3"	1	5.0	162	6
67-456	100/4"	2	6.0	199	6
67-457	150/6"	3	8.0	262	6
67-458	200/8"	4	9.5	324	6
67-459	250/10"	1	5.0	337	6
67-460	250/10"	2	6.0	349	6
67-461	30/1 1/4"	1	5.0	87	6
67-462	30/1 1/4"	2	6.0	87	6

TORX

67-494	80/3 1/4"	T10	4.0	167	6
67-495	80/3 1/4"	T15	4.0	167	6
67-496	100/4"	T20	4.0	187	6
67-497	100/4"	T25	5.0	199	6
67-498	125/5"	T27	5.5	224	6
67-499	125/5"	T30	5.5	224	6
67-500	125/5"	T40	6.0	237	6

STANLEY

MAGNUM

Available loose (Product No I- prefix)
or carded (Product No -0- prefix)

See current price list for details

POZIDRIV

STANLEY

The best tools you can lay hands on

We reserve the right to amend specification without prior notice
Stanley Tools, The Stanley Works Ltd., Woodside, Sheffield S3 9PD
Tel No (0742) 768888 Telex 54150 Fax (0742) 739038

SALES OFFICE FAX. NO. (0709) 532465

LT132 APRIL 1992

Pozidriv is the registered trademark of European Industrial Services
Torx is a registered trademark of Textron