



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes





6B

TERM. NO.'s FOR REF. ONLY
CUSTOMER TERM. NO.'s IN ()



LOT CODE & DATE CODE



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	5-6 @20°C	0.032 ohms ±20%
D.C. RESISTANCE	4-7 @20°C	0.032 ohms ±20%
D.C. RESISTANCE	1-10 @20°C	0.285 ohms ±20%
INDUCTANCE	5-6 tie(4+5, 6+7), 100kHz, 100mVAC, Ls	2.70uH ±10%
DIELECTRIC	5-1 tie(4+5, 6+7), 625VAC, 1 second	500VAC, 1 minute
TURNS RATIO	(1-10):(5-6), tie(4+5, 6+7)	4:1, ±1%

6D

6C GENERAL SPECIFICATIONS:
OPERATING TEMPERATURE RANGE: -40°C to +125°C.

REV.	DATE
6D	4/08
6C	10/07
6B	7/07
6A	5/07

DETAILS SUBJECT TO CHANGE

Packaging Specifications
Method: Tape & Reel
PKG-0499
www.midcom-inc.com

6B

Unless otherwise specified:
Tolerances: Fractions: ±1/64
Angles: ±1° Decimals: ±.005[.127]
This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE

TRANSFORMER

eiSos p/n: 750310084



DRAWING NO.

750310084

REVISIONS: SEE SHEET 1

SCALE ---

SHEET 2 OF 5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Electronics:](#)

[750310084](#)