

HONEYWELL
PART NUMBER

BZ-2RL131T

CATALOG LISTING

BZ-2RL131T


AJH9600

REPLACES: X201840-BZ

REV	DOCUMENT	CHANGED BY		CHECK
A	0050465	MBN	31MAR09	CMH

B


A



6-32 UNC X (.218) BINDER
HEAD TERMINAL SCREW AND
LOCKWASHER (SEMS) (3)

NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 - WEIGHT: .063 LB

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: INCH		DRAWN	MBN	25 MAR 09	Honeywell					
OPERATING FORCE - - - - - 10 OZ MAX		CONTACT ARRANGEMENT		TOLERANCES UNLESS NOTED:		CHECK	DB	25 MAR 09						
RELEASE FORCE - - - - - 1/4 OZ MIN		S P D T		NO PLACES X ± -		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE					
DIFFERENTIAL TRAVEL - - - - - .020 MAX		-L96- 15 A-125, 250, OR 480 VAC 1/2 A-125 VDC; 1/4 A-250 VDC 1/8 HP-125 VAC, 1/4 HP-250 VAC		ONE PLACE .X ± .030					SWITCH - BASIC					
OVER TRAVEL - - - - - .060		-L288- -L306- -L315-		THREE PLACE .XX ± .015		INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	CAGE CODE	DRAWING NAME		REV
		CE  16A 250V ~ T85 5E4		TWO PLACE .XXX ± .005					B	I	-	BZ-2RL131T		A
				ANGLES X ± -		THIRD ANGLE PROJECTION			SCALE		NONE	SHEET		OF
						RASTER								