


NOTES:

1. MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01)
2. COLOR: BLACK.
COLOR WHITE AVAILABLE BY SPECIAL ORDER ONLY.

PART NO.	MAXIMUM PANEL THICKNESS	HOLE DIAMETER	"A"±.020	"B" REF
PGM-1	.062 [1.57]	.250±.003 [6.35±0.08]	.312 [7.9]	.312 [7.9]
PGM-2		.312±.003 [7.9±0.08]	.375 [9.5]	
PGM-3		.468±.002 [11.9±0.05]	.531 [13.5]	
PGM-4	.067 [1.7]	.189±.004 [4.8±0.1]	.236 [6]	.205 [5.2]
PGM-5	.062 [1.57]	.500±.002 [12.7±0.05]	.562 [14.3]	.250 [6.35]
PGM-6	.067 [1.7]	.252 [6.4±0.1]	.299 [7.6]	.221 [5.6]
PGM-7	.063 [1.6]	.278±.002 [7.05±0.05]	.433 [11]	.276 [7]
PGM-8		.307±.008 [7.8±0.2]	.375 [9.5]	.236 [6]
PGM-9		.376±.002[9.55±0.05]	.511 [13]	.256 [6.5]
PGM-10	.055 [1.4]	.386±.008 [9.8±0.2]		.236 [6]
PGM-11	.062 [1.57]	.531±.002 [13.48±0.05]	.593 [15.1]	.250 [6.35]
PGM-12		.625±.002 [15.9±0.05]	.718 [180.2]	
PGM-13	.083 [2.1]	.506±.006 [12.85±0.15]	.669 [17]	.315 [8]
PGM-14	.062 [1.57]	.750±.002 [19.05±0.05]	.843 [21.4]	.250 [6.35]
PGM-15		.781±.002 [19.84±0.05]	.890 [22.6]	
PGM-16	.079 [2]	.628±.002[15.95±0.05]	.787 [20]	.315 [8]
PGM-17	.062 [1.57]	.875±.002 [22.22±0.05]	.968 [24.6]	.250 [6.35]
PGM-18	.125 [3.2]	1.250±.002 [31.75±0.05]	1.375 [34.9]	.465 [11.8]
PGM-19		.746±.002 [18.95±0.05]	.925 [23.5]	.413 [10.5]
PGM-20		1.375±.002 [34.93±0.05]	1.500 [38.1]	.465 [11.8]
PGM-21		1.750±.002 [44.45±0.05]	1.906 [48.4]	
PGM-22	.118 [3]	.864±.002 [21.95±0.05]	1.024 [26]	.378 [9.6]
PGM-23	.125 [3.2]	2.000±.002 [50.8±0.05]	2.170 [55.1]	.470 [11.9]
PGM-24		.500±.002 [12.7±0.05]	.578 [14.7]	.406 [10.3]
PGM-25		1.004±.004 [25.5±0.1]	1.102 [28]	.500 [12.7]
PGM-26		.562±.002 [14.27±0.05]	.656 [16.7]	.406 [10.3]
PGM-27		.625±.002 [15.88±0.05]	.718 [18.2]	
PGM-28		.687±.002 [17.45±0.05]	.781 [19.8]	
PGM-29		.875±.002 [22.22±0.05]	1.125 [28.6]	.453 [11.5]
PGM-30		1.203±.002 [30.55±0.05]	1.339 [34]	.512 [13]
PGM-31		1.500±.002 [38.1±0.05]	1.671 [42.4]	.465 [11.8]
PGM-32		1.097±.004 [27.86±0.1]	1.218 [30.9]	
PGM-33		.375±.002 [9.5±0.05]	.468 [11.9]	.406 [10.3]
PGM-34		.437±.002 [11.1±0.05]	.531 [13.5]	

TITLE: PUSH GROMMET HOLE PLUG [M SERIES]



DWG IN IN [MM]



CREATED USING SOLIDWORKS

FILE #: PGM

DWN: SK

APP: SK

FINAL

TOLERANCES UNLESS NOTED

SHEET: 1 OF 1

SHEET SIZE: A

DT: 02/14/08

CHKD: D.Z

PART #

PRINT TYPE

XX=±.010
XXX=±.005
FRAC.=±1/64
ANG.=±1°

RE: RICHCO, INC.

RICHCO, INC.
ENG@RICHCO-INC.COM
(773) 539-4060

SEE TABLE

CA

F	SEE CO 200321 FOR CHANGES	SK	02/09/09
-	SEE ENGINEERING FOR REV A-E	-	----
REV.	DESCRIPTION	ENGR.	DATE