

Power



- ## "X" Mounting - Drawing




Mtg. Style	Dimensions (Inches)							
	A	B	C	D	F	G	H	J
Z6	2.00	2.50	2.50	1.75	2.00	1.06	3.00	2.50
Z7	2.25	2.88	3.25	1.88	2.38	1.25	3.38	2.81
Z8	2.25	2.81	3.63	1.75	2.25	1.50	3.38	2.81
Z9	2.50	3.13	3.81	2.00	2.69	1.33	3.75	3.13

Mtg. Style	Dimensions (Inches)					G-Mtg. Slot
	A	B	C	D	E	
X2	1.88	2.44	2.50	1.50	1.56	.19 x .31
X4	2.19	2.50	2.63	1.75	1.44	.19 x .25
X5	2.19	2.63	2.63	1.75	1.56	.19 x .25
X6	2.50	2.75	3.06	2.00	1.69	.203 x .38
X7	2.50	3.00	3.06	2.00	1.94	.203 x .38
X7A	2.50	3.00	3.13	2.00	2.06	.203 x .38
X7B	2.50	3.00	3.13	2.00	2.19	.203 x .38
X8	2.50	3.25	3.06	2.00	2.19	.203 x .38
X9	2.50	3.75	3.06	2.00	2.69	.203 x .38
X9A	2.88	3.50	3.50	2.25	2.44	.203 x .38
X9B	3.13	3.50	3.50	2.50	2.38	.203 x .38
X10	3.13	3.50	3.81	2.50	2.19	.203 x .38
X10A	3.13	3.50	3.88	2.50	2.38	.203 x .38
X11	3.13	3.75	3.81	2.50	2.44	.203 x .38
X13	3.75	4.00	4.56	3.00	2.81	.203 x .38
X14	3.75	4.50	4.56	3.00	3.31	.203 x .38
X15	3.75	5.00	4.56	3.00	3.81	.203 x .38
X19	3.13	4.00	3.81	2.50	2.69	.203 x .38

"Classic" Plate & Filament (263-282 Series)

Power

Part No.	VA	Primary		A.C. High Voltage Secondary (R.M.S.)	Filament #1 (VAC)	Filament #2 (VAC)	Dim. Ref.
		VAC	Hz.				
263AX	32	115	60	200V C.T. @ 115ma.	5V @ 2A	-	X2
269AX	40	115	60	250V C.T. @ 115ma.	6.3V @ 2A	-	X4
269BX	38	115	60	300V C.T. @ 86ma.	6.3V @ 2A	-	X4
263CX	116	115	60	360V C.T. @ 287ma.	5V C.T. @ 3A	-	X9
269EX	43	115	60	380V C.T. @ 71ma.	6.3V @ 2.5A	-	X5
269GX	48	115	60	450V C.T. @ 75ma.	6.3V @ 2.5A	-	X5
270X	41	115	60	480V C.T. @ 46ma.	5V @ 2A	6.3V @ 1.5A	X4
270AX	42	115	60	480V C.T. @ 58ma.	6.3V @ 2.5A	-	X4
269JX	50	115	60	500V C.T. @ 69ma.	6.3V @ 2.5A	-	X5
270CAX	65	117	50/60	500V C.T. @ 81ma.	5V @ 2A	6.3V @ 2.5A	X7A
270DAX	76	117	50/60	520V C.T. @ 104ma.	6.3V @ 3.5A	-	X7B
270DAZ	76	117	60	520V C.T. @ 104ma.	6.3V @ 3.5A	-	Z7
270BX	53	115	60	550V C.T. @ 57.5ma.	5V @ 2A	6.3V @ 2A	X6
270CX	59	115	60	550V C.T. @ 75ma.	6.3V @ 0.6A	6.3V @ 2.5A	X6
270DX	83	115	60	550V C.T. @ 104ma.	5V @ 2A	6.3V @ 3A	X7
270EX	118	115	60	550V C.T. @ 144ma.	5V @ 3A	6.3V @ 4A	X9
270FX	138	115	60	550V C.T. @ 173ma.	5V @ 3A	6.3V C.T. @ 5A	X10
270HX	176	115	60	550V C.T. @ 230 ma.	5V C.T. @ 3A	6.3V C.T. @ 6A	X19
271X	63	115	60	560V C.T. @ 69ma.	5V @ 2A	6.3V C.T. @ 2A	X6
272BX	95	115	60	600V C.T. @ 115ma.	5V @ 2A	6.3V @ 3A	X8
272DX	123	115	60	600V C.T. @ 144ma.	5V @ 3A	6.3V @ 4A	X9
272FX	146	115	60	600V C.T. @ 172ma.	5V C.T. @ 3A	6.3V C.T. @ 5A	X10
272HX	186	115	60	600V C.T. @ 230ma.	5V C.T. @ 3A	6.3V C.T. @ 6A	X19
272JX	236	115	60	600V C.T. @ 287ma.	5V C.T. @ 4A	6.3V C.T. @ 8A	X13
272X	74	115	60	620V C.T. @ 80ma.	5V @ 2A	6.3V @ 2.4A	X7
276X	150	115	60	640V C.T. @ 172ma.	5V C.T. @ 3A	6.3V C.T. @ 5A	X10
273AZ	49	117	50/60	650V C.T. @ 46ma.	5V @ 2A	6.3V @ 2A	Z6
273CZ	159	117	50/60	650V C.T. @ 172ma.	5V @ 3A	6.3V C.T. @ 5A	Z9
273DX	101	117	50/60	700V C.T. @ 103ma.	5V @ 2A	6.3V C.T. @ 3A	X9A
273DZ	101	117	50/60	700V C.T. @ 103ma.	5V @ 2A	6.3V C.T. @ 3A	Z8
273X	120	115	60	700V C.T. @ 126ma.	5V @ 2A	6.3V C.T. @ 4A	X9
273BX	182	115	60	700V C.T. @ 201ma.	5V @ 3A	6.3V C.T. @ 5A	X19
274AX	137	117	50/60	720V C.T. @ 138ma.	5V @ 3A	6.3V C.T. @ 3.5A	X10A
274X	138	115	60	750V C.T. @ 126ma.	5V @ 3A	6.3V C.T. @ 5A	X10
274BX	198	115	60	750V C.T. @ 201ma.	5V C.T. @ 3A	6.3V C.T. @ 6A	X19
275X	167	115	60	800V C.T. @ 155ma.	5V C.T. @ 3A	6.3V C.T. @ 5A	X11
278X	229	115	60	800V C.T. @ 230ma.	5V C.T. @ 3A	6.3V C.T. @ 6A	X19
278CX	454	115	60	800V C.T. @ 535ma.	6.3V C.T. @ 6A	-	X15
279X	186	115	60	850V C.T. @ 172ma.	5V @ 3A	6.3V C.T. @ 5A	X19
282X	273	115	60	1,000V C.T. @ 230ma.	5V C.T. @ 3A	6.3V C.T. @ 6A	X14



Notes : Filament #1 and #2 windings may not exist or may not have C.T. connections. Refer to table above.

EUROPE

Basingstoke, UK 01256 812812

AUSTRALIA

Queenstown, Australia 61-8-8240-2244

www.hammondmfg.com



CANADA

Guelph, Ontario (519) 822-2960
St. Laurent, Quebec (514) 343-9010

USA

Cheektowaga, NY (716) 630-7030



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Hammond:

[263CX](#) [263AX](#) [270HX](#) [270DAZ](#) [270DAX](#) [282X](#) [273CZ](#) [270CX](#) [270AX](#) [270EX](#) [270CAX](#) [276X](#) [272X](#) [269BX](#)
[269AX](#) [269JX](#) [269GX](#) [278CX](#) [274BX](#) [274AX](#) [273BX](#) [273AZ](#) [273DZ](#) [273DX](#) [270BX](#) [270FX](#) [270DX](#) [272JX](#)
[272HX](#) [272BX](#) [273X](#) [270X](#) [275X](#) [271X](#) [272DX](#) [279X](#) [272FX](#) [274X](#) [278X](#)