

The drawing consists of two parts. The top part is a side view of the 'NYLON PLASTIC CINCH RING'. It shows a U-shaped ring with a central slot. Dimension lines indicate: 'E' for the height of the ring, 'C REF.' for the width of the central slot, 'B' for the thickness of the ring material, and 'F REF.' for the overall length of the ring. The bottom part shows a side view of a cable being secured by the cinch ring. Dimension lines indicate: 'A' for the thickness of the cable and 'D' for the height of the cinch ring when it is clamped onto the cable.

| PANDUIT<br>PART NO. | BUNDLE DIA.     |                 | A<br>in (mm)  | B<br>in (mm)  | C<br>in (mm)  | D<br>in (mm) | E<br>in (mm)   | F<br>in (mm)  | MIN. LOOP<br>TENSILE lbs.<br>(N) | CROSS<br>SECTION | APPROXIMATE WEIGHT<br>lbs/100 PARTS (g) |
|---------------------|-----------------|-----------------|---------------|---------------|---------------|--------------|----------------|---------------|----------------------------------|------------------|-----------------------------------------|
|                     | MIN. in<br>(mm) | MAX. in<br>(mm) |               |               |               |              |                |               |                                  |                  |                                         |
| UCT3S               | .63<br>(16.0)   | 3.0<br>(76.2)   | .100<br>(2.5) | .85<br>(21.6) | .45<br>(11.4) | .14<br>(3.6) | 1.10<br>(27.9) | 12.0<br>(305) | 50<br>(222)                      | STANDARD         | .59 (267)                               |
| UCT5S               | .63<br>(16.0)   | 5.0<br>(127)    | .100<br>(2.5) | .85<br>(21.6) | .45<br>(11.4) | .14<br>(3.6) | 1.10<br>(27.9) | 18.0<br>(457) | 50<br>(222)                      | STANDARD         | .81 (366)                               |

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.  
2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

SS\_27366\_00.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

TAK-TY HOOK & LOOP CABLE TIES  
ULTRA-CINCH HOOK & LOOP TIES

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± .25      (.XXX) ± .030  
(.XX) ± .125      ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY  
JABO

MAT'L:

SCALE NONE

|      |         |
|------|---------|
| DATE | 6/19/02 |
|------|---------|

WOVEN NYLON  
HOOK/LOOP  
COLOR: BLACK

DRAWING NO.

SS-27366

DWG  
A  
SIZE

|     |         |     |     |                    |       |     |      |     |  |
|-----|---------|-----|-----|--------------------|-------|-----|------|-----|--|
|     |         |     |     |                    |       |     |      |     |  |
|     |         |     |     |                    |       |     |      |     |  |
|     |         |     |     |                    |       |     |      |     |  |
|     |         |     |     |                    |       |     |      |     |  |
|     |         |     |     |                    |       |     |      |     |  |
|     |         |     |     |                    |       |     |      |     |  |
|     |         |     |     |                    |       |     |      |     |  |
| 7   | 4/12/06 | FAB |     | ADDED PART WEIGHTS | 27366 | 7   |      |     |  |
| REV | DATE    | BY  | CHK | DESCRIPTION        | ECN   | - R | CUST | SUP |  |