


For use with: W 61, W 101, W 201

Description and Model	Width A	Order-No. 260°C	Order-No. 310°C	Order-No. 370°C	Order-No. 425°C
-----------------------	---------	--------------------	--------------------	--------------------	--------------------

For 60 W soldering iron (W61)

Chisel tip straight



1,6 mm

CT5A5

5 42 005 99

CT5A6

5 42 006 99

CT5A7

5 42 007 99

CT5A8

5 42 008 99

2,4 mm

CT5B5

5 42 015 99

CT5B6

5 42 016 99

CT5B7^①

5 42 017 99

CT5B8

5 42 018 99

3,2 mm

CT5C5

5 42 025 99

CT5C6

5 42 026 99

CT5C7

5 42 027 99

CT5C8

5 42 028 99

5,0 mm

CT5D5

5 42 035 99

CT5D6

5 42 036 99


CT5D7

5 42 037 99

CT5D8

5 42 038 99

Chisel tip bent (45°)



1,6 mm

CT5AX5

5 42 105 99

CT5AX6

5 42 106 99

CT5AX7

5 42 107 99

CT5AX8

5 42 108 99

2,4 mm

CT5BX5

5 42 115 99

CT5BX6

5 42 116 99

CT5BX7

5 42 117 99

CT5BX8

5 42 118 99

3,2 mm

CT5CX5

5 42 125 99

CT5CX6

5 42 126 99

CT5CX7

5 42 127 99

CT5CX8

5 42 128 99

5,0 mm

CT5DX5

5 42 135 99

CT5DX6

5 42 136 99

CT5DX7

5 42 137 99

CT5DX8

5 42 138 99

For 100 W soldering iron (W101)

Chisel tip straight



3,2 mm

-

CT6C6

5 42 206 99

CT6C7

5 42 207 99

CT6C8

5 42 208 99

5,0 mm

-

CT6D6

5 42 216 99

CT6D7

5 42 217 99

CT6D8

5 42 218 99

7,0 mm

-

CT6E6

5 42 226 99


CT6E7^①

5 42 227 99

CT6E8

5 42 228 99

Chisel tip bent (45°)



3,2 mm

-

CT6CX6

5 42 306 99

CT6CX7

5 42 307 99

CT6CX8

5 42 308 99

5,0 mm

-

CT6DX6

5 42 316 99

CT6DX7

5 42 317 99

CT6DX8

5 42 318 99

7,0 mm

-

CT6EX6

5 42 326 99

CT6EX7


5 42 327 99

CT6EX8

5 42 328 99

For 200 W soldering iron (W201)

Chisel tip straight



7,0 mm

-

CT2E6

5 42 406 99

CT2E7

5 42 407 99

CT2E8

5 42 408 99

10,0 mm

-

CT2F6

5 42 416 99

CT2F7^①

5 42 417 99

CT2F8

5 42 418 99

11,0 mm

-

CT2G6

5 42 426 99


CT2G7

5 42 427 99

CT2G8

5 42 428 99

Chisel tip bent



7,0 mm

^① Scope of delivery W61

-

CT2EX6

5 42 506 99

CT2EX7

5 42 507 99

CT2EX8

5 42 508 99

10,0 mm

-

CT2FX6

5 42 516 99

CT2FX7

5 42 517 99

CT2FX8

5 42 518 99