

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0872040153](#)
Status: **Obsolete**
Description: D-Subminiature Shielded I/O PCB Female Receptacle, Right Angle, Through Hole, 15 Circuits, 4-40 Hex Internal Thread Screws Assembled, Gold (Au) 0.38µm (15µ")
Replacement Part Number: NO REPLACEMENT PART AVAILABLE

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	I/O Connectors
Series	87204
Application	Wire-to-Board
Comments	Shell: Steel
Component Type	Receptacle
Obsolete Date	2006/06/01
Product Name	D-Sub, DB15
Replacement Part Number	NO REPLACEMENT PART AVAILABLE
Type	N/A


Physical

Circuits (Loaded)	15
Circuits (maximum)	15
Flammability	94V-0
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Orientation	Right Angle
PC Tail Length	3.18mm (.125")
PCB Retention	Yes
PCB Thickness - Recommended	1.00mm (.039")
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	2.77mm (.109")
Plating min - Mating	0.381µm (15µ")
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-55°C to +85°C
Termination Interface: Style	Through Hole
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	1A
Shielded	Yes
Voltage - Maximum	300V

Material Info



EU RoHS Not RoHS Compliant REACH SVHC Not Reviewed Low-Halogen Status Not Reviewed	China RoHS
--	-----------------------

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[87204Series](#)

Mates With
[87203](#)