


PANDUIT PART NUMBER	LENGTH	WEIGHT	 WEIGHT/LENGTH
FRSHC6**2 (SEE NOTE 1)	78.74 IN ±.18 IN (2000.0mm ±4.6mm)	2.95 LB (1338g)	0.45 LB/FT (6.6g/cm)
FRSHC6**6 (SEE NOTE 1)	72.00 IN ±.18 IN (1828.8mm ±4.6mm)	2.70 LB (1225g)	0.45 LB/FT (6.6g/cm)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBERRUNNER 6x4 SPLIT HINGED COVER REQUIRES NO TOOLS FOR INSTALLATION. THE SPLIT HINGED COVER CREATES A 3/4" (19.1) RADIUS OPENING TO ALLOW FOR NEW CABLES TO BE ADDED WITHOUT THE NEED FOR REMOVING THE COVERS.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D37847CL_DC_FRSHC6_01.prt

A diagram showing a triangle with its top vertex labeled 'B'.

\FRSHC6.pdf

PANDUIT CORP. TINLEY PARK, ILLINOIS

FIBERRUNNER 6x4 SPLIT HINGED
COVER (FRSHC6**2, FRSHC6**6)

CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ±	(.XXX) ±
(.XX) ±.03 (0.8)	ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JHNU

DATE 8-16-01

CHK'D DJWA

MAT'L:	
--------	--

PVC

SCALE	NONE
-------	------

DRAWING NO.
37847-77

DWG
A
SIZE

-	-----	---	---	G. REMOVED DIMENSION F. ADDED DIMENSIONS	-----	---	---		
-	-----	---	---	E. RELOCATED DIMENSION D. REVISED GENERAL NOTES	-----	---	---		
2	7-24-06	DTP	RN	C. REVISED ENTIRE CHART B. REVISED CAD FILENAME	37847-77	RN	RN		
1	9-19-02	JHNU	DJWA	A. REVISED TABLE: g/cm WAS g/FT	37847-77	RN	RN		
R	8-16-01	JHNU	DJWA	RELEASED TO PRODUCTION	37847-77	HIW	HIW		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMB