




FEATURES:

- Accepts .080 pin tip plugs
- Mounts in panels up to .250" thick.

MATERIAL:

Insulation – Polycarbonate - Molded to pin tip jack body
Lockwasher, #8 Internal Tooth – Steel - Nickel plated
Hex Nut, #8-32 – Brass – Nickel plated
Pin Tip Jack Body: Brass – Gold plated

RATINGS:

Operating Temperature: +115°C. (+239°F.) Max.
Operating Voltage: 1500 VDC
Current: 5 Amperes.

ORDERING INFORMATION: Model 3542-*

*=Color Code – See Tabulation Block
Sold in packages of 10

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA