







LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
1R	-		B2	DURABILITY CYCLE UPDATED AFTER TESTING	26AUG2011	PS	RRP
			-	-	-	-	-
			-	-	-	-	-
			-	-	-	-	-
			-	-	-	-	-




- NOTE:
- TOLERANCE UNLESS OTHERWISE SPECIFIED: $\pm 0,15$.
 - DURABILITY IS 200 CYCLES MAX ACCORDING TO TEST REPORT 502-19807 THIS WILL TAKE PRECEDENCE OVER THE PRODUCT SPECIFICATION.



2,54
1,27 TYP.
8,9



PRINTED CIRCUIT BOARD LAYOUT
[VIEW SHOWN IS CIRCUIT (NONCOMPONENT) SIDE OF BOARD.]
PRINTED CIRCUIT BOARD THICKNESS: 1,6 mm NOMINAL.
TOLERANCE UNLESS OTHERWISE SPECIFIED: $\pm 0,05$



200 PIECES IN A TRAY	8 POS./8 CONTACTS	IN CONTACT AREA: 0,15µm MIN. SEL. GOLD OVER 1,2µm MIN. NICKEL. SOLDER TINES: 2,5µm MIN. TIN OVER 1,2µm MIN. NICKEL.	HSG COLOR: GREY PBT. UL 94V-0	PBT. UL 94V-0	PH BRONZE	1705951-4			
1000 PIECES IN A BOX			HSG COLOR: GREY PBT. UL 94V-0	PBT. UL 94V-0	PH BRONZE	1705951-3			
1000 PIECES IN A BOX			HSG COLOR: BLACK PBT. UL 94V-0	PBT. UL 94V-0	PH BRONZE	1705951-2			
200 PIECES IN A TRAY			HSG COLOR: BLACK PBT. UL 94V-0	PBT. UL 94V-0	PH BRONZE	1-1705951-1			
TAPE MOUNTED 700 PCS./REEL			HSG COLOR: BLACK PBT. UL 94V-0	PBT. UL 94V-0	PH BRONZE	1705951-1			
PACKAGING	FINISH	MATERIAL	HOUSING	CONTACT INSERT	CONTACTS	PART NUMBER			
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN J.V.D.HEIJDEN						
			CHK P.WILLEMS						
			APVD J.BROEKSTEEG						
			PRODUCT SPEC 108-19064						
			APPLICATION SPEC 114-19019						
			SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO		
			A200779		C=1705951		-		
			CUSTOMER DRAWING				SCALE 5:1	SHEET 1 OF 1	REV B2