







APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/14/05	
A		REDRAWN	3/23/16	AY/CT
B		UPDATE DIM.	9/6/18	AY/TW



#4-40 UNC SCREWLOCK INSTALLED

SPECIFICATIONS:

Material:

Insulator: PBT, Thermoplastic, glass filled, rated UL 94V-0

Insulator color: Black

Contacts: Copper alloy

Shell: Steel, Tin plated

Boardlock: Brass, Tin plated

Screwlock: Steel, Nickel plated

Plating:

Gold flash over Nickel underplate on contact area.

Electrical:

Voltage rating: 250 VAC/rms

Current rating: 3 Amp

Contact resistance: 20 mohms

Insulation resistance: 1,000 Mohms @ 500 VDC

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Environmental:

Lead free, RoHS compliant.



DXXX	NO. OF CONTACTS	DIMENSIONS				
		A	B	C	D	E
DE09	9	1.213 [30.81]	.984 [24.99]	.666 [16.92]	.436 [11.08]	.756 [19.20]
DA15	15	1.543 [39.20]	1.311 [33.30]	.994 [25.25]	.763 [19.39]	1.091 [27.70]
DB25	25	2.089 [53.05]	1.852 [47.04]	1.534 [38.96]	1.309 [33.24]	1.618 [41.10]
DC37	37	2.732 [69.40]	2.500 [63.50]	2.182 [55.42]	1.963 [49.86]	2.256 [57.30]

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS		DATE
DRAWN	SS	4/14/05
CHECKED		
APPROVED		

ADAM
TECH
 INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE
 D-SUB PLUG, RIVETED #4-40 JACKSCREWS
 RIVETED #4-40 STANDOFFS W/BOARDLOCKS

SIZE	PART NO.	REV.
X	DXXX-PT-1-BL-JS	B
REF: S00087T	SCALE: NTS	SHEET 1 OF 1