

4

3

2

1

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT - By -		ALL RIGHTS RESERVED.	
PROJECT	PRJ-16-000909157		
PART NO.	X-2308346-X		
DESCRIPTION	FULL METAL HOODS SIZE 5		
CUSTOMER	GENERAL MARKET		


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECR-16-013123	19SEP2016	KK	GG

D


C

B

A



1-2308346-7



D

C

B

A

NOTES:

- FINISH:
- 1-2308346-1 TO 1-2308346-8 - CASE RAW
 - 1-2308346-9 TO 2-2308346-6 - CASE NICKEL-PLATED
 - LOCKING SCREWS: NICKEL-PLATED
 - OTHER SCREWS: ZINC-PLATED
 - TEMPERATURE RANGE: -40°C TO +90°C
 - CABLE DIAMETER WITH EXTERNAL DIAMETER CABLE CLAMP: 8-16 mm.
 - STRAND DIAMETER OF CRIMP FLANGE: 3.7-10.7 mm.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KIRAN K 29JUL2016	TE Connectivity		
		CHK GUNASEKHAR G 29JUL2016			
DIMENSIONS: mm		APVD GUNASEKHAR G 29JUL2016	NAME FULL METAL HOODS SIZE 5		
		PRODUCT SPEC			
		APPLICATION SPEC			
MATERIAL		WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C=2308346
		CUSTOMER DRAWING	SCALE NTS	SHEET 1 OF 2	REV A1

1471-9 (1/15)