




FEATURES:

- ✓ Ideal test adapters for rapid testing of the hard-to-get to sockets of multi-socket connectors.
- ✓ Flexible tip allows testing of adjacent contacts.
- ✓ Full insulation protects against shorting or contact damage.

MATERIALS:

Insulation: Polyvinyl chloride (PVC).

Banana Jack Body (upper connector)

Material: Brass.

Finish: Bright Tin plated

Pin (lower connector):

Material: Brass

Finish: Gold plated over nickel plating

Model	Contact Size	Type	Current
4691	22 AWG .030" (.76mm)	Pin	5 Amps
3561	20 AWG .040" (1.02mm)	Pin	7.5 Amps
3563	16 AWG .063" (1.60mm)	Pin	13 Amps
3565	12 AWG .093" (2.36mm)	Pin	24 Amps

Ratings:

Hands free testing in controlled voltage environments:
2500 Vrms Max. *For CE compliance:* not intended for
hand-held use at voltages above 33 Vrms/70 Vdc.
Operating Temperature: +131F (+55C) Max.

ORDERING INFORMATION: Model: 3561-*, 3563-*, 3565-*, 4691-*

*=Color, -0 Black, -2 Red Ordering Example: 3561-2 (red adapter)

Test Kit 6481: contains 18 pieces, one red and one black adapter of each adapter; 3560, 3561, 3562, 3563, 3564, 3565, 4690, 4691 and one set of model 6358 test leads.

For banana jack to test sockets see models: 3560, 3562, 3564, 4690

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Sales: 800-490-2361 Fax: 888-403-3360 Technical Support: 800-241-2060 (technicalsupport@pomonatest.com)

For "Where to Buy" information, visit the Pomona web site at www.pomonaelectronics.com