



GREENLEE®
A Textron Company

MADE FOR THE TRADE!™

PUNCH-ISO 25 (UPC)

Standard Slug-Splitter Knockout Punches



Image
Unavailable

Cat No: 04602

UPC No: 783310046028

Description

- Slug-Splitter SC heavy-duty punches are designed to punch up through 10 gauge (3.5 mm) stainless steel
- Unique slug-splitting design and tool steel construction easily punch 10 gauge (3.5 mm) mild steel and stainless steel
- Self-centering punch aligns itself on pilot hole. (Slug-Splitter SC)
- No need to draw crosshairs or line up die alignment marks
- (Slug-Splitter SC)
- Unique punch profile also splits slugs for easier slug removal
- Heavy-duty dies and stainless steel draw studs for longer life
- Excellent abrasion resistance for punching fiberglass and plastic
- Slug-Splitter SC punch units consist of: punch, die and draw stud
- Check individual punch for specific capacity
- U.S. Patent No. 4,543,722 for standard Slug-Splitter
- Patent Pending for Self-centering Slug-Splitter SC

Specifications

- Application : For Standard Slug-Splitter Knockout Punch Unit
- Capacity Stainless Steel : 10 GA (3.500 MM)
- Draw Studs :
 - 31872, 29452 Hydraulic Driver
 - 30227 Ratchet Driver
- ISO : 25
- Size : 1.000 IN (25.400 MM)