










- 5 UL/CSA DESIGNATION STAMPED IN THIS AREA, OPTIONAL.
- 6 STEEL PER ASTM-A-109.
- 7 BRASS PER MIL-C-50 AND ASTM-B-36 UNS NO. C26000.
- 8 FINISH: CADMIUM PLATED PER QQ-P-416.
- 9 GOLD PLATED PER MIL-G-45204 TYPE II, GRADE C, CLASS 1 OVER COPPER PER MIL-C-14550, CLASS IV.
- 10 FINISH: TIN PER ASTM-B-545 .000400 MIN THK OVER COPPER PER AMS2418 .000050 MIN THK.
- 11 FINISH: ZINC PLATE PER ASTM-B-633 .000200-.000400 THK WITH SUPPLEMENTARY CHROMATE (Cr3+).



	.120	—	5-212542-4
	.120	—	5-212542-1
	.120	—	212542-4
	.154	311P405-21S-B-15	212542-3
	.120	311P405-21S-B-12	212542-2
	.120	—	212542-1
REMARKS	ØA	GSFC P/N	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. C.C. THOMAS 21.JAN88 CHK. A. EMADI APP'D. 27.JAN88		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
		PRODUCT SPEC APPLICATION SPEC		RECEPTACLE ASSEMBLY AMPLITUDE 27C2 SIZE 4, SERIES 109, COAX MIX	
MATERIAL		WEIGHT		SIZE CASE CODE DRAWING NO A1 00779 C 212542	
FINISH		CUSTOMER DRAWING		RESTRICTED TO SCALE 4:1 SHEET 1 OF 1 REV N	