

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130025-0076](#)
Status: **Active**
Overview: [Brad® Mini-Change® Connectors](#)
Description: DeviceNet* Thick Stranded Cable, Double-Ended Mini-Change Cordset, 5 Poles, Female (Straight) to Male (Straight), 6.0m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Cordsets
Series [130025](#)
Connector End A Mini-Change®
Connector End B Mini-Change®
IP Rating IP67
Overview [Brad® Mini-Change® Connectors](#)
Product Name DeviceNet* Trunk, Mini-Change®
Type Double Ended
UPC 78678829919

Physical

Cable Diameter 12.10mm (.480")
Cable Length 6.0m (19.68')
Color - Cable Jacket Gray
Coupling Style Threaded
Gender Female-Male
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Contact Copper
Material - Coupling Nut Die-Cast Zinc
Material - Plating Mating Gold over Nickel
Net Weight 45.780/g
Orientation Straight
Poles 5
Temperature Range - Operating -20°C to +80°C
Wire Size AWG 18
Wire/Cable Type N/A


Electrical

Current - Maximum per Contact 4A
Voltage - Maximum 300V AC/DC

Material Info

Old Part Number DN11A-M060

*DeviceNet is a trademark of the ODVA



Series

image - Reference only

EU RoHS

RoHS Compliant by Exemption

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130025Series](#)