


Die Cut PCM SCR Darlington Module



Features

Low thermal resistance
Natural tack

Applications

SCR Darlington Module

Properties

-  REACH Compliant
-  RoHS Compliant

Property	PC99	Unit	Tolerance	Test Method
Colour	Yellow	-	-	Visual
Thickness	0.06	mm	-	ASTM D374
Phase Change Softening Point	52	°C	-	-
Specific Gravity	2.35	g/cm ³	±0.2	ASTM D792
Working Temperature	-40 to 200	°C	-	-
Surface Resistance	>10 ¹²	Ohm-cm	-	ASTM D257
Elongation	5	%	±13	ASTM D412
Tensile Strength	0.1	Kgf/cm ²	-	ASTM D412
Standard Shape	-	Sheets 320-320mm	-	-
Thermal Resistance 30psi	0.1	°C-cm ² /w	-	-

Dimensions / mm							Ordering part number
A	B	C	D	E	F	G	
93	50	80.00	38.1	6			DC0040/01 - XXX - T
94	86.1	80.00	73.9	5.6			DC0040/02 - XXX - T
95.00	62	80	48	6			DC0040/03 - XXX - T
98	64	63	52.1	6			DC0040/04 - XXX - T
102.1	91	80	73.9	6.4			DC0040/05 - XXX - T
108	62	93	48	6.4			DC0040/06 - XXX - T
113	90	93	70.1	6.4			DC0040/07 - XXX - T
114	114	93	93	6.4			DC0040/08 - XXX - T
139.7	94	80	80	8.3			DC0040/09 - XXX - T
160	76.7	80	62.7	6.8			DC0040/10 - XXX - T
190.5	94	80	80	6.8			DC0040/11 - XXX - T