

TP1414

TP1414

TP1414 : VIN RG 1614, SD 12, 1/4



ACTIVE

RoHS compatible

Assistant

Add to Favorites

Email Datasheet

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Price request

Specifications

Download document

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Stud Hole (Size)	#3 1/4 in. #10 #8 #6 #4 #2 #1 #12		
Tongue Width (in)	0.4 in.		
Wire Insulation Grip	No		
Insulation Diameter (Max)	0.18 in.		
Physical			
Conductor Size	14 AWG 16 AWG		
Element A Index	Hand Tools		
Insulation Type	PVC		
Color Code	Blue		
Conductor Size (Range)	16 AWG to 14 AWG		
Approvals / Certifications			
Military Listed	No		
UL Listed	Yes		
CSA Certified	Yes		
Other Features			
Tape Mounted Catalog Number	BA14E14M		
Tongue Type	Ring		
Bulk Catalog Number	BA14E14		
UPC	78181071304		
Keyword	smlterm		