

[Request more info](#)**Part Number : 5219240F**

5219240F



This is a
RoHS Compliant Product
[To learn more click here](#)

General Description

Series	521
Configuration	5 mm Lens
Description	Discrete LED Lamp
Package Options	Bulk Packaging
Sizes	5mm
Lamp Type	Single Color
Lens Color	Tinted Diffused

Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	25mA
Forward Current Pulsed	60mA
Solder Temperature	260° for 5 sec
Operating Temperature	-55~+100
Storage Temperature	-55~+100

Operating Characteristics

LED Type	GaAsP/GaP
Color	Red 
Luminous Intensity Min	2.2
Luminous Intensity Typical	6.3
Test Current mA	10mA
Power Dissipation Max	60mW

[Share](#) |

|