

TORQUE CONTROL

Electronic torque wrenches

Series E.306A

For accurate torquing, control and traceability!

AVAILABLE
NOVEMBER 2009
IN UK



PERFORMANCE:

- High Performance even under intensive use: accurate to $\pm 2\%$ ± 1 digit.
- Can be preset to 9 torque values.
- USB connection allows storage of 250 values.

ERGONOMIC:

- LEDs remain visible, even where access is difficult.
- Ultra simple to use: self test and reset when switched on.
- Visual and audible indications (LEDs and beeper).

The ultra-simple operation and affordable price make this the ideal tool for both workshop and laboratory.

► Electronic indicating torque wrenches

- ISO 6789 - DIN EN ISO 6789 – NF EN ISO 6789.
- Accuracy:
 - $\pm 2\%$ from 20% to 100% of full scale reading.
- Measuring mode: peak or tracking.
- Measuring units N.m, ft.lb ; in.lb ; Kg.cm.
- 9x12 or 14x18 end fittings.
- Numbered and supplied with a calibration certificate ISO 6789 and supplied in a foam-lined plastic case.

		Electronic torque wrench	Nm Min -max	End fitting	☒	Ratchet	Length
E.306A30R	3148518349536	30 Nm	1,5 - 30	9 x 12	1/4"	R.372	390 mm
E.306A135J	3148518349611	135 Nm	6,7 - 135	9 x 12	3/8"	J.372V	415 mm
E.306A135S	3148518349703	135 Nm	7 - 135	9 x 12	1/2"	S.372V	415 mm
E.306A200S	3148518349888	200 Nm	10 - 200	14 x 18	1/2"	S.382V	530 mm
E.306A340S	3148518349963	340 Nm	17 - 340	14 x 18	1/2"	S.382V	650 mm

Torque testers

Torque testing available to all!

Series E.2000

AVAILABLE
NOVEMBER 2009
IN UK

FAST AND SIMPLE:

- Very easy to use with minimum adjustment to avoid errors.
- For anything from a quick test before using a wrench up to an ISO6789 calibration certificate.
- 3 testers to cover a large torque range from 2 to 1000 Nm.

