


LOC	DIST	P	F	REVISIONS			DATE	APPD
				ZONE	LTR	DESCRIPTION		
G	86				E	REV PER 0G3A-0561-01	07OCT02	JR MS



1 CIRCULAR MIL AREA RANGE: 275-325 MCM
2 TIN PL 0.00381 [.000150] MIN THK PER MIL-T-10727

OBSOLETE	.208 lbs	REQD	9.91 [.390]	3/8	276917-2
	.211 lbs	NONE	8.33 [.328]	5/16	276917-1
	WEIGHT	SIGHT HOLE	A	B	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.51 [.020] 3 PLC DEC ± - ANGLES ± - MATERIAL ANNEALED COPPER ASTM B-75 FINISH △	DR 03/09/90 DK SCHRUM	AMP AMP INCORPORATED Harrisburg, Pa. 17105			
	CHK 23JAN95 MS FEHER				
	APPD 23JAN95 WJ VOCKROTH	NAME TERMINAL, AMPOWER, WIRE SIZE: 300 MCM			
	APPD 23JAN95 TL SHUTTER				
	PRODUCT SPEC 108-30200	SIZE C CAGE CODE 00779 DRAWING NO 276917			
	APPLICATION SPEC -				
	WEIGHT -	SCALE 2:1	SHEET 1 OF 1		

