

Bergquist Part Number: 400430

Revision: A

Description: 12.1" 8-wire Resistive Touch Screen

Mechanical Dimensions and Construction.

	Specification	Remarks
Overall Dimensions	268.00mm x 204.00mm	+/- .50mm
Overall Thickness	2.1mm	+/- .30mm
Viewable Area	250.00mm x 188.00mm	+/- .50mm
Active Area	246.00mm x 185.00mm	+/- .50mm
Nominal Glass Thickness	1.8mm	

*See mechanical drawing for additional specification

Environmental Specification

	Specification	Remarks
Operating Temperature	-10° C ~ +60° C	
Storage Temperature	-40° C ~ +80° C	
Constant Temperature/ Humidity	70° C/ 80% RH/ 500 Hrs.	Tested at ambient temperature after cycle
Thermal Shock	-40° C ~ +80° C 60 min/cycle/10 times	Tested at ambient temperature after cycle
Chemical Resistance	Acetone, methylene chloride, methyl ethyl ketone, isopropyl alcohol, mineral spirits, unleaded gasoline, diesel fuel, antifreeze, vinegar, coffee, tea, cooking oil, most commercial cleaners including laundry detergent, and ammonia based glass cleaners	10 minutes at room temperature

Optical Characteristics

	Specification	Remarks
Light Transmission	>80%	Anti-Glare
Haze	<10%	Anti-Glare

Linearity Characteristics

	Specification	Remarks
Direction X	<1.5%	Linearity is the value of the max. error voltage
Direction Y	<1.5%	Linearity is the value of the max. error voltage

Durability

	Specification	Remarks
Activations	10 Million	
Activation Force	≤82g Stylus	
Top Film Hardness	3H	ASTM D3363
Tail Bond Strength	>13 lbs	90° Tail Pull

Electrical Specifications

	Specification	Remarks
Operating Voltage	5.5V or Less	
Insulation Resistance	≥ 10 MΩ at 25 V(DC)	
Electrostatic Protection	Withstands 15KV air discharge	EN 61000-4-2

Warranty

1-year limited warranty

Mechanical Drawing

**See attached drawing