





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AI	—	E1		text for packaging corrected	ECR-08-001868	23.01.08	SR ST
		E2		REVISED PER ECO-11-002591		17FEB11	HMR MM




Contact arrangement view from termination side


Printing 1-24 Thermo




Printing 1-24 Screw



Printing 25-48 Screw




Printing 12+6+6 Screw/Thermo




Contact arrangement view from termination side


Printing 1-24




Printing 25-48



Panel cut-out for contact insert when used without housing



assembly directions





× distance for a safe
contact max: max: 21 mm

NOTES:

- SUITABLE CRIMP CONTACTS: SERIES HE/HA
OUTER DIMENSIONS OF INSULATION: MAX. Ø3,2 MM
- SUITABLE HOOD SIZE 8; 12: SERIES HB; HD; HIP; EMV
SUITABLE INSERTION AND EXTRACTION TOOL:
SCREWDRIVER 0,5x3 DIN 5264
- Strip lenght: Screw conection 10mm
Spring clamp conection 10mm Crimp conection 7.5mm
- STANDARDS:
DIN EN 61984; DIN EN 60664-1

- 5 PACKAGING:
5 SETS IN A CARTON, PRE-MOUNTED
- 6 SPECIAL PACKAGING: Krauss-Maffei
PACKAGING UNIT: 220 PIECES

	1									Socket contact		light grey	5	earth wire contact with drillings Ø3,3 / without fixing screws					
		1					1	1		Deckel Federklemmversion		light grey	4						
									1	Crimp Crimp version		light grey	3						
1				1	1	1				Cover screw version		light grey	2						
1		1		1	1	1	1	1	1	Buchseneinsatz		light grey	1						
0-10-29-31-89-49-57-97-12-92-31-91-71-1										DESCRIPTION / BENENNUNG	MATERIAL	COLOR / FARBE	ITEM NO. POS.						
HE.24.Bu.S. B1-24 KM										THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm  MATERIAL — TOLERANCES UNLESS OTHERWISE SPECIFIED: GENERAL TOLERANCES n. ISO 8015 n. ISO 2768 - mH - E n. DIN 16901 - 140  FINISH —	DWN 08.02.2000 Schneider	 Tyco Electronics Corporation Harrisburg, Pa 17105-3608							
HE.24.Bu.C-3.3 B1-24											CHK 08.02.2000 Schweiger					NAME Female insert HE.24.BU.S/C			
HE.24.Bu.SC-AU B1-24											APVD —					PRODUCT SPEC —			
HE.24.Bu.S-T B 12+6+6											APPLICATION SPEC —				SIZE A2		CAGE CODE 00779	DRAWING NO C=1103641	RESTRICTED TO —
HE.24.Bu.S-AU B25-48											WEIGHT —								
HE.24.Bu.S-AUB1-24											CUSTOMER DRAWING				SCALE 1:1		SHEET 1 OF 1	REV E2	
HE.24.Bu.SC.B.25-48																			
HE.24.Bu.SC.B1-24																			
HE.24.Bu.C.B.25-48																			
HE.24.Bu.C.B1-24																			
HE.24.Bu.S.B.25-48																			
HE.24.Bu.S-T																			
HE.24.Bu.S B1-24																			
ORDERING TEXT / BESTELLTEXT																			