

Product Description

Glass fibre-reinforced for maximum mechanical stability; Supporting surface for spanner means scratches on the housing are avoided



Application range

- For locking SKINTOP® cable glands in boreholes without thread.

Benefits

- Glass fibre-reinforced for maximum mechanical stability
- Supporting surface for spanner means scratches on the housing are avoided

Design

- PG connection thread

Approvals

- UL File Nr. E79903

Note

- UL approval only when used with the UL-approved SKINTOP® polyamide cable glands
- Designed for use with SKINTOP® ST(R)

Technical Data

Upon request

Available without collar (without surface for assembling tool)

Colour delivered

Silver grey (RAL 7001) Light grey (RAL 7035) Black (RAL 9005), UV-resistant

Material

Polyamide, glass fibre-reinforced

Temperature range

-20°C to +100°C

Article List

Part number	Article designation / size	SW (mm)	Pieces / PU
SKINTOP® GMP-GL silver grey with collar			
53019000	GMP-GL 7	19	100
53019010	GMP-GL 9	22	100
53019020	GMP-GL 11	24	100
53019030	GMP-GL 13,5	27	100
53019040	GMP-GL 16	30	100
53019050	GMP-GL 21	36	50
53019060	GMP-GL 29	46	50
53019070	GMP-GL 36	60	25
53019080	GMP-GL 42	65	25
53019090	GMP-GL 48	70	25
SKINTOP® GMP-GL black with collar			
53019200	GMP-GL 7	19	100
53019210	GMP-GL 9	22	100
53019220	GMP-GL 11	24	100
53019230	GMP-GL 13,5	27	100
53019240	GMP-GL 16	30	100
53019250	GMP-GL 21	36	50
53019260	GMP-GL 29	46	50
53019270	GMP-GL 36	60	25
53019280	GMP-GL 42	65	25
53019290	GMP-GL 48	70	25
SKINTOP® GMP-GL light grey with collar			
53019001	GMP-GL 7	19	100
53019011	GMP-GL 9	22	100

53019021	GMP-GL 11	24	100
53019031	GMP-GL 13,5	27	100
53019041	GMP-GL 16	30	100
53019051	GMP-GL 21	36	50
53019061	GMP-GL 29	46	50
53019071	GMP-GL 36	60	25
53019081	GMP-GL 42	65	25
53019091	GMP-GL 48	70	25

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.