



PART NUMBER		TAB SIZE	WIRE RANGE AWG (mm ²)	DIMENSIONS in		
PREFIX	PKG			A $\pm .03$ (0.8)	B $\pm .01$ (0.3)	C $\pm .01$ (0.3)
D18-188B	-C -M	.187 × .020 (4.8 × 0.5)	22-18 (.5-1.0)	.56 (14.2)	.23 (5.8)	.10 (2.5)
D14-188B	-C -M	.187 × .020 (4.8 × 0.5)	16-14 (1.5-2.5)	.56 (14.2)	.23 (5.8)	.10 (2.5)



NOTES:

- USED FOR:
A. STRANDED COPPER WIRE ONLY
B. 302°F (150°C) MAX TEMP RATING
- PACKAGE QTY:
A. STD: C=100
B. BULK: M=1000
- MATERIAL:
A. STAMPING: .016 (0.41) THK BRASS, TIN PLATED
- WIRE STRIP LENGTH $9/32 \begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix}$ (7.1 $\begin{smallmatrix} +0.8 \\ -0 \end{smallmatrix}$)
- FIRST INSERTION FORCE: 12 LB (53N) MAX
FIRST WITHDRAWAL FORCE: 12 LB (53N) MAX
6 LB (27N) MIN
- INSTALLATION TOOLS:
A. CT-100 (POCKET B)
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS OR mm²



CERTIFIED
LR31212

A41303_06

06	7/03	KLFU		ADDED INTERNAL SERRATIONS WIRE RANGE .5 WAS .38						 PANDUIT CORP.				TINLEY PARK, ILLINOIS	
05	1/01	RM	SKB	FILESPEC WAS N41303AA_PCD_04	8933		JAC	CCH							
04	4/95	MS		REMOVED SLOT FROM TERMINAL	03131										
03	10/94	TH	RS	UPDATED NOTES AND DIMENSIONS	02549		LA	TFK							
REV	DATE	BY	CHK	DESCRIPTION	ECN #	QA	CUST	PM	APP	DRAWN BY	CHK'D	SCALE	DRAWING NO.		
										DAW		NONE	A41303		

NON-INSULATED FEMALE DISCONNECT,
BUTTED SEAM (.188 SERIES)