

Hacksaw Blades



ECLIPSE*Plus* 30

Bi-Metal

Plus 30

Cuts 30% more effectively than a conventional blade. Benefits include a sharper first cut, faster cut and longer blade life

Size (mm)	(in)	Teeth Per(in)	Order Code	Price Each
250 x 13 x 0.65	10 x ½ x 0.025	18	137-3895	
250 x 13 x 0.65	10 x ½ x 0.025	24	137-3896	
250 x 13 x 0.65	10 x ½ x 0.025	32	137-3897	
300 x 13 x 0.65	12 x ½ x 0.025	18	137-3898	
300 x 13 x 0.65	12 x ½ x 0.025	24	137-3899	
300 x 13 x 0.65	12 x ½ x 0.025	32	137-3901	

Hi-Cut

HSS cutting edge, electron beam welded to a tough spring back. More shatter-resistant than other types of blade.

Size (mm)	(in)	Teeth Per(in)	Order Code	Price Each
300 x 25 x 1.25	12 x 1 x 0.050	10	137-3914	
300 x 25 x 1.25	12 x 1 x 0.050	14	137-3915	
300 x 25 x 1.25	14 x 1 x 0.050	10	137-3916	
300 x 25 x 1.25	14 x 1 x 0.050	14	137-3917	
350 x 32 x 1.6	14 x 1¼ x 0.062	6	137-3918	
350 x 32 x 1.6	14 x 1¼ x 0.062	10	137-3919	
400 x 32 x 1.6	16 x 1¼ x 0.062	6	137-3920	
400 x 32 x 1.6	16 x 1¼ x 0.062	10	137-3921	
400 x 40 x 2.0	16 x 1½ x 0.075	6	137-3922	
450 x 32 x 1.6	18 x 1¼ x 0.062	6	137-3923	
450 x 32 x 1.6	18 x 1¼ x 0.062	10	137-3925	
450 x 40 x 2.0	18 x ½ x 0.075	6	137-3926	
525 x 40 x 2.0	21 x 1½ x 0.075	6	137-3927	
525 x 45 x 2.5	21 x 1¾ x 0.088	6	137-3928	

Flexible Silicon Steel

Designed primarily for the occasional user. Will cut most types of softer materials.

Size (mm)	(in)	Teeth Per(in)	Order Code	Price Each
250 x 13 x 0.65	10 x ½ x 0.025	18	137-3902	
250 x 13 x 0.65	10 x ½ x 0.025	24	137-3903	
300 x 13 x 0.65	12 x ½ x 0.025	14	137-3904	
300 x 13 x 0.65	12 x ½ x 0.025	18	137-3905	
300 x 13 x 0.65	12 x ½ x 0.025	24	137-3906	
300 x 13 x 0.65	12 x ½ x 0.025	32	137-3907	

All Hard

Plus 30

Cuts 30% more effectively than a conventional blade. Benefits include a sharper first cut, faster cut and longer blade life.

Size (mm)	(in)	Teeth Per(in)	Order Code	Price Each
250 x 13 x 0.65	10 x ½ x 0.025	18	137-3887	
250 x 13 x 0.65	10 x ½ x 0.025	24	137-3888	
300 x 13 x 0.65	12 x ½ x 0.025	14	137-3889	
300 x 13 x 0.65	12 x ½ x 0.025	18	137-3890	
300 x 13 x 0.65	12 x ½ x 0.025	24	137-3892	
300 x 13 x 0.65	12 x ½ x 0.025	32	137-3893	

High speed steel. with strong rigid back to assist in accurate cutting.

493775

Size (mm)	(in)	Teeth Per(in)	Order Code	Price Each
300 x 16 x 0.8	12 x ⅝ x 0.032	14	137-3856	
300 x 16 x 0.8	12 x ⅝ x 0.032	18	137-3858	
300 x 16 x 0.8	12 x ⅝ x 0.032	24	137-3859	
300 x 25 x 1.25	12 x 1 x 0.050	10	137-3860	
300 x 25 x 1.25	12 x 1 x 0.050	14	137-3861	
350 x 25 x 1.25	14 x 1 x 0.050	10	137-3862	
350 x 25 x 1.25	14 x 1 x 0.050	14	137-3864	
350 x 32 x 1.6	14 x 1¼ x 0.062	6	137-3865	
350 x 32 x 1.6	14 x 1¼ x 0.062	10	137-3866	
350 x 40 x 2.0	14 x 1½0.075	6	137-3867	
400 x 32 x 1.6	16 x 1¼ x 0.062	6	137-3868	
400 x 40 x 2.0	16 x 1¼ x 0.062	10	137-3871	
400 x 40 x 2.0	16 x 1½ x 0.075	4	137-3872	
425 x 25 x 1.25	16 x 1½ x 0.075	6	137-3873	
425 x 25 x 1.25	17 x 1 x 0.050	10	137-3874	
425 x 32 x 1.6	17 x 1 x 0.050	14	137-3875	
425 x 32 x 1.6	17 x 1¼ x 0.062	6	137-3876	
450 x 32 x 1.6	17 x 1¼ x 0.062	10	137-3877	
450 x 32 x 1.6	18 x 1¼ x 0.062	6	137-3878	
450 x 40 x 2.0	18 x 1¼ x 0.062	10	137-3879	
525 x 40 x 2.0	18 x 1½ x 0.075	6	137-3880	
525 x 45 x 2.25	21 x 1½ x 0.075	6	137-3881	
600 x 50 x 2.5	21 x 1¾ x 0.088	6	137-3883	
600 x 50 x 2.5	24 x 1¾ x 0.088	6	137-3884	
600 x 50 x 2.5	24 x 2 x 0.100	4	137-3885	
600 x 50 x 2.5	24 x 2 x 0.100	6	137-3886	