



8501NR51



8501NR61



8501NR52



8501NR62



8501NR82



8501NR45



8501NR41



8501NR42



8501NH7



8501NR43



8501NR34

How to Order:

To Order Specify:	Catalog Number	
• Class Number	Class	Type
• Type Number	8501	NR51B

8501 NR sockets are designed for use with plug-in 8501 K and Type R relays, 8430 MPS phase failure relays and 9050 JCK timers. The 8501 NR45 screw terminal sockets have pressure wire clamps that accept 1 or 2 #16–22 wires. All other sockets have pressure clamps that will accept 1 or 2 #12–22 wires.

The recommended tightening torque for all terminals is 7-8 lb-in.

- All devices stocked in central warehouse
- DIN track mount or direct panel mount
- Tubular sockets available in easy-to-wire single tier or space-saving double tier versions

Snapmount Sockets

For Use With			Description	Socket Rating		Type	Price	Std. Qty.▲
Class 8501	Class 8430	Class 9050		UL	CSA			
KP12 KPD12	MPS (240 volts)	JCK11 – 19	8 Pin Tubular Single Tier Screw Terminal	600 V, 10 A	300 V, 10 A	NR51	\$8.20	1
		JCK31 – 39		300 V, 15 A		NR51B	6.80	10
		JCK60	8 Pin Tubular Double Tier Screw Terminal	600 V, 5 A	300 V, 10 A	NR52	8.20	1
		JCK1 F JCK3 F JCK5 F		300 V, 16 A		NR52B	6.80	10
KP13 KPD13	...	JCK21 – 29	11 Pin Tubular Single Tier Screw Terminal	600 V, 5 A	300 V, 10 A	NR61	12.30	1
		JCK41 – 49		300 V, 15 A		NR61B	11.00	10
		JCK70	11 Pin Tubular Double Tier Screw Terminal	600 V, 5 A	300 V, 10 A	NR62	12.30	1
		JCK2F JCK4F		300 V, 16 A		NR62B	11.00	10
KL KU	MPS (480 Volts)	...	11 Pin Spade Double Tier Screw Terminal	300 V, 15 A	300 V, 15 A	NR82	13.70	1
						NR82B	12.30	10
RS41 RSD41	...	...	5 Pin Spade Double Tier Screw Terminal	300 V, 15 A	300 V, 15 A	NR41	19.10	1
						NR41B	17.80	10
RS42 RSD42	...	...	8 Pin Spade Double Tier Screw Terminal	300 V, 10 A	300 V, 10 A	NR42	19.10	1
						NR42B	17.80	10
RS43 RSD43	...	...	11 Pin Spade Double Tier Screw Terminal	300 V, 10 A	300 V, 10 A	NR43	19.10	1
						NR43B	17.80	10
RS44 RSD44	...	...	14 Pin Spade Double Tier Screw Terminal	300 V, 10 A	300 V, 10 A	NR34	19.10	1
						NR34B	17.80	10
RS4 RSD4 RS14 RSD14 RS24 RSD24 RS34 RSD34	...	...	14 Pin Spade Double Tier Screw Terminal	300 V, 10 A	300 V, 10 A	NR45	19.10	1
						NR45B	17.80	10

▲ Must be ordered in multiples of the quantity listed. Units provided in standard quantity of one are individually packaged; devices with B suffix have a standard quantity of 10 per bulk pack.
■ Rated for use with Class 8430 Type MPS at 480 Volts. Rated 10 A at 300 volts by CSA.

Note: For DIN 3 mounting track and end clamps, see page 22-16 or refer to the NEMA type terminal block section 9080CT9601 or the IEC type terminal block section 9080CT9901R5/02.

Socket Accessories

Socket	For Use With	Description	Type	Price Each	Std. Pack♦
8501NR51	8501KP12, KPD12 8430MPSV24 9050JCK	Hold Down Clip	NH51	\$0.68	10
		Hold Down Spring	NH7	5.50	1
		Hold Down Spring	NH7	5.50	1
8501NR52	8501KP12, KPD12 8430MPSV24 9050JCK	Hold Down Clip	NH52	0.68	10
		Hold Down Spring	NH7	5.50	1
		Hold Down Spring	NH7	5.50	1
8501NR61	8501KP13, KPD13 9050JCK	Hold Down Clip	NH61	0.68	10
		Hold Down Spring	NH7	5.50	1
8501NR62	8501KP13, KPD13 9050JCK	Hold Down Clip	NH52	0.68	10
		Hold Down Spring	NH7	5.50	1
8501NR82	8501KU and KL 8430MPSV29	Hold Down Clip	NH82	0.68	10
		Hold Down Spring	NH7	5.50	1
8501NR41	8501RS41, RSD41	Hold Down Clip	Supplied with socket as standard	...	...
8501NR42	8501RS42, RSD42	Hold Down Clip	8501NH42	0.68	10
8501NR43	8501RS43, RSD43	Hold Down Clip	8501NH42	0.68	10
8501NR34	8501RS44, RSD44	Hold Down Clip	8501NH42	0.68	10
8501NR45	8501RS4, RSD4 8501RS14, RSD14 8501RS24, RSD24 8501RS34, RSD34	Hold Down Clip	8501NH45	0.68	10

♦ Must be ordered in multiples of the quantity listed.

UL/CSA:



File
CCN

E66924
SW1V2



File
Class

211268
3211 07



For additional information, reference Catalog #8501CT0301.