


ZETTLER MAGNETICS CO., LTD.

EI41-5.0VA TRANSFORMER AHI SERIES

FEATURES,

- Conform to IEC EN61558-1 Safety Standards
- UL 5085 Approved Class 2&3:UL File No.E214561
(for 2.5VA and 10VA only)
- Dielectric Strength 4200Vrms
- Optional 115/230V input at 50/60Hz
- Material Meet UL 94V-O Flammability Requirement
- Splited Bobbin Wall Slots Eliminates,all Wire Crossovers
- 3 Standard Sizes for a Variety of Power Application

OUTLINE DIMENSIONS



ELECTRONIC SPECIFICATIONS

Part NO	Input Voltage (V)	Series		Parallel		Rated Power (VA)	Certificate	
		Voltage (Vac)	Current (mA)	Voltage (Vac)	Current (mA)		UL	CE
AHI05010	115V/230V	10	500	5	1000	5.0VA	●	
AHI05012	115V/230V	12.6	400	6.3	800	5.0VA	●	
AHI05016	115V/230V	16	310	8	620	5.0VA	●	
AHI05020	115V/230V	20	250	10	500	5.0VA	●	
AHI05024	115V/230V	24	210	12	420	5.0VA	●	
AHI05028	115V/230V	28	180	14	360	5.0VA	●	
AHI05036	115V/230V	36	140	18	280	5.0VA	●	