

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200070473

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

Micro-Change (M12) Double-Ended Cordset, 4 Poles, Female (Straight) to Male (Straight), 0.34mm² PVC Cable, 1.0m (3.28') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E152210

General

Product Family

Series

Connector End A

Connector End B

IP Rating

Material - Contact

Overview

Product Name

Protocol

Region

Type

UPC

Industrial Cordsets

120007

Micro-Change (M12)

Micro-Change (M12)

IP67

Copper Alloy

Brad Micro-Change (M12) Connectors

Micro-Change (M12)

N/A

Europe

Double Ended

883906073541

Physical

Cable Diameter

Cable Length

Color - Cable Jacket

Coupling Style

Gender

Keyway

LED Indicator

Material - Cable Jacket

Material - Connector Body

Material - Coupling Nut

Material - O-Ring

Material - Plating Mating

Net Weight

Orientation

Poles

Temperature Range - Operating

Wire Size AWG

Wire/Cable Type

5.40mm (.213")

1.0m (3.28')

Black

Threaded

Female-Male

Single

No

PVC

PUR

Nickel-plated Brass

Fluoro-elastomer

Gold

78.597/g

Straight to Straight

4

-30°C TO +80°C

N/A

UL 2464

Electrical

Current - Maximum per Contact

Voltage - Maximum

4.0A

250V AC/DC

Material Info

Engineering Number

884030E03M010

Reference - Drawing Numbers

Sales Drawing

1200668084-000

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120007 Series

This document was generated on 01/21/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION