


FP-CA-AU 630VDC Audio Capacitors Polypropylene Metallised



CAPACITANCE μF	D	L
1.0 – 2.2	25mm	50mm
2.2+ - 4.7	30mm	50mm
4.,7+ - 6.8	30mm	70mm
6.8+ -12.0	35mm	70mm
12.0+ - 16.0	40mm	70mm
16.0+ - 20.0	45mm	70mm
20.0+ -30.0	45mm	100mm

AMPOHM Audio Capacitors are specially designed for high performance audio systems, used in various applications. The capacitors are hand wound and have their insulated tinned copper leads hand soldered before being assembled in a flame retardant plastic case and resin sealed. All are individually hand tested, hermetically sealed and as a polypropylene metallised capacitor self healing. This construction results in the capacitors having low ESR and low inductance and possessing high stability with respect to both temperature and frequency.

Custom designs available.

Type: FP-CA-AU
Capacitance: 1.0 μF – 30.0 μF
Dissipation Factor: < 0.001@ 1KHz
Tolerance: +/- 5%
Rated Voltage: 630V DC
Temperature Range: -40 to +85C
Outer Foil: Line on label denotes outer foil

Marking:

AMPOHM
 AUDIO CAPACITOR
 TYPE
 VALUE/VOLTAGE
 SPEC
 DATE CODE

Line on label denotes outer foil

Witness Innovation... Experience Technology



Registered Office: Ampohm Wound Products Ltd, Unit 1d Treburley Industrial Estate, Treburley, Launceston, Cornwall, PL15 9PU
 Tel: 01423 865641 • Fax: 01423 798246 • E-mail: sales@ampohm.co.uk • Website: www.ampohm.co.uk

Witness Innovation... Experience Technology

Registered Office: Ampohm Wound Products Ltd, Unit 1d Treburley Industrial Estate, Treburley, Launceston, Cornwall, PL15 9PU
Tel: 01423 865641 ▪ Fax: 01423 798246 ▪ E-mail: sales@ampohm.co.uk ▪ Website: www.ampohm.co.uk



Registered in England & Wales No: 5654904

VAT Registration: 874 7628 73