





This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

PRODUCT NUMBER
85854-XXX OR 85854-YYYY
85854-XXYLF OR 85854-XXYYLF



mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date		0.X ± 0.3	COPY		www.fciconnect.com	
DE	V06-0492	DCH	2006-05-23	linear	0.XX ± 0.13	projection		title METRAL SIGNAL HEADER	
DF	DG07-0487	Cenh	12/05/07		.XXX ± .051			4 MOD, 5 ROW PRESS-FIT	
DG	DG09-0344	TER	2009-11-10	angles	0° ± 2°			product family METRAL	
-	-	-	-	dr	T.BRUNGARD 11/19/99	MIM		code 213	
DB	V04-0353	DAI	05/04/04	enrg	M.STRAWSE 11/19/99			size	
DC	V04-0560	HTB	06/01/04	chr	M.STRAWSE 11/19/99	scale		dwg no 85854	
DD	V04-1100	DAI	01/26/05	appd	M.STRAWSE 02/29/00	2:1	A	sheet 1 of 20	
sheet	revision	DG	...	DG					
index	sheet	I	...	20					




This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

A

B



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE
SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

1 | 2

3 |

4

KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.30
2	5.75	4.30
3	6.50	4.30
4	7.25	4.30
5	5.00	13.60
6	5.75	13.60
7	6.50	13.60
8	7.25	13.60
9	5.00	17.00
10	5.75	17.00
11	6.50	17.00
16	7.00	4.30
19	8.00	4.30
20	8.00	13.60
21	8.00	17.00
25	5.75	15.60
39	8.00	14.40
44	5.75	12.10
49	5.75	15.10
52	8.00	15.10
54	5.00	11.50

A

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER				www.fciconnect.com	
ltr	ecn no.	dr	date	linear	0.X ±0.3		projection 	title METRAL SIGNAL HEADER 4 MOD, 5 ROW PRESS-FIT	product family		METRAL		code
DG					0.XX ±0.13				MM 	size	dwg no	85854	213
					.XXX ±.051								
				angles	0° ±2°		scale 1 : 1						
				dr	T.BRUNGARD	11/19/99							
				enrg	M.STRAWSER	11/19/99							
				chr	M.STRAWSER	11/19/99						sheet	
				appd	M.STRAWSER	02/29/00						2	
sheet	revision												
index	sheet												

B

1 | 2

Pro/E

3 |

cage code 22526

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

A


B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X01 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X02 SEE NOTE 10 LEAD FREE OPTION	E	19	3	19	19	3	19	3	3	19	3	3	19	3	3	19	3	3	19	3	3	19	3	3	19
	D	3	19	19	19	19	3	3	19	3	3	19	3	3	19	3	3	19	3	3	19	3	3	19	3
	C	19	3	19	19	19	3	3	19	3	3	19	3	3	19	3	3	19	3	3	19	3	3	19	3
	B	3	19	19	19	19	3	3	19	3	3	19	3	3	19	3	3	19	3	3	19	3	3	19	3
	A	19	19	19	19	19	3	3	19	3	3	19	3	3	19	3	3	19	3	3	19	3	3	19	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X03 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	-	-	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	-	-	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	19	19	2	2	2	2	2	-	-	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	-	-	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	-	-	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X04 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	D	1	1	1	19	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	19	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com			
litr	ecn no.	dr	date	linear	0. X ±0.3		COPY			title			
DG					0. XX ±0.13		projection			METRAL SIGNAL HEADER			
					. XXX ±.051					4 MOD, 5 ROW PRESS-FIT			
				angles	0° ±2°					product family		METRAL	code
				dr	T.BRUNGARD	11/19/99				size	dwg no	213	
				engr	M.STRAWER	11/19/99						sheet	
				chr	M.STRAWER	11/19/99	scale		A	85854		3	
				appd	M.STRAWER	02/29/00	1:1						
sheet index	revision sheet												

Pro/E

3

cage code 22526

4

A

B



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X09 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	4	4	19	19
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X10 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4
	B	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X11 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8
	B	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X12 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	1	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	1	
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
85854-X13 SEE NOTE 10 LEAD FREE OPTION	E	3	2	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	2	3
	D	3	2	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	2	3
	C	3	2	1	1	1	1	3	1	1	1	1	3	1	1	1	1	1	1	1	1	1	2	3
	B	3	2	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	2	3
	A	3	2	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	2	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X14 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	1	2	
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X15 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	1	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X16 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	8	8	20	20	
	B	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	0.X ±0.3	projection 	COPY	www.fciconnect.com	
DG					0.XX ±0.13				
					.XXX ±.051				
					angles 0° ±2°				
				dr	T.BRUNGARD 11/19/99		scale 1:1	product family	
				enrg	M.STRAWSE 11/19/99			METRAL	
				chr	M.STRAWSE 11/19/99			size	dwg no
				appd	M.STRAWSE 02/29/00			A	85854
sheet index	revision sheet								code
									213
									sheet 4

Pro/E

3

cage code 22526

4

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	
85854-X17 SEE NOTE 10 LEAD FREE OPTION	E	3																							3	
	D																								3	
	C																								3	
	B																								3	
	A	3																					2		3	

[illegible]

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22
85854-X19 SEE NOTE 10 LEAD FREE OPTION	E	-	-	-	-	-	2	2	2	2	2	2	52	52	52	52	52	52	19	19	19	19	19
	D	-	-	-	-	-	2	2	2	2	2	2	52	52	52	52	52	52	19	19	19	19	19
	C	-	-	-	-	-	2	2	2	2	2	2	52	52	52	52	52	52	19	19	19	19	19
	B	-	-	-	-	-	2	2	2	2	2	2	52	52	52	52	52	52	19	19	19	19	19
	A	-	-	-	-	-	2	2	2	2	2	2	52	52	52	52	52	52	19	19	19	19	19



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

[illegible]

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0. X $\pm$ 0.3		COPY			title	
DG					0. XX $\pm$ 0.13		projection			METRAL SIGNAL HEADER	
					.XXX $\pm$.051					4 MOD, 5 ROW PRESS-FIT	
				angles	0° $\pm$ 2°				product family		
				dr	T.BRUNGARD	11/19/99	MM		METRAL		code
				engr	M. STRAWSER	11/19/99			size		213
				chr	M. STRAWSER	11/19/99	scale		dwg no		sheet
				appd	M. STRAWSER	02/29/00	1:1		A		5
sheet index		revision sheet									

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X21 SEE NOTE 10 LEAD FREE OPTION	E	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44
	D	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44
	C	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44
	B	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44
	A	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44	44

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X22 SEE NOTE 10 LEAD FREE OPTION	E	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	19	19	19	19	19	19
	D	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	19	19	19	19	19	19
	C	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	19	19	19	19	19	19
	B	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	19	19	19	19	19	19
	A	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	52	19	19	19	19	19	19

[illegible][illegible]



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X25 SEE NOTE 10 LEAD FREE OPTION	E	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6
	D	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	C	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	A	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X26 SEE NOTE 10 LEAD FREE OPTION	E	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2
	D	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	2	2	2
	C	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	2	2	2	2
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	2	2	2
	A	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X27 SEE NOTE 10 LEAD FREE OPTION	E	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6
	D	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	6	6	6	6	6
	C	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	6	6	6	6
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	6	6	6	6	6
	A	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4																
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24								
85854-X28 SEE NOTE 10 LEAD FREE OPTION	E	9	1	1	1	0	1	0	1	0	1	0	1	0	9	1	1	1	0	1	0	1	0	1	0	1	1	1	1	9			
	D	9	1	1	1	0	1	0	1	0	1	0	1	0	9	1	1	1	0	1	0	1	0	1	0	1	0	1	1	1	9		
	C	9	1	1	1	0	1	0	1	0	1	0	1	0	9	1	1	1	0	1	0	1	0	1	0	1	0	1	0	1	1	9	
	B	9	1	1	1	0	1	0	1	0	1	0	1	0	1	0	9	1	1	1	0	1	0	1	0	1	0	1	0	1	1	1	9
	A	1	3	2	2	2	2	2	2	2	2	2	2	2	1	3	2	2	2	2	2	2	2	2	2	2	3	3	3	3	1		

3																									
METRAL P/N		CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
ROW		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X29 SEE NOTE 10 LEAD FREE OPTION		E	5	7	6	6	6	6	6	6	6	6	6	5	7	6	6	6	6	6	6	6	7	7	5
		D	5	7	6	6	6	6	6	6	6	6	6	5	7	6	6	6	6	6	6	6	7	7	5
		C	5	7	6	6	6	6	6	6	6	6	6	5	7	6	6	6	6	6	6	6	7	7	5
		B	5	7	6	6	6	6	6	6	6	6	6	5	7	6	6	6	6	6	6	6	7	7	5
		A	5	7	6	6	6	6	6	6	6	6	6	5	7	6	6	6	6	6	6	6	7	7	5

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X30 SEE NOTE 10 LEAD FREE OPTION	E	1	3	2	2	2	2	2	2	2	2	2	1	3	2	2	2	2	2	2	2	3	3		
	D	1	3	2	2	2	2	2	2	2	2	2	1	3	2	2	2	2	2	2	2	3	3		
	C	1	3	2	2	2	2	2	2	2	2	2	1	3	2	2	2	2	2	2	2	3	3		
	B	1	3	2	2	2	2	2	2	2	2	2	1	3	2	2	2	2	2	2	2	3	3		
	A	1	3	2	2	2	2	2	2	2	2	2	1	3	2	2	2	2	2	2	2	3	3		

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X31 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-
	D	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	4	2	2	2	4
	C	2	-	4	-	2	-	2	-	2	-	2	-	2	-	4	-	2	-	2	-	2	-	4	-
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	4	4	4	4
	A	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	4	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X32 SEE NOTE 10 LEAD FREE OPTION	E	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-
	D	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1
	C	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-
	B	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1
	A	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	www.fciconnect.com	
DG					0.XX ±0.13			title	
					.XXX ±.051			METRAL SIGNAL HEADER	
					angles 0° ±2°			4 MOD, 5 ROW PRESS-FIT	
				dr	T.BRUNGARD 11/19/99	MIM	scale	product family	
				enrg	M.STRAWER 11/19/99			METRAL	
				chr	M.STRAWER 11/19/99			size	
				appd	M.STRAWER 02/29/00			dwg no	
sheet index		revision sheet						85854	
								code	
								213	
								sheet	
								6	

cage code 22526

Pro/E

3

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

A

B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X33 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	3	3	3	3	3	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3	2	2
	C	3	3	3	3	3	3	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3	3	2
	B	2	2	2	3	3	3	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3	3	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X34 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	19	3	3	3	3	3	3	3	3	19	3	3	3	3	3	4
	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4
	C	3	3	3	3	3	3	3	3	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4
	B	3	19	3	3	19	3	3	3	19	3	19	3	19	3	3	3	3	3	3	3	3	3	3	4
	A	3	3	3	3	3	3	3	3	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X35 SEE NOTE 10 LEAD FREE OPTION	E	4	4	3	3	3	3	3	3	3	3	19	19	3	3	3	3	3	3	3	3	3	3	19	19
	D	4	4	3	3	3	3	3	3	3	3	19	19	3	3	3	3	3	3	3	3	3	3	19	19
	C	4	4	3	3	3	3	3	3	3	3	19	19	3	3	3	3	3	3	3	3	3	3	19	19
	B	4	4	3	3	3	3	3	3	3	3	19	19	3	3	3	3	3	3	3	3	3	3	19	19
	A	4	4	3	3	3	3	3	3	3	3	19	19	3	3	3	3	3	3	3	3	3	3	19	19
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X36 SEE NOTE 10 LEAD FREE OPTION	E	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	39	54	54	54
	D	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	39	54	54	54
	C	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	39	54	54	54
	B	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	39	54	54	54
	A	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	54	39	54	54	54

mat'l code				--		tolerances unless otherwise specified		CUSTOMER				www.fciconnect.com		
litr	ecn no.	dr	date	linear	0. X ±0.3		COPY			title METRAL SIGNAL HEADER 4 MOD, 5 ROW PRESS-FIT				
DG					0. XX ±0.13		projection							
					.XXX ±.051									
				angles	0° ±2°									
				dr	T.BRUNGARD 11/19/99				product family		METRAL		code	
				engr	M. STRAWSER 11/19/99				size		dwg no		213	
				chr	M. STRAWSER 11/19/99				scale		A		sheet	
				appd	M. STRAWSER 02/29/00		1:1				85854		7	
sheet index		revision sheet												



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

A

B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X41 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	C	2	2	2	2	1	1	2	2	2	2	1	1	2	2	2	2	1	1	2	2	2	2	1	1
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X42 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3
	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X43 SEE NOTE 10 LEAD FREE OPTION	E	-	5	5	-	5	5	-	5	5	-	5	5	-	5	5	-	5	5	-	5	5	-	5	5
	D	-	5	5	-	5	5	-	5	5	-	5	5	-	5	5	-	5	5	-	5	5	-	5	5
	C	-	-	-	-	5	5	-	5	5	-	5	5	-	-	-	-	5	5	-	5	5	-	5	5
	B	-	-	-	-	5	5	-	5	5	-	5	5	-	-	-	-	5	5	-	5	5	-	5	5
	A	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X44 SEE NOTE 10 LEAD FREE OPTION	E	8	20	8	20	8	20	8	20	20	7	7	20	20	20	20	7	20	7	20	20	20	20	20	20
	D	8	20	8	20	8	20	8	20	20	7	7	20	20	20	20	7	20	7	20	20	20	20	20	20
	C	20	20	20	20	20	20	8	20	20	7	7	20	20	20	20	20	7	20	7	20	20	20	20	20
	B	7	20	7	20	7	20	7	20	7	7	20	20	20	7	20	20	20	20	20	20	20	20	20	20
	A	20	7	7	7	7	7	7	7	7	7	20	20	20	20	20	20	20	7	20	7	20	7	7	20

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	title	www.fciconnect.com
DG					0.XX ±0.13				
				angles	.XXX ±.051		product family	METRAL	code
					0° ±2°				
				dr	T.BRUNGARD 11/19/99	scale	size	dwg no	sheet
				engr	M.STRAWSE 11/19/99				
				chr	M.STRAWSE 11/19/99	1:1	A	85854	8
				appd	M.STRAWSE 02/29/00				
sheet index	revision sheet								

Pro/E

3

cage code 22526

4

A

B



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

A

B

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X49 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3
	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	3
METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X50 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	D	3	1	1	1	1	1	1	1	1	1	1	1	3	1	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	B	3	1	1	1	1	1	1	1	1	1	1	1	3	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X51 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	4	4	4	4	4	4	4	4	4	4	4	1	1	1	1	1	1	1	4	4	4	4	4	4
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X52 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2	2	2
	D	1	1	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2	2	2
	C	1	1	2	2	2	2	1	1	2	2	2	2	1	2	2	2	2	2	1	1	2	2	2	2
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X53 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	C	1	1	2	2	2	2	1	1	2	2	2	2	1	1	2	2	2	2	1	1	2	2	2	2
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X54 SEE NOTE 10 LEAD FREE OPTION	E	-	1	1	-	-	-	-	-	-	-	-	-	-	1	1	-	-	-	-	-	-	-	1	1
	D	-	1	1	-	-	-	-	-	-	-	-	-	-	1	1	-	-	-	-	-	-	-	1	1
	C	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1	1
	B	-	-	-	-	1	1	-	1	1	-	1	1	-	-	-	-	1	1	-	1	1	-	1	1
	A	-	1	1	-	-	1	-	1	1	-	1	1	-	1	1	-	1	1	-	1	1	-	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X55 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	3	3	-	-	3	3	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	3	3	-	-	3	3	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	3	3	-	-	3	3	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	3	3	-	-	3	3	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	19	19	-	-	19	19	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X56 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3

A

B

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
litr				ecr no.		COPY		www.fciconnect.com	
date				linear		projection		title	
DG								METRAL SIGNAL HEADER	
								4 MOD, 5 ROW PRESS-FIT	
				angles		scale		product family	
				dr		1:1		METRAL	
				enrg				code	
				chr				size	
				appd				dwg no	
								85854	
sheet index				revision sheet				sheet	
								9	

Pro/E

3

cage code 22526

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X57 SEE NOTE 10 LEAD FREE OPTION	E	-	1	1	-	-	-	-	-	-	-	-	-	1	1	-	-	-	-	-	1	1	-	1	1
	D	-	1	1	-	-	-	-	-	-	-	-	-	1	1	-	-	-	-	-	-	-	-	1	1
	C	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	1
	B	-	-	-	1	1	-	1	1	-	1	1	-	-	-	1	1	-	1	1	-	1	1	1	1
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	-	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X58 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1
	D	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	-	-	-	-
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	-	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X59 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1
	D	1	1	1	1	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	C	1	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1
	B	1	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1
	A	1	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X60 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	3	2	2	2	2	2	2	2	2	2	2	3	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	3	2	2	2	2	2	2	2	2	2	2	3	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
85854-X61 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	4	2	2	2	2	2	4	2	2	2	2	2	1	2	2	2	2	2	4	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X62 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	A	1	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X63 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	1	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	19	19	19	19	19	19	19	19	19	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	19	3	3	3	3	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X64 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	A	1	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
lfr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	www.fciconnect.com	
DG					0.XX ±0.13				
					.XXX ±.051				
				angles	0° ±2°	MIM	scale	product family	
				dr	T.BRUNGARD 11/19/99				
				engr	M.STRAWER 11/19/99				
				chr	M.STRAWER 11/19/99	1:1	A	size	
				appd	M.STRAWER 02/29/00				
sheet	revision							dwg no	
index	sheet								
								85854	
								213	
								10	
								cage code	
								22526	

Pro/E

3

cage code
22526

4</



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X73 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	4	2	2	2	1	2	2	2	2	2	2	2	4	2	2	2	2	2	2
	D	2	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2
	C	2	2	2	2	2	4	2	2	2	3	3	3	2	2	2	2	2	4	2	2	2	2	2	2
	B	2	2	2	2	2	4	2	2	2	3	2	2	2	2	2	2	2	4	2	2	2	2	2	2
	A	2	2	2	2	2	4	2	2	2	3	2	2	2	2	2	2	2	4	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X74 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	1	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X75 SEE NOTE 10 LEAD FREE OPTION	E	3	19	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	19
	D	3	19	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	19
	C	3	19	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	19
	B	3	19	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	19
	A	3	19	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X76 SEE NOTE 10 LEAD FREE OPTION	E	4	4	4	4	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
	D	1	4	4	4	4	4	3	3	3	3	3	3	3	3	3	3	3	3	3	4	4	4	1	3
	C	3	3	4	4	4	4	3	3	3	3	3	3	3	3	3	3	3	3	3	4	4	4	4	3
	B	3	3	3	4	4	4	3	3	3	3	3	3	3	3	3	3	3	3	3	4	4	4	4	3
	A	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4	3	4	4	3	3	3

3																									
METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X77 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	2	4	2	2	2
	D	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	4	2	2	2	2
	C	2	-	4	-	2	-	2	-	2	-	2	-	2	-	4	-	2	-	2	2	2	4	4	4
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	4	4	1	1
	A	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	2	4	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X78 SEE NOTE 10 LEAD FREE OPTION	E	1	1	2	1	1	1	1	2	1	1	1	1	1	2	1	1	1	1	1	2	1	1	1	2
	D	1	1	2	1	1	1	1	2	1	1	1	1	1	2	1	1	1	1	1	1	1	1	1	2
	C	1	1	2	1	1	1	1	2	1	1	1	1	1	2	1	1	1	1	1	1	1	1	1	2
	B	1	1	2	1	1	1	1	2	1	1	1	1	1	2	1	1	1	1	1	1	1	1	1	2
	A	1	1	2	1	1	1	1	2	1	1	1	1	1	2	1	1	1	1	1	1	1	1	1	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X79 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1	3
	D	2	1	1	1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	1	1	1	1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X80 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	2	2	1	1	1	1	1	1	1	1	1	2	2	1	1	1	1	1	1	1
	D	2	2	2	1	1	2	2	2	2	2	2	2	2	2	1	1	2	2	2	2	2	2	2	2
	C	1	1	1	3	2	2	2	2	2	2	2	2	2	2	1	1	2	2	2	2	2	2	2	2
	B	1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCI			
litr	ecn no.	dr	date	linear	0.X ±0.3				COPY	www.fciconnect.com			
DG					0.XX ±0.13				projection	title			
					.XXX ±.051					METRAL SIGNAL HEADER			
				angles	0° ±2°					4 MOD, 5 ROW PRESS-FIT			
				dr	T.BRUNGARD 11/19/99				MIM	product family		METRAL	
				engr	M.STRAWER 11/19/99					size		dwg no	
				chr	M.STRAWER 11/19/99				scale	A		85854	
				appd	M.STRAWER 02/29/00				1:1			sheet	
sheet index		revision sheet											

Pro/E

3

cage code 22526

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X81 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2
	D	2	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2
	C	2	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2
	B	2	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2
	A	2	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2	4	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X82 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	2	2	2	2	2
	D	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	2	2	2	2
	C	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	2	2	2	2	2
	B	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	2	2	2	2	2	2
	A	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X83 SEE NOTE 10 LEAD FREE OPTION	E	3	19	3	19	3	19	3	19	19	1	1	19	19	19	19	1	19	1	19	19	19	19	19	19
	D	4	19	3	19	3	19	3	19	19	1	1	19	19	4	19	1	19	1	19	19	1	19	1	19
	C	1	19	19	19	19	19	3	19	19	1	1	19	19	19	19	19	1	19	1	19	19	19	19	19
	B	4	19	4	19	1	19	1	19	1	1	19	19	19	1	19	19	19	19	19	19	19	19	19	19
	A	19	1	1	1	1	1	1	1	1	1	19	19	19	19	19	1	19	1	19	1	1	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X84 SEE NOTE 10 LEAD FREE OPTION	E	4	-	-	-	3	3	4	4	3	4	3	4	4	2	2	2	2	4	4	4	4	2	2	2
	D	4	-	-	-	3	3	4	4	3	4	3	4	4	4	4	4	2	2	4	2	2	4	2	2
	C	4	-	-	-	3	3	4	4	3	4	3	4	4	2	2	4	2	2	4	2	2	4	2	2
	B	4	-	-	-	3	3	4	4	3	4	3	4	4	2	2	4	4	2	4	2	2	4	2	2
	A	4	-	-	-	3	3	4	4	3	4	3	4	4	2	2	4	2	2	4	2	2	4	2	2

3																										
METRAL P/N		CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4									
		ROW	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X85 SEE NOTE 10 LEAD FREE OPTION		E	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-
		D	1	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1
		C	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-
		B	1	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1
		A	1	1	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-	1	-

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X86 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	4
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X87 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3	3	1	3	3	3	3	3	19	19	19	19	19	19	19
	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4	4	4	4	4	4	4
	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4	4	4	4	4	4	4
	B	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4	4	4	4	4	4	4
	A	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X88 SEE NOTE 10 LEAD FREE OPTION	E	5	5	5	5	5	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	D	5	5	5	5	5	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	5	5	5	5	5	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	5	5	5	5	5	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	5	5	5	5	5	5	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCI			
litr	ecn no.	dr	date	linear	0.X ±0.3				COPY	www.fciconnect.com			
DG					0.XX ±0.13				projection	title			
					.XXX ±.051					METRAL SIGNAL HEADER			
				angles	0° ±2°					4 MOD, 5 ROW PRESS-FIT			
				dr	T.BRUNGARD 11/19/99				MIM	product family			
				engr	M.STRAWSE 11/19/99					METRAL			
				chr	M.STRAWSE 11/19/99				scale	size			
				appd	M.STRAWSE 02/29/00				1:1	dwg no			
sheet index	revision sheet									85854			
										code			
										213			
										sheet			
										13			

Pro/E

3

cage code 22526

4



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

A

B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X89 SEE NOTE 10 LEAD FREE OPTION	E	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-
	D	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2
	C	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-
	B	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2
	A	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-	2	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X90 SEE NOTE 10 LEAD FREE OPTION	E	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	07	59	07	59	07	59	59
	D	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	07	59	07	59	07	59	59
	C	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	07	59	07	59	07	59	59
	B	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	07	59	07	59	07	59	59
	A	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	59	07	59	07	59	07	59	59

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X91 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	D	8	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	8	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	8	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X92 SEE NOTE 10 LEAD FREE OPTION	E	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7
	D	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7
	C	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7
	B	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7
	A	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7	20	7	7	7	7	7

mat'l code				tolerances unless otherwise specified				CUSTOMER		 www.fciconnect.com			
ltr	ecn no.	dr	date	linear	0.X ±0.3				COPY				
DG					0.XX ±0.13				projection				
					.XXX ±.051								
				angles	0° ±2°					product family METRAL			
				dr	T.BRUNGARD 11/19/99								
				engr	M.STRAWER 11/19/99								
				chr	M.STRAWER 11/19/99				scale	size A			
				appd	M.STRAWER 02/29/00								
sheet index		revision sheet								dwg no		213	
										85854		sheet 14	

Pro/E				3				cage code				22526				4			
-------	--	--	--	---	--	--	--	-----------	--	--	--	-------	--	--	--	---	--	--	--

1 | 2

Pro/E

3

cage code 22526

4

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X97 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	2	1	1	2	2	2	2	2	2	2	2	2	2	2	1	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
85854-X98 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	2	2	3	1	3	3	2	2	2	3	3	4	2	4	3	4	3	3	3
	D	3	3	3	3	2	2	3	1	3	3	2	2	2	3	3	4	2	4	3	4	3	3	3
	C	3	3	3	3	2	2	3	1	3	3	1	2	2	3	3	4	4	4	4	4	3	3	3
	B	3	3	3	3	2	2	3	1	3	3	2	2	2	3	3	4	2	4	3	4	3	3	3
	A	3	3	3	3	2	2	3	1	3	3	2	2	2	3	3	4	2	4	3	4	3	3	3

[illegible]

This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
85854-X100 SEE NOTE 10 LEAD FREE OPTION	E	3	3	7	7	8	7	8	7	8	7	8	7	8	7	8	7	8	7	8	7	8	7	8
	D	3	3	7	8	8	7	8	7	8	7	8	7	8	7	8	7	8	7	8	7	8	7	8
	C	3	3	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8	8
	B	3	3	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	3	3	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0. X $\pm$ 0.3		COPY			title	
DG					0. XX $\pm$ 0.13		projection			METRAL SIGNAL HEADER	
					.XXX $\pm$.051					4 MOD, 5 ROW PRESS-FIT	
				angles	0° $\pm$ 2°					product family	
				dr	T.BRUNGARD	11/19/99	scale			METRAL	
				engr	M. STRAWSER	11/19/99	size			dwg no	
				chr	M. STRAWSER	11/19/99	A		85854		213
				appd	M. STRAWSER	02/29/00					sheet 15
sheet index		revision sheet									

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
85854-X101 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	2	1	1	2	2	1	1	1	1	2	2	2	2	2	1
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	
85854-X102 SEE NOTE 10 LEAD FREE OPTION	E	1	1	1	1	1	1	1	1	1	1	1	1	1	2	1	1	1	1	1	2	1	1		
	D	1	1	1	1	1	1	1	1	1	1	1	1	1	2	1	1	1	1	1	2	1	1		
	C	1	1	1	1	1	1	1	1	1	1	1	1	1	2	1	1	1	1	1	2	1	1		
	B	1	1	1	1	1	1	1	1	1	1	1	1	1	2	1	1	1	1	1	2	1	1		
	A	1	1	1	1	1	1	1	1	1	1	1	1	1	2	1	1	1	1	1	2	1	1		

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4					
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23
85854-X103 SEE NOTE 10 LEAD FREE OPTION	E	5	5	6	5	5	5	5	6	5	5	5	5	6	5	6	5	5	5	5	6	5	6	6
	D	5	5	6	5	5	5	5	6	5	5	5	5	5	6	6	5	5	5	6	5	5	5	5
	C	5	5	6	5	5	5	5	6	6	6	6	6	6	6	6	6	6	5	5	6	5	6	6
	B	5	5	6	5	5	5	5	6	5	5	5	5	5	5	5	5	5	5	5	6	5	6	6
	A	5	5	6	5	5	5	5	6	5	5	5	5	5	5	5	5	5	5	5	6	5	6	6

[illegible]



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X105 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	4	3	3	4	3	3	4	3	3	4	3	3	4	3	3	4	3	3	4	3	3	3	3	3
	C	3	3	4	3	3	4	3	3	4	3	3	4	3	3	4	3	3	4	3	3	3	3	3	3
	B	3	4	3	3	4	3	3	4	3	3	4	3	3	4	3	3	4	2	1	3	3	3	3	3
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X106 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4
	D	3	3	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4	3	4
	C	3	3	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4
	B	3	3	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4
	A	3	3	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4	2	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X107 SEE NOTE 10 LEAD FREE OPTION	E	7	20	7	20	7	20	7	20	20	5	5	20	20	20	20	5	20	5	20	20	20	20	20	20
	D	8	20	7	20	7	20	7	20	20	5	5	20	20	8	20	5	20	5	20	5	20	5	20	5
	C	5	20	20	20	20	20	7	20	20	5	5	20	20	20	20	5	20	5	20	5	20	20	20	20
	B	8	20	8	20	5	20	5	20	5	5	20	20	20	5	20	20	20	20	20	20	20	20	20	20
	A	20	5	5	5	5	5	5	5	5	5	20	20	20	20	20	5	20	5	20	5	5	20	20	20

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X108 SEE NOTE 10 LEAD FREE OPTION	E	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6
	D	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-
	C	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6
	B	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-
	A	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6	-	6

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER				www.fciconnect.com					
ltr	ecn no.	dr	date	linear		0.X ±0.3		COPY				title METRAL SIGNAL HEADER 4 MOD, 5 ROW PRESS-FIT					
DG						0.XX ±0.13		projection									
						.XXX ±.051											
						angles 0° ±2°											
				dr		T.BRUNGARD 11/19/99				product family		METRAL		code			
						M.STRAWER 11/19/99				size		dwg no		213			
						M.STRAWER 11/19/99				scale		85854		sheet			
						M.STRAWER 02/29/00				1:1		A		16			
sheet index		revision sheet															

Pro/E

3

cage code 22526

4

This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.



A

B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X113 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X114 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	4	2	2	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	4	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X115 SEE NOTE 10 LEAD FREE OPTION	E	8	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
	D	8	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
	C	8	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
	B	8	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
	A	8	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5	5
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X116 SEE NOTE 10 LEAD FREE OPTION	E	2	4	4	2	19	6	6	6	6	2	19	2	2	2	6	6	6	6	6	6	2	1	2	
	D	2	4	4	2	19	6	6	6	6	2	19	2	2	2	6	6	6	6	6	6	6	2	3	2
	C	2	4	4	2	19	6	6	6	6	2	19	2	2	2	6	6	6	6	6	6	6	2	2	2
	B	2	4	4	2	19	6	6	6	21	6	2	19	2	2	2	6	6	6	6	21	6	2	2	2
	A	2	4	4	2	19	6	6	6	6	2	19	2	2	2	6	6	6	6	6	6	6	2	2	2
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X117 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	6	6	6	2	6	2	2	2	2	2	2	6	6	6	6	6	2	2	2	2	2
	D	2	2	2	6	6	6	2	6	2	2	2	2	2	2	6	6	6	6	6	2	2	2	2	2
	C	2	2	2	6	6	6	2	6	2	2	2	2	2	2	6	6	6	6	6	2	2	2	2	2
	B	2	2	2	6	6	6	21	6	2	2	2	2	2	2	2	6	6	6	6	21	6	2	2	2
	A	2	2	2	6	6	6	2	6	2	2	2	2	2	2	2	6	6	6	6	6	2	2	2	2

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER				www.fciconnect.com	
lfr	ecn no.	dr	date			linear	0.X ±0.3	COPY					
DG							0.XX ±0.13	projection				title	
							.XXX ±.051					METRAL SIGNAL HEADER	
						angles	0° ±2°					4 MOD. 5 ROW PRESS-FIT	
						dr	T.BRUNGARD 11/19/99					product family	
						engr	M.STRAWER 11/19/99					METRAL	
						chr	M.STRAWER 11/19/99					size	
						appd	M.STRAWER 02/29/00					dwg no	
sheet		revision										85854	
index		sheet										213	
												sheet	
												17	

A

B



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X123 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1	2	2	2	3	3
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X124 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1	2	2	2	2	3	3
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X125 SEE NOTE 10 LEAD FREE OPTION	E	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	D	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
	A	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6	6
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X126 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X127 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2

mat'l code				tolerances unless otherwise specified		CUSTOMER			
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		www.fciconnect.com	
DG					0.XX ±0.13	projection		title	
					.XXX ±.051			METRAL SIGNAL HEADER	
				angles	0° ±2°	MIM		4 MOD, 5 ROW PRESS-FIT	
				dr	T.BRUNGARD 11/19/99	scale		product family	
				engr	M.STRAWER 11/19/99	1:1		METRAL	
				chr	M.STRAWER 11/19/99	A		size	
				appd	M.STRAWER 02/29/00			dwg no	
sheet		revision						85854	
index		sheet						code	
								213	
								sheet	
								18	

Pro/E

cage code 22526



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

REV E - 2006-04-18

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X133 SEE NOTE 10 LEAD FREE OPTION	E	2	2	2	2	2	2	2	2	2	2	2	2	1	1	2	2	2	2	2	2	2	2	2	2
	D	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1
	C	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	1
	B	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2	1	1	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X134 SEE NOTE 10 LEAD FREE OPTION	E	2	1	2	1	1	3	1	3	3	3	3	3	3	3	1	1	1	1	1	1	1	1	1	1
	D	2	1	2	1	1	3	1	3	3	3	3	3	3	3	1	1	1	1	1	1	1	1	1	1
	C	2	1	2	1	1	3	1	3	3	3	3	3	3	3	1	1	1	1	1	1	1	1	1	1
	B	2	1	2	1	1	3	1	3	3	3	3	3	3	3	1	1	1	1	1	1	1	1	1	1
	A	2	1	2	1	1	3	1	3	3	3	3	3	3	3	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X135 SEE NOTE 10 LEAD FREE OPTION	E	7	7	7	7	7	7	7	7	7	7	7	7	7	7	20	7	7	20	7	7	8	7	20	
	D	7	7	7	7	7	7	7	7	7	7	7	7	7	7	20	7	7	20	7	7	8	7	20	
	C	7	7	7	7	7	7	7	7	7	7	7	7	7	7	20	7	7	20	7	7	8	7	20	
	B	7	7	7	7	7	7	7	7	7	7	7	7	7	7	20	7	7	20	7	7	8	7	20	
	A	7	7	7	7	7	7	7	7	7	7	7	7	7	7	6	7	7	20	7	7	8	7	20	

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
85854-X136 SEE NOTE 10 LEAD FREE OPTION	E	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	3	3	19	3	3	4	3	19	
	D	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	3	3	19	3	3	4	3	19	
	C	3	3	3	3	3	3	3	3	3	3	3	3	3	3	19	3	3	19	3	3	4	3	19	
	B	3	3	3	4	4	4	4	4	4	4	4	4	4	4	19	3	3	19	3	3	4	3	19	
	A	3	3	3	2	2	2	2	2	2	2	2	2	2	2	2	3	3	19	3	3	4	3	19	

mat'l code				--		tolerances unless otherwise specified		CUSTOMER				www.fciconnect.com	
litr	ecn no.	dr	date	linear	0.X ±0.3		COPY			title METRAL SIGNAL HEADER 4 MOD, 5 ROW PRESS-FIT			
DG					0.XX ±0.13		projection						
					.XXX ±.051								
				angles	0° ±2°					product family		METRAL	code
				dr	T.BRUNGARD 11/19/99		MIM			size	dwg no	85854	213
				enrg	M.STRAWSE 11/19/99		scale						
				chr	M.STRAWSE 11/19/99		1:1						
				appd	M.STRAWSE 02/29/00				A				sheet 19
sheet index	revision sheet												

cage code 22526

Pro/E

3

4



PRODUCT NUMBER
85854-XXX OR 85854-YYYY
85854-XYLFF OR 85854-YYYYLF

NOTES:

- FOR DIM A AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL
POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL:
PHOSPHOR BRONZE.
- PLATING ON PRESS-FIT TAIL:
85854-XXX IS SnPb
85854-XYLFF IS SN (LEAD FREE)
PLATING ON CONTACT AREA CONFORMS TO PERFORMANCE
LEVEL SHOWN IN TABLE BELOW.
- PRODUCT MARKING:
PART NUMBER DESIGNATION & BATCH I.D.
- ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXP
- PRODUCT SPECIFICATION GS-12-180
APPLICATION SPECIFICATION BUS-20-073
- AFTER INSERTION INTO CIRCUIT BOARD WITH
QUALIFIED TOOL.
- THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF MEET THE
EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-22-008.

ALL PRODUCTS EXCEPT THOSE WITH PART NUMBERS CONTAINING
(DRAWING NO.)-N1--- OR (DRAWING NO.)-N5---WILL WITHSTAND EXPOSURE
TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR
VAPOR PHASE REFLOW OVEN. PART NUMBERS (DRAWING NO.)-N1---
AND (DRAWINGS NO.)-N5---WILL NOT WITHSTAND REFLOW AND Au CONTACT
SURFACE OF THE CONTACTS SHALL BE EXPOSED TO A MAXIMUM 140°C FOR
NO LONGER THAN 15 SECONDS IN A WAVE SOLDER APPLICATION.

PLATING IN CONTACT AREA		NOTES
DASH NUMBER	PERFORMANCE LEVEL	
-PYY OR -PYYY	0.25 um GOLD MIN.	-
-NIYY OR -NIYYY	TELCORDIA CO (NXT)	-
-NSYY OR -NSYYY	TELCORDIA UE (NXT)	-
-IYY OR -IYYY	TELCORDIA CO	-
-2YY OR -2YYY	TELECOM CLASS	-
-3YY OR -3YYY	IEC CLASS I	-
-5YY OR -5YYY	TELCORDIA UE	-
-NIYYLF OR -NIYYLFF	TELCORDIA CO (NXT) IEC CLASS I	SEE NOTE 9
-NSYYLF OR -NSYYLFF	TELCORDIA UE (NXT)	SEE NOTE 9
-IYYLF OR -IYYLFF	TELCORDIA CO IEC CLASS I	SEE NOTE 9
-2YYLF OR -2YYLFF	TELECOM CLASS	SEE NOTE 9
-5YYLF OR -5YYLFF	TELCORDIA UE	SEE NOTE 9

10. FOR LEAD FREE PART NUMBERS ADD AN "LF" SUFFIX..
EXAMPLE: 85854-X0ILF

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER				www.fciconnect.com		
litr	ecn no.	dr	date	linear	0. X ±0.3		COPY			title METRAL SIGNAL HEADER 4 MOD, 5 ROW PRESS-FIT				
DG					0. XX ±0.13		projection							
					. XXX ±.051									
				angles	0° ±2°				product family METRAL			code 213		
					dr T.BRUNGARD 11/19/99									
					enrg M.STRAWER 11/19/99		scale 1:1		size A		dwg no 85854		sheet 20	
					chr M.STRAWER 11/19/99									
				appd	M.STRAWER 02/29/00									
sheet index	revision sheet													

cage code 22526