

DEWALT[®]

ONSITE OFFERS **EXTRA**

NEW PRODUCTS ■ SERVICE ■ NEWS ■ TECHNICAL ■ COMPETITIONS ■ FREE TO THE TRADE

NEW!

**36
VOLT**

Li-Ion

NEW See
pages 4-5
36 VOLT

**NEW XRP
DRILLS** See
page 7

7
PAGES OF

**GREAT
DEALS**

See pages 8-9, 10-11,
13, 16-17

**NEW
XRP**

See page 7

See page 13

**MORE
VALUE**



THE POWER OF CORDED WITHOUT THE CORD™

The 36 Volt cordless battery platform was developed to provide professional contractors **with the performance needed to complete high-powered applications** which, previously, were only possible with corded tools.

The **unique Nano-Phosphate lithium-ion technology**, which is exclusive to DeWALT, has been developed to offer a high level of power, run-time and durability

compared to conventional lithium technology. This brand new battery technology offers **over 2000 charge cycles**, which is significantly better than previous battery technology.

With this breakthrough innovation, the new DeWALT 36 Volt tools will live up to DeWALT's commitment to providing Guaranteed Tough product for the professional end user.



HEAVY-DUTY 36V BATTERY PACK & 1 HOUR CHARGER


Li-Ion 36 VOLT DE9360

DeWALT Exclusive Nano-Phosphate Lithium-ion Cells
Provide high power for corded performance
Deliver 2-3x more run-time vs 18V batteries
Offer long battery life & durability: 2000 recharges

Lightweight Design
1kg - same weight as a DeWALT 18V battery
No Memory & No Self-Discharge
For maximum productivity & less downtime



1-Hour Charging
Provides fast charging for minimum downtime




DE9000

Battery Fuel Gauge
Indicates how much charge is in the battery

Cord Wrap
Provides improved cord storage

DeWALT 3-Stage Charging System
Provides maximum run-time and extends overall life of the battery



Heavy-Duty 36V Cordless Hammerdrill/Drill/Driver Kit



36V 1 Hr Charger



Heavy-Duty 36V Cordless SDS Rotary Hammer Kit



Heavy-Duty 36V Cordless Impact Wrench Kit



Heavy-Duty 36V Battery Pack



Heavy-Duty 36V Cordless Circular Saw Kit



DC509 Heavy-Duty 36V Cordless Floodlight



Heavy-Duty 36V Cordless Jigsaw Kit



Heavy-Duty 36V Cordless Reciprocating Saw Kit

www.DEWALT.co.uk/36v

CONTENTS THIS ISSUE!

GREAT DEALS & NEW PRODUCTS FOR YOU

DeWALT®

GREAT DEALS FOR YOU!

■ **NEW!** Deals for you

..... 8 - 11, 13, 16-17

NEW FOR YOU - CORDLESS

■ **NEW!** 36V Range 4 - 5

■ **NEW!** XRP 7

NEW FOR YOU - MACHINERY

■ **NEW!** Machinery / Saws 14

■ **NEW!** Woodworking 15

NEW FOR YOU - DRILLS

■ **NEW!** Percussion Drills 12

NEW FOR YOU - ACCESSORIES

■ **NEW!** Drill Bits 18

■ **NEW!** Bonded Discs 19

NEW FOR YOU - CONSTRUCTION


■ **NEW!** Lasers 13

SERVICE POLICY 6



NEW XRP

NEW XRP
ONLY £199.00
Ex. VAT



4-5

36 VOLT

Li-Ion

ALL NEW



10-11

GREAT DEALS

DC618KA NAILER
+ 3RD BATTERY
ALL FOR ONLY
£399.00
Ex. VAT

**DeWALT OFFICIAL TOOL SUPPLIER
TO THE WILLIAMS F1 TEAM**



WILLIAMS F1 TEAM
OFFICIAL SUPPLIER

NEW! 36V CORDLESS RANGE




THE POWER OF CORDED WITHOUT THE CORD™



HEAVY-DUTY 36V CORDLESS HAMMERDRILL/DRILL/DRIVER KIT

DC900KL

COMING SOON!





Cat. No.:	DC900KL
Power (mw):	800
Chuck Size (mm):	13
Speeds (rpm):	3 0-400 / 0-1200 / 0-1600
Hammerdrill (bpm):	0-7650 / 0-20400 / 0-27200
Clutch Settings:	22
Weight (kg):	3.1
Includes:	2 x 36V Battery Packs, 1 Hour Charger, 360° Side Handle & Heavy-Duty Kitbox

HEAVY-DUTY 36V CORDLESS IMPACT WRENCH KIT

DC800KL

COMING SOON!



Cat. No.:	DC800KL
Max Torque (Nm):	440
Speed (rpm):	0 - 1400
Impacts per min (ipm):	0 - 2500
Drive (inches):	1/2" Square with Detent Pin
Switch Type:	Rocker
Weight (kg):	3.4
Includes:	2 x 36V Battery Packs, 1 Hour Charger, & Heavy-Duty Kitbox

HEAVY-DUTY 36V CORDLESS SDS ROTARY HAMMER KIT

DC234KL

COMING SOON!




Cat. No.:	DC234KL
Chuck Type:	SDS
Speed (rpm):	0 - 1150
Blows per minute (bpm):	0 - 4300
Impact Energy (Joules):	2.5
Weight (kg):	3.8
Includes:	2 x 36V Battery Packs, 1 Hour Charger, Side handle with depth stop & heavy duty kitbox

HEAVY-DUTY 36V CORDLESS RECIPROCATING SAW KIT

DC305KL

COMING SOON!





Cat. No.:	DC305KL
Speed (spm):	0-3000
Stroke Length (mm):	29
Keyless Blade Clamp:	Yes, 4 Position
Adjustable Shoe:	Yes, 3 Position
Electric Brake:	Yes
Weight (kg):	3.8
Includes:	2 x 36V Battery Packs, 1 Hour Charger, Blade & Heavy-Duty Kitbox

HEAVY-DUTY 36V CORDLESS JIGSAW KIT

DC308KL

COMING SOON!





Cat. No.:	DC308KL
Speed (spm):	0 - 2700
Stroke Length (mm):	26
Keyless Blade Clamp:	Yes
Orbital Action:	Yes, 4 Position
Electric Brake:	Yes
Weight (kg):	3.4
Includes:	2 x 36V Battery Packs, 1 Hour Charger, blades & Heavy-Duty Kitbox

HEAVY-DUTY 36V CORDLESS CIRCULAR SAW KIT

DC300KL

COMING SOON!



Cat. No.:	DC300KL
Speed (rpm):	4000
Bevel Capacity: (Degrees °)	0°-50° 90°/62mm 45°/41mm
Blade size (mm):	184
Bore Size (mm):	20
Keyless Blade Change:	Yes
Weight (kg):	4.5
Includes:	2 x 36V Battery Packs, 1 Hour Charger, 24T Carbide Tipped Blade, Rip Fence & Heavy-Duty Kitbox

HEAVY-DUTY 36V CORDLESS COMBO KITS

DCX6401

- KIT INCLUDES:**
- Hammerdrill/Drill/Driver
 - Jigsaw
 - Circular Saw
 - Floodlight
 - 2 x 36V battery packs
 - 1 hour charger
 - 360° side handle
 - 184mm carbide tipped saw blade
 - Rip fence
 - Jigsaw blade
 - Heavy-duty kit box

COMING SOON!



DCX6402

- KIT INCLUDES:**
- Rotary Drill
 - Reciprocating Saw
 - Circular Saw
 - Floodlight
 - 2 x 36V battery packs
 - 1 hour charger
 - 360° side handle
 - 184mm carbide tipped saw blade
 - Rip fence
 - Reciprocating saw blade
 - Heavy-duty kit box

COMING SOON!



HEAVY-DUTY 36V CORDLESS FLOODLIGHT

DC509



COMING SOON!

HEAVY-DUTY 36V BATTERY PACK

DE9360

- DeWALT Exclusive Nano-Phosphate Lithium-Ion Cells**
Provide high power for corded performance. Deliver 2-3x more run-time vs 18V batteries. Offer long battery life & durability: 2000 recharges.
- Lightweight Design**
1Kg - same weight as a DeWALT 18V battery.
- No Memory & No Self-Discharge**
For maximum productivity & less downtime.

COMING SOON!



THE POWER OF CORDED WITHOUT THE CORD™



The 36 Volt cordless battery platform was developed to provide professional contractors with the performance needed to complete high-powered applications which, previously, were only possible with corded tools.

The unique Nano-Phosphate lithium-ion technology, which is exclusive to DeWALT, has been developed to offer a high level of power, run-time and durability compared to conventional lithium technology. This brand new battery technology guarantees over 2000 charge cycles, which is significantly better than previous battery technology.

With this breakthrough innovation, the new DeWALT 36 Volt tools will live up to DeWALT's commitment to providing Guaranteed Tough product for the professional end user.

WHAT MAKES DeWALT A 5-STAR SERVICE?

- ★ **FAST REPAIR TURNAROUND**
We know that time is money and you need your tools back in action in the fastest time possible. There's even a 'While U Wait' service for urgent smaller jobs.
- ★ **HIGH QUALITY**
All repairs are carried out by factory-trained technicians, using genuine parts and all work is backed by our 90-Day warranty.
- ★ **QUICK PARTS AVAILABILITY**
DeWALT Agents carry the most frequently used spare parts. If a part is not in stock, we would expect to have it delivered within 24 hours.
- ★ **THE UTMOST CONVENIENCE**
Our locations and opening times are determined by the needs of our customers. Our technical tool specialists are available to answer questions, whether you're on or off the job site.
- ★ **SUPERIOR CUSTOMER SERVICE**
Every completed repair comes with our Repair Satisfaction Tag, which lists everything that's been done and gives a number to call should you be less than 100% happy with any of the work.

SPARE PARTS SALES & REPAIRS
We offer a full repair service on DeWALT power tools and supply a comprehensive range of spare parts, batteries and chargers.

RAPID REPAIR SERVICE
Subject to parts availability, repairs should not take more than 48 hours. There is a 'While U Wait' service for urgent smaller jobs.

WARRANTY REPAIRS
If the tool is covered by its original DeWALT 1 Year Warranty, all repairs are free, including parts and labour. Proof of purchase must be produced.

SPECIALIST REPAIRS
DeWALT Agents offering 5 star service can undertake repairs to specialised products such as Radial Arm Saws, Nailers and Compressors.

GENUINE FACTORY PARTS
All parts used for repairs are original DeWALT factory parts.

FACTORY TRAINED TECHNICIANS
Our repair technicians are fully trained to DeWALT factory standards.

ON-LINE TECHNICAL SUPPORT
Access via the Internet on a wide range of DeWALT related subjects, from finding a Service Agent to replacing a lost instruction manual.



Note: Whilst all DeWALT Agents provide the highest quality standards, they do not all offer the full range of services listed above. All agents display their full list of services, which can also be accessed by visiting our website. www.DeWALT.co.uk



For your nearest Service Repair Agent please visit www.DeWALT.co.uk or call 0700 4 DeWALT (339258)

NEW! DC925KB COMBINATION DRILL

DC925KB Combination Drill

NEW! Transmission development for quick & precise gear change

NEW! PM47 XT Motor for increased power

NEW! Self tightening chuck for effective bit retention

NEW! Clutch development

NEW! Switch upgrade for increased load and durability

NEW! 30 Minute Charger for twice the charging speed

NEW! 2.6Ah NiMH Batteries for increased runtime

THE BEST JUST GOT BETTER

XRP
NEW! DeWALT XRP DRILLS
More Power • More Run Time • More Productivity

POWER
To perform high speed and high torque applications

RUN TIME
To work day in day out in all weathers from dusk till dawn with the NEW 2.6Ah NiMH Battery

DURABILITY
To withstand the strains of heavy duty work in a job site environment

ERGONOMICS
To ensure maximum productivity with minimum fatigue levels

■ MORE POWER ■ MORE RUN TIME ■ MORE PRODUCTIVITY

SPECIFICATION					
CAT. No.:	DC925KB	DC920KB	DC935KB	DC945KB	DC940KB
Type:	Combi	Drill Driver	Combi	Combi	Drill Driver
Voltage:	18	18	14.4	12	12
Chuck Type:	Rohm Self Tightening	Rohm SS	Rohm Self Tightening	Rohm Self Tightening	Rohm SS
Chuck Size:	13mm	13mm	13mm	13mm	13mm
Battery Amp Hour:	2.6Ah NiMH	2.6Ah NiMH	2.6Ah NiMH	2.6Ah NiMH	2.6Ah NiMH
Power Output (Watts) :	480	480	380	310	310
Max No Load Speed (rpm) :	2000	2000	1800	1800	1800
Max Sustained Torque (Nm) :	56	56	50	48	48
Max Capacity Wood (mm) :	50	50	45	38	38
Max Capacity Metal (mm) :	13	13	13	13	13
Max Capacity Masonry (mm) :	16	-	14	12	-
Max BPM:	34000	-	30600	30600	-
Weight (Kg):	2.8	2.7	2.5	2.4	2.3

- FEATURES AND BENEFITS...**
- **Performance** - Drilling and fastening performance have been significantly improved with a new, more powerful DeWALT built motor. The new transmission and clutch efficiently deliver this extra power.
 - **Increased productivity** - New 2.6Ah batteries now deliver increased runtime, while the new 30 minute charger also means less downtime.
 - **Durability** - The new housing design combined with improvements to the switch, motor and transmission make this the most durable Cordless drill DeWALT have ever made.
 - **Ease of use** - provided by DeWALT best in class ergonomics and NEW self tightening keyless chuck which grips the drill bit tighter than a conventional keyless chuck.



■ ALSO AVAILABLE:

DC920KB
18 Volt 13mm
Heavy Duty
Drill/ Driver

DC935KB
14.4 Volt 13mm
Heavy Duty
Hammerdrill/ Driver

DC945KB
12 Volt 13mm
Heavy Duty
Hammerdrill / Driver

DC940KB
12 Volt 13mm
Heavy Duty
Drill/ Driver

BUY THIS... DC925KD 18.0 VOLT COMBINATION DRILL


XRP

NEW! **SYSTEM 18 VOLT**



GET THIS
EXTRA 3RD
BATTERY DE9503

- NEW! Transmission development
- NEW! PM47 XT Motor
- NEW! Self tightening chuck
- NEW! Clutch development
- NEW! Switch upgrade
- NEW! 2.6Ah NiMH batteries



BUY THIS... DC935KD 14.4 VOLT COMBINATION DRILL

XRP


NEW! **SYSTEM 14.4 VOLT**



Also available as
12.0 Volt DC945
supplied with
2 batteries.
(No 3rd battery)

GET THIS
EXTRA 3RD
BATTERY DE9502

- NEW! Transmission development
- NEW! PM47 XT Motor
- NEW! Self tightening chuck
- NEW! Clutch development
- NEW! Switch upgrade
- NEW! 2.6Ah NiMH batteries



BUY THIS... DC756FA 12 VOLT 13MM HEAVY DUTY EXTRA RUNTIME CORDLESS DRILL/DRIVER



GET THIS

DE0109-XJ 109
PIECE BIT SET
& DW904-XJ
12.0V 90° PIVOT
HEAD CORDLESS
FLASHLIGHT

- Powerful 12 Volt drill driver for drilling and screwdriving applications
- Compact, lightweight design.
- 17 position adjustable torque control
- Two speed settings, variable speed and reverse switch.



BUY THIS... DC729KQ3 18.0 VOLT 10MM CORDLESS DRILL DRIVER



GET THIS


DC056N
18.0 VOLT COMPACT
IMPACT DRIVER

- Electronic motor brake for added control
- High performance fan cooled motor for maximum power and durability
- 17 position adjustable torque



DC5PAKB 18.0 VOLT HEAVY DUTY CORDLESS COMBOPACK

XRP



SYSTEM 18 VOLT

**INCLUDES
NEW XRP**



Combopack contains:
18.0 Volt heavy duty 13mm hammerdrill /driver, DC390 - 18.0 Volt heavy duty XRP circular saw, DC380 - 18.0 Volt heavy duty reciprocating saw, DC330 - 18.0 Volt heavy duty top handle jigsaw and DW919 - 18.0 Volt heavy duty flexible floodlight. 2 batteries 2.6NiMH. 30 minute charger. Kitbox included.

HEAVY DUTY 18.0 VOLT CORDLESS TWINPACKS

XRP

DC925JB 18.0 Volt Heavy Duty Cordless Combopack

Combopack contains:
DC925KB - 18.0 Volt heavy duty 13mm hammerdrill /driver and DC330 18.0 Volt heavy duty top handle jigsaw. 2 batteries 2.6NiMH. 30 minute charger. Kitbox included.



**INCLUDES
NEW XRP**

DC925SB 18.0 Volt Heavy Duty Cordless Combopack

Combopack contains:
DC925KB - 18.0 Volt heavy duty 13mm hammerdrill /driver and DC390 18.0 Volt heavy duty circular saw 2 batteries 2.6NiMH. 30 minute charger. Kitbox included.



**INCLUDES
NEW XRP**

DC925CB 18.0 Volt Heavy Duty Cordless Combopack

Combopack contains:
DC925KB - 18.0 Volt heavy duty 13mm hammerdrill /driver and DC390 18.0 Volt heavy duty reciprocating saw 2 batteries 2.6NiMH. 30 minute charger. Kitbox included.



**INCLUDES
NEW XRP**

BUY THIS... DW979KQ3 12.0 VOLT HEAVY DUTY CORDLESS DRYWALL SCREWDRIVER



GET THIS

DC010 7.2 -
18.0 VOLT
CORDED/CORDLESS
RADIO& DE9075-XJ
12.0 VOLT
BATTERY

- Compact and ergonomic 12.0 Volt drywall screwdriver
- Removeable depth sensitive "set and forget" nosepiece for consistent fastener depth
- 6.35 mm hex shank magnetic tool holder
- Up to 8.5 Nm of sustainable torque for maximum performance
- Ergonomically-designed soft grip and trigger for added user comfort
- Two speed settings, variable speed and reverse switch for maximum control

INCLUDES: 1 hour charger, 2 batteries, magnetic bit holder, screwdriver bit and heavy duty carrying case.




BUY THIS... DC380KA XRP 18.0 VOLT RECIPROCATING SAW



GET THIS

EXTRA 3RD
BATTERY DE9095

- New DeWALT built motor for increased power
- Variable speed trigger and electronic motor brake for quick controlled cuts
- Keyless blade change




BUY THIS...
DC330KA 118.0 VOLT
CORDLESS JIGSAW



GET THIS
EXTRA 3RD
BATTERY DE9095

- 3000 strokes per minute for faster production rate
- 2.4Ah NiCd batteries for longer runtime
- Massive 130mm depth of cut




BUY THIS...
DC410KA 18.0 VOLT 115MM
CORDLESS FINISHING GRINDER



GET THIS
EXTRA 3RD
BATTERY DE9095

- Powerful DeWALT fan cooled motor with replaceable brushes delivers maximum power and durability
- 7000rpm provides high power for cutting and grinding applications
- Keyless guard for enhanced application versatility



BUY THIS...
DC213KA 18.0 VOLT
XRP 3 MODE HAMMER



NEW!

AVC



- Floating housing reduces vibration by 30%
- Extremely compact, high performance mechanism.
- Rubber switch trigger
- Easy to fit/remove rear mounted standard 24V/18V battery slide rail system

BUY THIS...
DC212N 18.0 VOLT
2 MODE HAMMER



NEW!

AVC



(No batteries
/charger
or kitbox)

- Floating housing reduces vibration by 30%
- Extremely compact, high performance mechanism.
- Rubber switch trigger
- Easy to fit/remove rear mounted standard 24V/18V battery slide rail system

CORDLESS SDS DRILLING


BUY THIS...
DC618KA 18.0 VOLT CORDLESS
GAUGE NAILER

XRP



- Powerful 18 Volt Heavy Duty Cordless 20" 16 gauge Nailer - NO gas required!
- The DC618KA uses any DeWALT 18 volt rechargeable battery without gas cartridges meaning it can be used anywhere without restrictive cables or noxious fumes

GET THIS
EXTRA 3RD
BATTERY DE9095



BUY THIS...
DC224KA 24.0 VOLT 3 MODE HAMMER
WITH QUICK CHANGE CHUCK

NEW!

**SYSTEM
24
VOLT
AVC**

Also available:
DC222KA
DC223KA



- Compact hammer 'Mode change selector'
- Rounded ergonomic housings
- Floating housing reduces vibration by 30%
- Extremely compact, high performance mechanism

BUY THIS...
DC234KL HEAVY DUTY 36.0 VOLT
CORDLESS SDS ROTARY HAMMER

NEW!

**36
VOLT**



- 2.6 Joules impact energy provides corded power without the cord
- Compact L-shape design allows access in tight spaces
- Anti-slip comfort grip
- Active vibration control DeWALT built high torque, High efficiency motor

NEW! D21815KS

NEW! improved hammer selector for positive & reliable mode selection

Increased power & torque for heavy duty applications

NEW! metal gear case with improved ergonomics

NEW! patented ball clutch for increased reliability

NEW! improved 2 speed selector for increased reliability

NEW! patented armature support for increased durability

NEW! Gear Shaft

Keyless Chuck

FEATURES AND BENEFITS...

- Durability** - The durability and reliability have been significantly enhanced with a new patented ball clutch and transmission design. The friction clutch system has been replaced with a new sintered ball clutch design which is more robust and extends unit life. The motor size has increased and is wound for optimum power and efficiency. The transmission system has been upgraded in order to transmit this extra power with a patented armature support system combined with an increase in gear face width and tooth strength.
- Power** - The drilling performance and user productivity have been increased with a new higher power motor. The increased power density of the motor delivers more torque under load to the user resulting in increased penetration speed and a reduction in drilling time.
- Ergonomics** - The ergonomics and handling of the unit have been improved with a new low profile contoured gear case making the unit both shorter and lighter than current product offerings. The new two speed and percussion / rotary mode selectors ensure a more positive engagement.

■ DURABLE ■ POWERFUL ■ COMPACT

■ SPECIFICATION

CAT. No.:	D21805	D21805KS	D21810KS	D21815KS	D21441
Input (Watts):	770	770	770	850	770
No Load Speed:	0-1100 0-2700	0-1100 0-2700	0-1100 0-2700	0-1100 0-2700	0-1100 0-2700
FEATURES:					
Cord Length:	4M	4M	4M	4M	4M
Side Handle:	YES	YES	YES	YES	YES
Ball Clutch:	NO	NO	YES	YES	YES
Percussion:	YES	YES	YES	YES	NO
Gear Case:	PLASTIC	METAL	METAL	METAL	PLASTIC
Variable Speed:	YES	YES	YES	YES	YES
Chuck:	KEYED	KEYLESS	KEYLESS	KEYLESS	KEYLESS
Kitbox:	NO	YES	YES	YES	NO

■ PERCUSSION DRILLS - THE RANGE

D21805K
770 Watt
Variable Speed
Percussion Drill

D21810KS
770 Watt
Variable Speed
Percussion Drill with
Keyless Chuck and Clutch

D21441
770 Watt
Variable Speed
Rotary Drill with
Keyless Chuck and Clutch

D25002K 2KG
2 MODE HAMMER



- Ideal for drilling anchor fixings up to 22mm
- Impact stop mode for wood and metal drilling
- Delivers 2.4 joules of impact energy

D25103C 2KG 3 MODE SDS-PLUS
24MM COMBINATION INLINE
HAMMER




- Ideal for from 4 to 24mm. Rotation stop for light chiselling applications
- Impact stop for drilling wood, steel, Delivers 3 joules of impact energy

D25600K 6KG
COMBINATION HAMMER



- 1150 Watt motor and oversized mechanism delivers 9.8 joules of impact energy
- Active Vibration System keeps vibration under 10m/s²
- Ideal for drilling anchor, fixing and through holes in concrete and masonry from 12 to 45mm in diameter
- Core drilling up to 100mm. Unique dust sealing protection to prevent even the finest dust ingress into the hammer mechanism

BUY THIS...
D25900Q3 10KG DEMOLITION
HAMMER



- Large oversize hammer mechanism delivers extreme durability and excellent concrete breaking performance
- Controllable impact energy provides the optimum setting to suit any application in any masonry material

GET THIS

230MM 2100 WATTS ANGLE GRINDER & DeWALT JACKET

SPECIFICATION

CAT. No.:	D27111
Power Input :	1500
No Load Speed (rpm):	3000
Vertical Capacity:	90
X Cut Capacity (mm):	220
Mitre Capacity (R/L):	60°/50°
Mitre Fences:	High and sliding
Mitre Accuracy:	0.2mm
Slide:	Yes
Cut Capacity (R) (mm):	220
Weight (Kg):	26.5
Bevel Capacity (Right):	45°
Table Saw DOC (mm):	51
Table Size (mm):	457 x 305
Cable:	4m

STANDARD EQUIPMENT

- S40 305 X 48T CSB
- Push stick
- Guard

FEATURES AND BENEFITS

- **Accuracy** - Precision cast aluminium base and sliding head design guarantees high quality precision in both cutting modes.
- **Power** - Unit is provided with a high-torque induction motor with the power to cut pressure treated material and hardwoods
- **Ease of Use** - New mitre angle controls and the sliding head feature make setting up quick and easy.
- **Portability** - At only 26kg, the unit is easily transported around the jobsite. In addition handles are provided to improve the ease of use.
- **Capacity** - The sliding head design provides excellent cross cut capacity

D27111 305mm TABLE TOP MITRE SAW

Sliding Head Design makes it possible to cut up to 220mm in mitre saw mode

1500W Induction Motor delivers the power and torque for all applications and is extremely quiet in operation

Aluminium Table & Base Design provides a lightweight but durable unit

AVAILABLE OCTOBER

Parallel Fence maintains accuracy of cut within 0.4mm

Mitre Angle Adjustment provides easy and precise set up for all cutting requirements. (60°R/50°L)

220mm Cross Cut Capacity **90mm Depth of cut in Mitre Mode**

■ ACCURATE ■ POWERFUL ■ COMPACT ■ PORTABLE

SPECIFICATION

CAT. No.:	DW745
Power Input :	2000
No Load Speed (rpm):	3600
Vertical Capacity:	79
Cut Capacity R (mm):	410
Depth of Cut (mm):	77
Right Rip (mm):	410
Left Rip (mm):	315
Weight (Kg):	22
Bevel Capacity (Right):	45°
Table Size (mm):	457 x 305
Parallel Fence:	Rack & Pinion

STANDARD EQUIPMENT

- S40 250 X 24T
- Push Stick
- CSB
- Blade Guard
- Parallel Fence
- Wrench
- Mitre Fence

FEATURES AND BENEFITS...

- **Accuracy** - The rack and pinion fence design makes adjustments fast smooth and accurate ensuring that the fence is always parallel to the blade
- **Power** - Unit is provided with a high-torque motor with the power to cut pressure treated material and hardwoods
- **Durability** - The new roll cage design provides excellent durability
- **Portability** - At only 22kg, the unit is easily transported around the jobsite. In addition handles are provided to improve the ease of use.
- **Capacity** - With 410mm right rip capacity even the most challenging cutting applications can be achieved.

DW745 LIGHTWEIGHT TABLE SAW

Optimised footprint makes it the smallest saw with it's capacity by more than 20%

Capacity Right Rip = 410mm Left Rip = 315mm

Telescoping Fence provides 410mm of rip to the right of the blade

Weight 22Kg

AVAILABLE OCTOBER

95mm, 2600 MW motor delivers the power and torque for hardwoods and stacked cuts

Metal Roll Cage Base - Designed to withstand drops, unsecured transportation and jobsite use that ruins plastic bases

Rack & Pinion® Rails maintain accuracy of cut within 0.4mm

MACHINERY RANGE



D26441 ORBITAL PALM GRIP SANDER

NEW!



Dust sealed switch prevents contamination

100% sealed bearing - construction provides longer life

Anti-slip top & body soft grip

230W Motor for consistent sanding performance in all applications

High capacity - flexible dust bag with built in vacuum adapters

Dual-plane counter balanced fan - Reduced vibration & user fatigue with improved cooling

Hook & loop paper and conventional paper clamps for paper fixing - Fast paper changes, consistent adhesion & improved dust collection



DW341K COMPACT TOP HANDLE JIGSAW

NEW!

FEATURES AND BENEFITS...

- **Ergonomics** - Compact & lightweight, this unit is extremely comfortable & versatile in use.
- **Cut alignment** - Due to its no-flex construction these new units can deliver extremely accurate cuts, both in the horizontal and vertical planes.
- **Flush Cutting** - In combination with the DeWALT Flush cutting blade these new units can extend a cut up to an edge or vertical surface.
- **Power** - Using a 550 watt motor with large power reserves this unit delivers extremely high cutting performance while maintaining durability.

ALSO AVAILABLE...

DW343K COMPACT BODY GRIP JIGSAW



All airflow exits towards the front

Tool free blade change

Crabbing minimised with new mechanism


Built-in dust blower for cut line visibility

Variable speed control

Reduced girth gives excellent ergonomics

Reduced length

Design to take the supported flush cutting blade



BUY THIS... DW743NQ3 250MM FLIP OVER SAW COMPLETE KIT



- Classic TGS flip over bevelling saw
- Rapid tool free transformation from saw bench to a mitre saw
- Provides flexibility in a range of site and workshop applications


GET THIS
DE3472 RIGHT SIDE EXTENSION
TABLE PLUS
DE3497 ROLLER SUPPORT TABLE

BUY THIS... DW718Q2 MITRE SAW



- The best just got better
- Replacing the existing DW708, this new unit has new improved controls, increased capacity and yet is also more compact
- 163mm depth of cut

GET THIS
DE7023
LEGSTAND



BUY THIS... DW625Q3 2000 WATT 1/2" VARIABLE PLUNGE ROUTER



- Electronic speed control ensure that the same fine finish is achieved
- Two column precision guides with phosphor bronze bushes for plunging accuracy
- Soft start to eliminate any small initial movement that may mis-align the cutter

GET THIS
DE6240 CONSTRUCTION
WORK TOP JIG



BUY THIS... DW682KV BISCUIT JOINTER



- Rack and pinion control provides easy, accurate vertical fence adjustment
- Mitre fence that remains attached in all applications for simple use
- Anti-slip material grippers, eight guiding notches and fence window aid accurate cuts

GET THIS
BOX OF BISCUITS



NEW! PROFESSIONAL DRILL BITS RANGE

NEW! DeWALT BITS

COMING SOON...



FEATURES

■ Variant Multi Material Bit

- Special 120° grind for max. sharpness copper braze for heat resistance
- Special CrNiMo steel
- 3 flats on shank
- Fully supported head with aggressive angles to maximise life and speed
- Produced from top quality European steel
- Made in Germany
- Lot date coded and controlled

Multi Material Bit

Robust Multi Material Bit designed for drilling in different materials. This drill bit is designed for drilling where different materials (masonry, metal, wood) are sandwiched together.

NEW! DeWALT BITS

COMING SOON...



FEATURES

■ Extreme Cobalt Bits

- Unique new design for Cobalt drill bit range
- Special 130o tip eliminates walking and drills fast, accurate and clean hole
- Tapered central core for stronger, longer drill bit life
- 3 flats on shank eliminates slipping in chuck

Extreme Cobalt Bit

Bit 'spine' is larger near the base of the bit ensuring bit strength. Three flats on bit shaft eliminate bit slippage in chucks – No.1 end user complaint of round shaft drill bits.

NEW! DeWALT BITS

COMING SOON...



FEATURES

■ SDS 4 Cutter Drill Bits

- New 4 cutter head
- Large free space enables faster drilling and efficient debris removal
- 4 flute design enables rapid removal of material
- 4 cutter head drills more concentric hole for better fixing retention verses 2 cutter

SDS 4 Cutter Drill Bit

Low friction head design = high speed. Same SDS+Tip 2 cutter and MAX. Open mill entry to flutes. 4 cutter off-set head design maximises speed and minimises vibration.

NEW! BONDED DISCS

■ APPLICATIONS

- Cutting and Grinding applications in Stainless steel & thin metal
- Aluminium, Metal, Masonry, concrete and stone

■ ADVANTAGES

- Fast cutting
- Long Life
- Aggressive material removal

■ ADDITIONAL

- Improved communication and packaging
- Industry recognised colour coding and identification system to help user identify the right bonded disc for their application.



The **NEW!** range of cutting and grinding discs from DeWALT available in store now - **see your dealer for details**

NEW! METAL CUTTING & GRINDING DISCS



- Type 1 flat and Type 27 depressed centre metal cutting and grinding discs
- Professional grade Aluminium oxide for fast cutting, aggressive material removal and long life
- Premium resin bond for product consistency and quality
- Reinforced fibre glass for added durability and life
- Metal cutting discs 100mm-230mm
- Metal grinding discs 100mm-230mm

NEW! INOX AND THIN METAL CUTTING & GRINDING DISCS



- Type 1 flat and Type 27 depressed centre inox and thin metal cutting and grinding discs
- Professional grade Aluminium oxide and White aluminium oxide formulation for fast cutting, aggressive material removal and long life in harder metals
- Premium resin bond for product consistency and quality
- Reinforced fibre glass for added durability and life
- 1mm Inox and thin metal cutting discs
- Inox cutting discs 100mm-230mm
- Inox grinding discs 115mm-180mm

NEW! STONE CUTTING & GRINDING DISCS



- Type 1 flat and Type 27 depressed centre masonry, concrete and stone cutting discs
- Professional grade Silicon carbide formulation for fast cutting, aggressive material removal and long life
- Premium resin bond for product consistency and quality
- Reinforced fibre glass for added durability and life
- Stone cutting discs 100mm-230mm
- Stone grinding discs 115mm-230mm

NEW! ALUMINIUM CUTTING DISCS



- Type 1 flat aluminium cutting discs
- Professional grade Aluminium oxide and Silicon carbide formulation for fast cutting and long life in aluminium
- Premium resin bond for product consistency and quality
- Reinforced fibre glass for added durability and life
- Aluminium cutting discs 115mm and 125mm

BE SEEN ONSITE WITH DeWALT



YOUR CHANCE TO WIN! A DeWALT T-SHIRT

The DeWALT 2006 JOBSITE TOUR will be continuing in your local area between August and December 2006

DeWALT are giving away 10 Williams T-shirts every working day until December 2006 - for chance to WIN simply email onsite@DeWALT.com answering the following:

- Your name and address
- Your Jobsite Name and Location
- Number of people onsite
- Occupation

Winning entries will be able to have a dedicated DeWALT demonstration vehicle brought to your sight at your conveyance

By emailing you give DeWALT the right to email with our latest Onsite promotions and information



MORE FOR YOU

DeWALT®

SUBSCRIBE & WIN!

YOUR CHANCE TO WIN A NEW DeWALT 36V ROTARY HAMMER >>>>

WIN ONE OF THESE...

NEW 36 VOLT...

...ONLINE NOW!



36 VOLT



FOR YOUR CHANCE TO WIN A NEW 36 VOLT SDS ROTARY HAMMER AND TO RECEIVE ALL THE LATEST NEWS & EVENTS FROM DeWALT SIMPLY LOG ON TO www.DEWALT.co.uk AND FOLLOW THE LINK TO THE ONLINE COMPETITION

To receive all the latest product developments, news and reviews via E-mail. Simply visit www.DEWALT.co.uk and enter your details. Your subscription will be processed and you will receive regular information and updates of new products from DeWALT, up to the minute news, competitions and much more all via E-mail straight to your desktop!

DON'T MISS OUT - ENTER ONLINE NOW!

www.DEWALT.co.uk

UK

210 Bath Road, Slough, Berkshire SL1 3YD,
Telephone: 01753 567055, Fax: 01753 572112

Republic of Ireland

Caple House, Main Street, Blackrock, Co. Dublin,
Telephone: 2781800, Fax Dublin 2781811

Your DeWALT Dealer:

The yellow and black colour scheme is used on DeWALT Power Tools and Accessories as a trade mark.

MP01069-GB