




CIRCUIT: SPST
CONTACT CONFIGURATION

SWITCH FUNCTION	
CONNECTED TERM#	
POS 1	POS 2
↑	→
OFF	ON

LEGEND

- =OFF POSITION
■ =INDICATES KEY PULL
X =INDICATES NO KEY PULL



RECOMMENDED PANEL CUTOUT

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERM. NOS. FOR REFERENCE ONLY.
- RATING: 4A @125VAC, 2A @250VAC
- CONTACT RESISTANCE: 10mILLI-OHMS
- DIELECTRIC STRENGTH: 1500 VAC-1Minute
- INSULATION RESISTANCE: 200Mega-OHMS
- MATERIALS:

HOUSING: ZINC ALLOY DIE CAST
CYLINDER: ZINC ALLOY W/CHROME PLATING
TERMINAL AND CONTACTS: SILVER PLATED

▲ KEYS (2) CODE 10001: TUBULAR STEEL, NICKEL PLATED

B	13957	DIM WAS 31.80	4/23/04	AR
A	13915	RELEASED FOR PRODUCTION	4/15/04	AR
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

TITLE

K0113A-10001

SCALE

1.5:1

DATE

4/15/04

DR

AR

DWG

K200101

REV

B