




HONEYWELL PART NUMBER
12SM604-T
PRODUCT CODE TXA8300

REV	DOCUMENT	CHANGED BY	CHECK
5	0038444	KVS 09APR08	ASD



NOTE -
▲-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ±.002 CENTERS
2-TERMINALS ARE PLATED FOR SOLDERING
3-SWITCH WILL WITHSTAND TEMPERATURE OF 250° F
4-CONTACT MATERIAL 24 K GOLD PLATED

RELEASE NO.	PR - 3561
REPLACES	X60608-SM

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH		DRAWN	VK	15 FEB 08	Honeywell			
OPERATING FORCE — — — — 3 - 5 OZ		CONTACT ARRANGEMENT SPDT			TOLERANCES UNLESS NOTED:		CHECK	RJ	15 FEB 08				
RELEASE FORCE— — — — 1 OZ MIN					NO PLACE X ±		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC			
DIFFERENTIAL TRAVEL— — — .004 MAX					ONE PLACE .X ±								
OVERTRAVEL — — — — — .003 MIN					TWO PLACE .XX ±								
					THREE PLACE .XXX ±								
					FOUR PLACE .XXXX ±								
					ANGLES ±								
					THIRD ANGLE PROJECTION					INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			
										SIZE TYPE DRAWING NAME REV B I 12SM604-T 5			
										SCALE - WEIGHT .006 LB MAX SHEET 1 OF 1			