

Feed-Through Double Level

Altech double level terminals are the answer to high wiring density problems posed by certain unavoidable wiring arrangements. Double level terminals have the following advantages:

- Double wiring density available without extension of mounting rails.
- Interconnection/shorting can be done at both levels.
- Marking/identification by marking tags possible at both levels.

CDL4U(I.S) internally shorted double level terminals are useful for distribution applications by using shorting links at lower levels.




Terminal Width	
Height x Length	
Stripping Length	
Insulation Material	
Type of Connection	
Approvals	
Wire Range	
Voltage Rating	
Current Rating	
Torque	
Other Approvals	

Terminal Block

End Plate	
Separator Plate	
DIN Rail	
for ordering information	
refer to page 72	
End Stop	
for ordering information	
refer to page 74	

Internal Jumper		2 pole 3 pole 4 pole 10 pole
-----------------	---	---------------------------------------

Insulated Internal Jumper		2 pole 3 pole 4 pole 10 pole
---------------------------	---	---------------------------------------

Current Bars		2 pole 3 pole 4 pole 10 pole 10 pole (breakable) 10 pole
--------------	---	---

Shorting Sleeve & Screw		
External Jumper		2 pole 3 pole 4 pole 10 pole

Marking Tags		
--------------	---	--

CDL4U



6 mm
54 x 55.5 mm
9 mm
Polyamide 6.6
4 screw clamps & 2 tapped holes for cross connection
  
22-10 AWG 0.25-4 sq.mm 22-10 AWG
300V 500 V 600 V
35 A 32 A 35 A
7 lb-in 0.5 Nm 7 lb-in



Cat. No.	Std. Pk.
----------	----------

CDL4U	100
EPCDL4U	50
SPCDL4U	100
	
CA702	50
CA802	50

CA727/2	100
CA727/3	50
CA727/4	50
CA727/10	10

CA747/2	100
CA747/3	50
CA747/4	50
CA747/10	10

CA703/1	100
CA704/1	100
CA705/1	100
CA732/10	100
CA732/10-A	100
CA732/100	10

CA607/S/Q	100
CA714/2	100
CA714/3	100
CA714/4	50
CA714/10	25

MT2	100
-----	-----

CDL4U(I.S)



6 mm
54 x 55.5 mm
9 mm
Polyamide 6.6
4 screw clamps & 1 tapped hole for cross connection
  
22-10 AWG 0.25-4 sq.mm 22-10 AWG
300 V 250 V 600 V
35 A 32 A 35 A
7 lb-in 0.5 Nm 7 lb-in



Cat. No.	Std. Pk.
----------	----------

CDL4U(I.S)	100
EPCDL4U	50
SPCDL4U	100
	
CA702	50
CA802	50

CA727/2	100
CA727/3	50
CA727/4	50
CA727/10	10

CA747/2	100
CA747/3	50
CA747/4	50
CA747/10	10

CA703/1	100
CA704/1	100
CA705/1	100
CA732/10	100
CA732/10-A	100
CA732/100	10

CA607/S/Q	100
CA714/2	100
CA714/3	100
CA714/4	50
CA714/10	25

MT2	100
-----	-----

COLOR BLOCKS

(other than grey standard)

When ordering please add color suffix to Cat. No.

Example: CTS2.5U-N/R

Color	Ordering Suffix
Red	R
Blue	BU
Black	BL
Orange	O
Green	G
Yellow	Y
White	W
Beige	BG
Dark Brown	DB