

4900 - 6900

Torque wrench

Use:

- Controlled screw tightening in the most widely used range from 2 to 300 N·m
- For use in all areas of industrial manufacturing

Features:

- Adjustable torque wrench with square drive and integrated ratchet-head function
- For controlled bi-directional tightening
- 1/4" (no. 4900), 3/8" (no. 6900) and 1/2" (no. 5900) push-through square drive with ball locking device as per DIN 3120 - A 6.3 / A 10 / A 12.5, ISO 1174
- Acc. to DIN EN ISO 6789, traceable to national standards
- Lever-breaking mechanism with a castor guarantee tactile-impulse and audible actuation signals
- Actuation accuracy: +/- 3% tolerance of the scale set torque
- Robust, powder-coated steel tube construction with zinc-plated ratchet head
- Dual scale N·m and lbf·ft underneath a window with a magnifying-glass effect
- N·m graduation of 0.1, 2.5, 5 or 10 N·m
- Black plastic handgrip with slip-resistant grained surface
- 5 models in the range from 2 to 300 N·m

Scope of delivery:

- Torque wrench with test certificate acc. to DIN EN ISO 6789
- Operating instructions
- Delivered in transparent plastic box with a practical suspension mounting

