



CKT. SIZE	DIM. A		DIM. B REF.	
	(MM)	INCH	(MM)	INCH
4	(5.08)	0.200	(2.54)	0.100
6	(7.62)	0.300	(5.08)	0.200
8	(10.16)	0.400	(7.62)	0.300
10	(12.70)	0.500	(10.16)	0.400
12	(15.24)	0.600	(12.70)	0.500
14	(17.78)	0.700	(15.24)	0.600
16	(20.32)	0.800	(17.78)	0.700
18	(22.86)	0.900	(20.32)	0.800
20	(25.40)	1.000	(22.86)	0.900
22	(27.94)	1.100	(25.40)	1.000
24	(30.48)	1.200	(27.94)	1.100
26	(33.02)	1.300	(30.48)	1.200
28	(35.56)	1.400	(33.02)	1.300
30	(38.10)	1.500	(35.56)	1.400
32	(40.64)	1.600	(38.10)	1.500
34	(43.18)	1.700	(40.64)	1.600
36	(45.72)	1.800	(43.18)	1.700
38	(48.26)	1.900	(45.72)	1.800
40	(50.80)	2.000	(48.26)	1.900
42	(53.34)	2.100	(50.80)	2.000
44	(55.88)	2.200	(53.34)	2.100
46	(58.42)	2.300	(55.88)	2.200
48	(60.96)	2.400	(58.42)	2.300
50	(63.50)	2.500	(60.96)	2.400
52	(66.04)	2.600	(63.50)	2.500
54	(68.58)	2.700	(66.04)	2.600
56	(71.12)	2.800	(68.58)	2.700
58	(73.66)	2.900	(71.12)	2.800
60	(76.20)	3.000	(73.66)	2.900
62	(78.74)	3.100	(76.20)	3.000
64	(81.28)	3.200	(78.74)	3.100
66	(83.82)	3.300	(81.28)	3.200
68	(86.36)	3.400	(83.82)	3.300
70	(88.90)	3.500	(86.36)	3.400
72	(91.44)	3.600	(88.90)	3.500
74	(93.98)	3.700	(91.44)	3.600
76	(96.52)	3.800	(93.98)	3.700
78	(99.06)	3.900	(96.52)	3.800
80	(101.60)	4.000	(99.06)	3.900
82	(104.14)	4.100	(101.60)	4.000
84	(106.68)	4.200	(104.14)	4.100
86	(109.22)	4.300	(106.68)	4.200
88	(111.76)	4.400	(109.22)	4.300
90	(114.30)	4.500	(111.76)	4.400
92	(116.84)	4.600	(114.30)	4.500
94	(119.38)	4.700	(116.84)	4.600
96	(121.92)	4.800	(119.38)	4.700
98	(124.46)	4.900	(121.92)	4.800
100	(127.00)	5.000	(124.46)	4.900

NOTES:

1. MATERIAL:
PIN: COPPER ALLOY
WAFER: GLASS FILLED LCP (LIQUID CRYSTAL POLYMER, UL 94V-0, COLOR: BLACK.
2. FINISH:

TIN = (0.00380)/.000150 MINIMUM TIN PLATE
OVER (0.00127)/.000050 MINIMUM NICKEL PLATE.
15 GOLD = (0.00038)/.000015 MINIMUM GOLD PLATE IN SELECT AREA,
(0.00190)/.000075 MINIMUM TIN PLATE IN SELECT AREA,
OVER (0.00127)/.000050 MINIMUM NICKEL PLATE OVERALL.
30 GOLD = (0.00076)/.000030 MINIMUM GOLD PLATE IN SELECT AREA,
(0.00190)/.000075 MINIMUM TIN PLATE IN SELECT AREA,
OVER (0.00127)/.000050 MINIMUM NICKEL PLATE OVERALL.
GT15 = (0.00038)/.000015 MINIMUM GOLD PLATE IN SELECT AREA,
(0.00254)/.000100 MINIMUM TIN PLATE IN SELECT AREA,
OVER (0.00127)/.000050 MINIMUM NICKEL PLATE OVERALL.

* THE PRIMARY SHIPPING CARTON WILL BE LABELED "COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC". CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH LEAD PLATING.



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE		CURRENT REV DESC: MIGRATED TO ECTR				molex			
MM/IN		4:1									
GENERAL TOLERANCES (UNLESS SPECIFIED)											
	MM	INCH	EC NO: 604937 DRWN: GSHARMA 2018/09/21 CHK'D: ISHWARG 2018/10/04 APPR: ISHWARG 2018/10/04				SALES ASSY-HIGH TEMP. DUAL ROW WAFER W/BREAK- OFF OPT. .025 SQ PINS				
4 PLACES	±	±									
3 PLACES	±	± 0.005									
2 PLACES	± 0.13	± 0.01									
1 PLACE	± 0.25	±									
0 PLACES	±	±									
ANGULAR TOL ± 0.5 °			INITIAL REVISION: DRWN: SMR 04/19/1993 APPR: SMR 04/19/1993				PRODUCT CUSTOMER DRAWING				
							DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
							SDA-70280-0001-4000		PSD	001	H
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
				C-SIZE	70280	SEE TABLE		GENERAL MARKET		1 OF 9	

12		11		10		9		8		7		6		5		4		3		2		1	
ENGINEERING NUMBER A-70280-		RELEASE FOR MANUFACTURE						E REF.		J REF.		C (0.25) ±.010						MATING END PLATING		P.C BOARD END PLATING		FOR PACKAGING INFORMATION, SEE NOTE 4, SHEET 1 (UNLESS OTHERWISE SPECIFIED BELOW)	
																		TYPE	D MEAS.		TYPE		
-0001/-0040		R.F.M.						(2.72) .107		(11.10) .437		(6.10) .240						TIN		(2.54) .100			
-0001/-0080		R.F.M.						(2.72) .107		(11.10) .437		(6.10) .240						15 GOLD		(2.54) .100			
-0081/-0120		R.F.M.						(2.72) .107		(11.10) .437		(6.10) .240						30 GOLD		(2.54) .100			
-0121/-0160		R.F.M.						(2.79) .110		(13.21) .520		(8.13) .320						TIN		(4.57) .180			
-0161/-0200		R.F.M.						(2.79) .110		(13.21) .520		(8.13) .320						15 GOLD		(4.57) .180			
-0201/-0240		R.F.M.						(2.79) .110		(13.21) .520		(8.13) .320						30 GOLD		(4.57) .180			
-0241/-0280		R.F.M.						(3.94) .155		(12.32) .485		(6.10) .240						30 GOLD		(2.54) .100			
CKTS	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	CKTS
	N.A.	AX-70280-0001	N.A.	AX-70280-0041	N.A.	AX-70280-0081	N.A.	AX-70280-0121	N.A.	AX-70280-0161	N.A.	AX-70280-0201	N.A.	AX-70280-0241									
4	010-89-7041	A-70280-0002	010-89-7042	A-70280-0042	010-89-7040	A-70280-0082	010-97-7045	A-70280-0122	010-97-7046	A-70280-0162	010-89-7043	A-70280-0202	010-87-9045	A-70280-0242	4								
6	010-89-7061	A-70280-0003	010-89-7062	A-70280-0043	010-89-7060	A-70280-0083	010-97-7065	A-70280-0123	010-97-7066	A-70280-0163	010-89-7063	A-70280-0203	010-87-9065	A-70280-0243	6								
8	010-89-7081	A-70280-0004	010-89-7082	A-70280-0044	010-89-7080	A-70280-0084	010-97-7085	A-70280-0124	010-97-7086	A-70280-0164	010-89-7083	A-70280-0204	010-87-9085	A-70280-0244	8								
10	010-89-7101	A-70280-0005	010-89-7102	A-70280-0045	010-89-7100	A-70280-0085	010-97-7105	A-70280-0125	010-97-7106	A-70280-0165	010-89-7103	A-70280-0205	010-87-9105	A-70280-0245	10								
12	010-89-7121	A-70280-0006	010-89-7122	A-70280-0046	010-89-7120	A-70280-0086	010-97-7125	A-70280-0126	010-97-7126	A-70280-0166	010-89-7123	A-70280-0206	010-87-9125	A-70280-0246	12								
14	010-89-7141	A-70280-0007	010-89-7142	A-70280-0047	010-89-7140	A-70280-0087	010-97-7145	A-70280-0127	010-97-7146	A-70280-0167	010-89-7143	A-70280-0207	010-87-9145	A-70280-0247	14								
16	010-89-7161	A-70280-0008	010-89-7162	A-70280-0048	010-89-7160	A-70280-0088	010-97-7165	A-70280-0128	010-97-7166	A-70280-0168	010-89-7163	A-70280-0208	010-87-9165	A-70280-0248	16								
18	010-89-7181	A-70280-0009	010-89-7182	A-70280-0049	010-89-7180	A-70280-0089	010-97-7185	A-70280-0129	010-97-7186	A-70280-0169	010-89-7183	A-70280-0209	010-87-9185	A-70280-0249	18								
20	010-89-7201	A-70280-0010	010-89-7202	A-70280-0050	010-89-7200	A-70280-0090	010-97-7205	A-70280-0130	010-97-7206	A-70280-0170	010-89-7203	A-70280-0210	010-87-9205	A-70280-0250	20								
22	010-89-7221	A-70280-0011	010-89-7222	A-70280-0051	010-89-7220	A-70280-0091	010-97-7225	A-70280-0131	010-97-7226	A-70280-0171	010-89-7223	A-70280-0211	010-87-9225	A-70280-0251	22								
24	010-89-7241	A-70280-0012	010-89-7242	A-70280-0052	010-89-7240	A-70280-0092	010-97-7245	A-70280-0132	010-97-7246	A-70280-0172	010-89-7243	A-70280-0212	010-87-9245	A-70280-0252	24								
26	010-89-7261	A-70280-0013	010-89-7262	A-70280-0053	010-89-7260	A-70280-0093	010-97-7265	A-70280-0133	010-97-7266	A-70280-0173	010-89-7263	A-70280-0213	010-87-9265	A-70280-0253	26								
28	010-89-7281	A-70280-0014	010-89-7282	A-70280-0054	010-89-7280	A-70280-0094	010-97-7285	A-70280-0134	010-97-7286	A-70280-0174	010-89-7283	A-70280-0214	010-87-9285	A-70280-0254	28								
30	010-89-7301	A-70280-0015	010-89-7302	A-70280-0055	010-89-7300	A-70280-0095	010-97-7305	A-70280-0135	010-97-7306	A-70280-0175	010-89-7303	A-70280-0215	010-87-9305	A-70280-0255	30								
32	010-89-7321	A-70280-0016	010-89-7322	A-70280-0056	010-89-7320	A-70280-0096	010-97-7325	A-70280-0136	010-97-7326	A-70280-0176	010-89-7323	A-70280-0216	010-87-9325	A-70280-0256	32								
34	010-89-7341	A-70280-0017	010-89-7342	A-70280-0057	010-89-7340	A-70280-0097	010-97-7345	A-70280-0137	010-97-7346	A-70280-0177	010-89-7343	A-70280-0217	010-87-9345	A-70280-0257	34								
36	010-89-7361	A-70280-0018	010-89-7362	A-70280-0058	010-89-7360	A-70280-0098	010-97-7365	A-70280-0138	010-97-7366	A-70280-0178	010-89-7363	A-70280-0218	010-87-9365	A-70280-0258	36								
38	010-89-7381	A-70280-0019	010-89-7382	A-70280-0059	010-89-7380	A-70280-0099	010-97-7385	A-70280-0139	010-97-7386	A-70280-0179	010-89-7383	A-70280-0219	010-87-9385	A-70280-0259	38								
40	010-89-7401	A-70280-0020	010-89-7402	A-70280-0060	010-89-7400	A-70280-0100	010-97-7405	A-70280-0140	010-97-7406	A-70280-0180	010-89-7403	A-70280-0220	010-87-9405	A-70280-0260	40								
42	010-89-7421	A-70280-0021	010-89-7422	A-70280-0061	010-89-7420	A-70280-0101	010-97-7425	A-70280-0141	010-97-7426	A-70280-0181	010-89-7423	A-70280-0221	010-87-9425	A-70280-0261	42								
44	010-89-7441	A-70280-0022	010-89-7442	A-70280-0062	010-89-7440	A-70280-0102	010-97-7445	A-70280-0142	010-97-7446	A-70280-0182	010-89-7443	A-70280-0222	010-87-9445	A-70280-0262	44								
46	010-89-7461	A-70280-0023	010-89-7462	A-70280-0063	010-89-7460	A-70280-0103	010-97-7465	A-70280-0143	010-97-7466	A-70280-0183	010-89-7463	A-70280-0223	010-87-9465	A-70280-0263	46								
48	010-89-7481	A-70280-0024	010-89-7482	A-70280-0064	010-89-7480	A-70280-0104	010-97-7485	A-70280-0144	010-97-7486	A-70280-0184													

12		11		10		9		8		7		6		5		4		3		2		1																										
ENGINEERING NUMBER A-70280-		RELEASE FOR MANUFACTURE						E REF.		J REF.		C (0.25) ±.010						MATING END PLATING		P.C BOARD END PLATING			FOR PACKAGING INFORMATION, SEE NOTE 4, SHEET 1 (UNLESS OTHERWISE SPECIFIED BELOW)																									
																		TYPE		D MEAS.					TYPE		F MEAS.																					
-0281/-0320		R.F.M.						(2.92) .115		(12.83) .505		(7.62) .300						TIN		(4.57) .180				TIN		(1.27) .050				PK-70873-0090																		
-0361/-0399		R.F.M.						(3.68) .145		(17.02) .670		(11.05) .435						TIN		(6.46) .254				TIN		(1.23) .048				PK-70873-0276																		
-0549/-0588		R.F.M.						(2.72) .107		(11.10) .437		(6.10) .240						TIN		(2.54) .100				TIN		(1.27) .050				PK-70873-0090																		
-0589/-0628		R.F.M.						(4.45) .175		(12.83) .505		(6.10) .240						TIN		(2.54) .100				TIN		(1.27) .050																						
CKTS	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	CKTS																			
	N.A	AX-70280-0281									N/A	A-70280-0549	N/A	A-70280-0589																																		
4	010-97-7047	A-70280-0282				70280-0361	A-70280-0361				70280-0550	A-70280-0550	70280-0590	A-70280-0590															4																			
6	010-97-7067	A-70280-0283				70280-0362	A-70280-0362				70280-0551	A-70280-0551	70280-0591	A-70280-0591															6																			
8	010-97-7087	A-70280-0284				70280-0363	A-70280-0363				70280-0552	A-70280-0552	70280-0592	A-70280-0592															8																			
10	010-97-7107	A-70280-0285				70280-0364	A-70280-0364				70280-0553	A-70280-0553	70280-0593	A-70280-0593															10																			
12	010-97-7127	A-70280-0286				70280-0365	A-70280-0365				70280-0554	A-70280-0554	70280-0594	A-70280-0594															12																			
14	010-97-7147	A-70280-0287				70280-0366	A-70280-0366				70280-0555	A-70280-0555	70280-0595	A-70280-0595															14																			
16	010-97-7167	A-70280-0288				70280-0367	A-70280-0367				70280-0556	A-70280-0556	70280-0596	A-70280-0596															16																			
18	010-97-7187	A-70280-0289				70280-0368	A-70280-0368				70280-0557	A-70280-0557	70280-0597	A-70280-0597															18																			
20	010-97-7207	A-70280-0290				70280-0369	A-70280-0369				70280-0558	A-70280-0558	70280-0598	A-70280-0598															20																			
22	010-97-7227	A-70280-0291				70280-0370	A-70280-0370				70280-0559	A-70280-0559	70280-0599	A-70280-0599															22																			
24	010-97-7247	A-70280-0292				70280-0371	A-70280-0371				70280-0560	A-70280-0560	70280-0600	A-70280-0600															24																			
26	010-97-7267	A-70280-0293				70280-0372	A-70280-0372				70280-0561	A-70280-0561	70280-0601	A-70280-0601															26																			
28	010-97-7287	A-70280-0294				70280-0373	A-70280-0373				70280-0562	A-70280-0562	70280-0602	A-70280-0602															28																			
30	010-97-7307	A-70280-0295				70280-0374	A-70280-0374				70280-0563	A-70280-0563	70280-0603	A-70280-0603															30																			
32	010-97-7327	A-70280-0296				70280-0375	A-70280-0375				70280-0564	A-70280-0564	70280-0604	A-70280-0604															32																			
34	010-97-7347	A-70280-0297				70280-0376	A-70280-0376				70280-0565	A-70280-0565	70280-0605	A-70280-0605															34																			
36	010-97-7367	A-70280-0298				70280-0377	A-70280-0377				70280-0566	A-70280-0566	70280-0606	A-70280-0606															36																			
38	010-97-7387	A-70280-0299				70280-0378	A-70280-0378				70280-0567	A-70280-0567	70280-0607	A-70280-0607															38																			
40	010-97-7407	A-70280-0300				70280-0379	A-70280-0379				70280-0568	A-70280-0568	70280-0608	A-70280-0608															40																			
42	010-97-7427	A-70280-0301				70280-0380	A-70280-0380				70280-0569	A-70280-0569	70280-0609	A-70280-0609															42																			
44	010-97-7447	A-70280-0302				70280-0381	A-70280-0381				70280-0570	A-70280-0570	70280-0610	A-70280-0610															44																			
46	010-97-7467	A-70280-0303				70280-0382	A-70280-0382				70280-0571	A-70280-0571	70280-0611	A-70280-0611															46																			
48	010-97-7487	A-70280-0304				70280-0383	A-70280-0383				70280-0572	A-70280-0572	70280-0612	A-70280-0612															48																			
50	010-97-7507	A-70280-0305				70280-0384	A-70280-0384				70280-0573	A-70280-0573	70280-0613	A-70280-0613															50																			
52	010-97-7527	A-70280-0306				70280-0385	A-70280-0385				70280-0574	A-70280-0574	70280-0614	A-70280-0614															52																			
54	010-97-7547	A-70280-0307				70280-0386	A-70280-0386				70280-0575	A-70280-0575	70280-0615	A-70280-0615															54																			
56	010-97-7567	A-70280-0308				70280-0387	A-70280-0387				70280-0576	A-70280-0576	70280-0616	A-70280-0616															56																			
58	010-97-7587	A-70280-0309				70280-0388	A-70280-0388				70280-0577	A-70280-0577	70280-0617	A-70280-0617															58																			
60	010-97-7607	A-70280-0310				70280-0389	A-70280-0389				70280-0578	A-70280-0578	70280-0618	A-70280-0618															60																			
62	010-97-7627	A-70280-0311				70280-0390	A-70280-0390				70280-0579	A-70280-0579	70280-0619	A-70280-0619															62																			
64	010-97-7647	A-70280-0312				70280-0391	A-70280-0391				70280-0580	A-70280-0580	70280-0620	A-70280-0620															64																			
66	010-97-7667	A-70280-0313				70280-0392	A-70280-0392				70280-0581	A-70280-0581	70280-0621	A-70280-0621															66																			
68	010-97-7687	A-70280-0314				70280-0393	A-70280-0393				70280-0582	A-70280-0582	70280-0622	A-70280-0622															68																			
70	010-97-7707	A-70280-0315				70280-0394	A-70280-0394				70280-0583	A-70280-0583	70280-0623	A-70280-0623															70																			
72	010-97-7727	A-70280-0316				70280-0395	A-70280-0395				70280-0584	A-70280-0584	70280-0624	A-70280-0624															72																			
74	010-97-7747	A-70280-0317				70280-0396	A-70280-0396				70280-0585	A-70280-0585	70280-0625	A-70280-0625															74																			
76	010-97-7767	A-70280-0318				70280-0397	A-70280-0397				70280-0586	A-70280-0586	70280-0626	A-70280-0626															76																			
78	010-97-7787	A-70280-0319				70280-0398	A-70280-0398				70280-0587	A-70280-0587	70280-0627	A-70280-0627															78																			
80	010-97-7807	A-70280-0320				70280-0399	A-70280-0399				70280-0588	A-70280-0588	70280-0628	A-70280-0628															80																			
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION DIMENSION UNITS SCALE MM/IN 1:1 GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>MM</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>±</td><td>±</td></tr><tr><td>3 PLACES</td><td>±</td><td>± 0.005</td></tr><tr><td>2 PLACES</td><td>± 0.13</td><td>± 0.01</td></tr><tr><td>1 PLACE</td><td>± 0.25</td><td>±</td></tr><tr><td>0 PLACES</td><td>±</td><td>±</td></tr><tr><td>ANGULAR TOL</td><td>± 0.5 °</td><td></td></tr></table> DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS THIRD ANGLE PROJECTION DRAWING C-SIZE SERIES 70280 CURRENT REV DESC: MIGRATED TO ECTR EC NO: 604937 DRWN: GSHARMA 2018/09/21 CHK'D: ISHWARG 2018/10/04 APPR: ISHWARG 2018/10/04 INITIAL REVISION: DRWN: SMR 04/19/1993 APPR: SMR 04/19/1993 SALES ASSY-HIGH TEMP. DUAL ROW WAFER W/BREAK- OFF OPT. .025 SQ PINS PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER SDA-70280-0001-4000 DOC TYPE PSD DOC PART 001 REVISION H MATERIAL NUMBER SEE TABLE CUSTOMER GENERAL MARKET SHEET NUMBER 3 OF 9																													MM	INCH	4 PLACES	±	±	3 PLACES	±	± 0.005	2 PLACES	± 0.13	± 0.01	1 PLACE	± 0.25	±	0 PLACES	±	±	ANGULAR TOL	± 0.5 °	
	MM	INCH																																														
4 PLACES	±	±																																														
3 PLACES	±	± 0.005																																														
2 PLACES	± 0.13	± 0.01																																														
1 PLACE	± 0.25	±																																														
0 PLACES	±	±																																														
ANGULAR TOL	± 0.5 °																																															
DOCUMENT STATUS	P1	RELEASE DATE	2018/10/04	09:58:28																																												
12		11		10		9		8		7		6		5		4		3		2		1																										

12		11		10		9		8		7		6		5		4		3		2		1		
ENGINEERING NUMBER A-70280-		RELEASE FOR MANUFACTURE						E REF.		J REF.		C (0.25) ±.010						MATING END PLATING		P.C BOARD END PLATING			FOR PACKAGING INFORMATION, SEE NOTE 4, SHEET 1 (UNLESS OTHERWISE SPECIFIED BELOW)	
																		TYPE	D MEAS.		TYPE	F MEAS.		
-0629/-0668		R.F.M.						(4.45) .175		(12.83) .505		(6.10) .240						15 GOLD	(2.54) .100		TIN	(1.27) .050		
-0669/-0708		R.F.M.						(4.45) .175		(12.83) .505		(6.10) .240						30 GOLD	(2.54) .100		TIN	(1.27) .050		
-0709/-0748		R.F.M.						(4.70) .185		(15.11) .595		(8.13) .320						TIN	(4.57) .180		TIN	(1.27) .050		
-0749/-0788		R.F.M.						(4.70) .185		(15.11) .595		(8.13) .320						15 GOLD	(4.57) .180		TIN	(1.27) .050		
-0789/-0828		R.F.M.						(4.70) .185		(15.11) .595		(8.13) .320						30 GOLD	(4.57) .180		TIN	(1.27) .050		
-0829/-0868		R.F.M.						(5.08) .200		(13.21) .520		(5.84) .230						TIN	(2.54) .100		TIN	(1.27) .050		
CKTS	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	CKTS
	N/A	A-70280-0629	N/A	A-70280-0669	N/A	A-70280-0709	N/A	A-70280-0749	N/A	A-70280-0789	N/A	A-70280-0829												
4	70280-0630	A-70280-0630	70280-0670	A-70280-0670	70280-0710	A-70280-0710	70280-0750	A-70280-0750	70280-0790	A-70280-0790	70280-0830	A-70280-0830												4
6	70280-0631	A-70280-0631	70280-0671	A-70280-0671	70280-0711	A-70280-0711	70280-0751	A-70280-0751	70280-0791	A-70280-0791	70280-0831	A-70280-0831												6
8	70280-0632	A-70280-0632	70280-0672	A-70280-0672	70280-0712	A-70280-0712	70280-0752	A-70280-0752	70280-0792	A-70280-0792	70280-0832	A-70280-0832												8
10	70280-0633	A-70280-0633	70280-0673	A-70280-0673	70280-0713	A-70280-0713	70280-0753	A-70280-0753	70280-0793	A-70280-0793	70280-0833	A-70280-0833												10
12	70280-0634	A-70280-0634	70280-0674	A-70280-0674	70280-0714	A-70280-0714	70280-0754	A-70280-0754	70280-0794	A-70280-0794	70280-0834	A-70280-0834												12
14	70280-0635	A-70280-0635	70280-0675	A-70280-0675	70280-0715	A-70280-0715	70280-0755	A-70280-0755	70280-0795	A-70280-0795	70280-0835	A-70280-0835												14
16	70280-0636	A-70280-0636	70280-0676	A-70280-0676	70280-0716	A-70280-0716	70280-0756	A-70280-0756	70280-0796	A-70280-0796	70280-0836	A-70280-0836												16
18	70280-0637	A-70280-0637	70280-0677	A-70280-0677	70280-0717	A-70280-0717	70280-0757	A-70280-0757	70280-0797	A-70280-0797	70280-0837	A-70280-0837												18
20	70280-0638	A-70280-0638	70280-0678	A-70280-0678	70280-0718	A-70280-0718	70280-0758	A-70280-0758	70280-0798	A-70280-0798	70280-0838	A-70280-0838												20
22	70280-0639	A-70280-0639	70280-0679	A-70280-0679	70280-0719	A-70280-0719	70280-0759	A-70280-0759	70280-0799	A-70280-0799	70280-0839	A-70280-0839												22
24	70280-0640	A-70280-0640	70280-0680	A-70280-0680	70280-0720	A-70280-0720	70280-0760	A-70280-0760	70280-0800	A-70280-0800	70280-0840	A-70280-0840												24
26	70280-0641	A-70280-0641	70280-0681	A-70280-0681	70280-0721	A-70280-0721	70280-0761	A-70280-0761	70280-0801	A-70280-0801	70280-0841	A-70280-0841												26
28	70280-0642	A-70280-0642	70280-0682	A-70280-0682	70280-0722	A-70280-0722	70280-0762	A-70280-0762	70280-0802	A-70280-0802	70280-0842	A-70280-0842												28
30	70280-0643	A-70280-0643	70280-0683	A-70280-0683	70280-0723	A-70280-0723	70280-0763	A-70280-0763	70280-0803	A-70280-0803	70280-0843	A-70280-0843												30
32	70280-0644	A-70280-0644	70280-0684	A-70280-0684	70280-0724	A-70280-0724	70280-0764	A-70280-0764	70280-0804	A-70280-0804	70280-0844	A-70280-0844												32
34	70280-0645	A-70280-0645	70280-0685	A-70280-0685	70280-0725	A-70280-0725	70280-0765	A-70280-0765	70280-0805	A-70280-0805	70280-0845	A-70280-0845												34
36	70280-0646	A-70280-0646	70280-0686	A-70280-0686	70280-0726	A-70280-0726	70280-0766	A-70280-0766	70280-0806	A-70280-0806	70280-0846	A-70280-0846												36
38	70280-0647	A-70280-0647	70280-0687	A-70280-0687	70280-0727	A-70280-0727	70280-0767	A-70280-0767	70280-0807	A-70280-0807	70280-0847	A-70280-0847												38
40	70280-0648	A-70280-0648	70280-0688	A-70280-0688	70280-0728	A-70280-0728	70280-0768	A-70280-0768	70280-0808	A-70280-0808	70280-0848	A-70280-0848												40
42	70280-0649	A-70280-0649	70280-0689	A-70280-0689	70280-0729	A-70280-0729	70280-0769	A-70280-0769	70280-0809	A-70280-0809	70280-0849	A-70280-0849												42
44	70280-0650	A-70280-0650	70280-0690	A-70280-0690	70280-0730	A-70280-0730	70280-0770	A-70280-0770	70280-0810	A-70280-0810	70280-0850	A-70280-0850												44
46	70280-0651	A-70280-0651	70280-0691	A-70280-0691	70280-0731	A-70280-0731	70280-0771	A-70280-0771	70280-0811	A-70280-0811	70280-0851	A-70280-0851												46
48	70280-0652	A-70280-0652	70280-0692	A-70280-0692	70280-0732	A-70280-0732	70280-0772	A-70280-0772	70280-0812	A-70280-0812	70280-0852	A-70280-0852												48
50	70280-0653	A-70280-0653	70280-0693	A-70280-0693	70280-0733	A-70280-0733	70280-0773	A-70280-0773	70280-0813	A-70280-0813	70280-0853	A-70280-0853												50
52	70280-0654	A-70280-0654	70280-0694	A-70280-0694	70280-0734	A-70280-0734	70280-0774	A-70280-0774	70280-0814	A-70280-0814	70280-0854	A-70280-0854												

[illegible]

[illegible]

		13		12		11		10		9		8		7		6		5		4		3		2		1			
J	ENGINEERING NUMBER A-70280-		RELEASE FOR MANUFACTURE						E REF.		J REF.		C (0.25) ±.010				CONNECTOR END PLATING		P.C. BOARD END PLATING		FOR PACKAGING INFORMATION, SEE NOTE 4, SHEET 1 (UNLESS OTHERWISE SPECIFIED BELOW)								
																	TYPE		D MEAS.		TYPE		F MEAS.						
	-0001/-0040		R.F.M.						(2.72) .107		(11.10) .437		(6.10) .240				TIN		(2.54) .100		TIN		(1.27) .050						
	-0041/-0080		R.F.M.						(2.72) .107		(11.10) .437		(6.10) .240				15 GOLD		(2.54) .100		TIN		(1.27) .050						
I	-0081/-0120		R.F.M.						(2.72) .107		(11.10) .437		(6.10) .240				30 GOLD		(2.54) .100		TIN		(1.27) .050						
	-0121/-0160		R.F.M.						(2.79) .110		(13.21) .520		(8.13) .320				TIN		(4.57) .180		TIN		(1.27) .050						
H	-0161/-0200		R.F.M.						(2.79) .110		(13.21) .520		(8.13) .320				15 GOLD		(4.57) .180		TIN		(1.27) .050						
	-0201/-0240		R.F.M.						(2.79) .110		(13.21) .520		(8.13) .320				30 GOLD		(4.57) .180		TIN		(1.27) .050						
	-0241/-0280		R.F.M.						(3.94) .155		(12.32) .485		(6.10) .240				30 GOLD		(2.54) .100		TIN		(1.27) .050						
CKTS		EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	EDP NUMBER	ENG NUMBER	CKTS			
		N.A.	AX-70280-0001	N.A.	AX-70280-0041	N.A.	AX-70280-0081	N.A.	AX-70280-0121	N/A	AX-70280-0161	N/A	AX-70280-0201	N/A	AX-70280-0241														
G	04	010-89-7041	A-70280-0002	010-89-7042	A-70280-0042	010-89-7040	A-70280-0082	010-97-7045	A-70280-0122	010-97-7046	A-70280-0162	010-89-7043	A-70280-0202	010-87-9045	A-70280-0242	04													
	06	010-89-7061	A-70280-0003	010-89-7062	A-70280-0043	010-89-7060	A-70280-0083	010-97-7065	A-70280-0123	010-97-7066	A-70280-0163	010-89-7063	A-70280-0203	010-87-9065	A-70280-0243	06													
	08	010-89-7081	A-70280-0004	010-89-7082	A-70280-0044	010-89-7080	A-70280-0084	010-97-7085	A-70280-0124	010-97-7086	A-70280-0164	010-89-7083	A-70280-0204	010-87-9085	A-70280-0244	08													
	10	010-89-7101	A-70280-0005	010-89-7102	A-70280-0045	010-89-7100	A-70280-0085	010-97-7105	A-70280-0125	010-97-7106	A-70280-0165	010-89-7103	A-70280-0205	010-87-9105	A-70280-0245	10													
	12	010-89-7121	A-70280-0006	010-89-7122	A-70280-0046	010-89-7120	A-70280-0086	010-97-7125	A-70280-0126	010-97-7126	A-70280-0166	010-89-7123	A-70280-0206	010-87-9125	A-70280-0246	12													
	14	010-89-7141	A-70280-0007	010-89-7142	A-70280-0047	010-89-7140	A-70280-0087	010-97-7145	A-70280-0127	010-97-7146	A-70280-0167	010-89-7143	A-70280-0207	010-87-9145	A-70280-0247	14													
	16	010-89-7161	A-70280-0008	010-89-7162	A-70280-0048	010-89-7160	A-70280-0088	010-97-7165	A-70280-0128	010-97-7166	A-70280-0168	010-89-7163	A-70280-0208	010-87-9165	A-70280-0248	16													
	18	010-89-7181	A-70280-0009	010-89-7182	A-70280-0049	010-89-7180	A-70280-0089	010-97-7185	A-70280-0129	010-97-7186	A-70280-0169	010-89-7183	A-70280-0209	010-87-9185	A-70280-0249	18													
F	20	010-89-7201	A-70280-0010	010-89-7202	A-70280-0050	010-89-7200	A-70280-0090	010-97-7205	A-70280-0130	010-97-7206	A-70280-0170	010-89-7203	A-70280-0210	010-87-9205	A-70280-0250	20													
	22	010-89-7221	A-70280-0011	010-89-7222	A-70280-0051	010-89-7220	A-70280-0091	010-97-7225	A-70280-0131	010-97-7226	A-70280-0171	010-89-7223	A-70280-0211	010-87-9225	A-70280-0251	22													
	24	010-89-7241	A-70280-0012	010-89-7242	A-70280-0052	010-89-7240	A-70280-0092	010-97-7245	A-70280-0132	010-97-7246	A-70280-0172	010-89-7243	A-70280-0212	010-87-9245	A-70280-0252	24													
	26	010-89-7261	A-70280-0013	010-89-7262	A-70280-0053	010-89-7260	A-70280-0093	010-97-7265	A-70280-0133	010-97-7266	A-70280-0173	010-89-7263	A-70280-0213	010-87-9265	A-70280-0253	26													
	28	010-89-7281	A-70280-0014	010-89-7282	A-70280-0054	010-89-7280	A-70280-0094	010-97-7285	A-70280-0134	010-97-7286	A-70280-0174	010-89-7283	A-70280-0214	010-87-9285	A-70280-0254	28													
	30	010-89-7301	A-70280-0015	010-89-7302	A-70280-0055	010-89-7300	A-70280-0095	010-97-7305	A-70280-0135	010-97-7306	A-70280-0175	010-89-7303	A-70280-0215	010-87-9305	A-70280-0255	30													
	32	010-89-7321	A-70280-0016	010-89-7322	A-70280-0056	010-89-7320	A-70280-0096	010-97-7325	A-70280-0136	010-97-7326	A-70280-0176	010-89-7323	A-70280-0216	010-87-9325	A-70280-0256	32													
	34	010-89-7341	A-70280-0017	010-89-7342	A-70280-0057	010-89-7340	A-70280-0097	010-97-7345	A-70280-0137	010-97-7346	A-70280-0177	010-89-7343	A-70280-0217	010-87-9345	A-70280-0257	34													
E	36	010-89-7361	A-70280-0018	010-89-7362	A-70280-0058	010-89-7360	A-70280-0098	010-97-7365	A-70280-0138	010-97-7366	A-70280-0178	010-89-7363	A-70280-0218	010-87-9365	A-70280-0258	36													
	38	010-89-7381	A-70280-0019	010-89-7382	A-70280-0059	010-89-7380	A-70280-0099	010-97-7385	A-70280-0139	010-97-7386	A-70280-0179	010-89-7383	A-70280-0219	010-87-9385	A-70280-0259	38													
	40	010-89-7401	A-70280-0020	010-89-7402	A-70280-0060	010-89-7400	A-70280-0100	010-97-7405	A-70280-0140	010-97-7406	A-70280-0180	010-89-7403	A-70280-0220	010-87-9405	A-70280-0260	40													
	42	010-89-7421	A-70280-0021	010-89-7422	A-70280-0061	010-89-7420	A-70280-0101	010-97-7425	A-70280-0141	010-97-7426	A-70280-0181	010-89-7423	A-70280-0221	010-87-9425	A-70280-0261	42													
	44	010-89-7441	A-70280-0022	010-89-7442	A-70280-0062	010-89-7440	A-70280-0102	010-97-7445	A-70280-0142	010-97-7446	A-70280-0182	010-89-7443	A-70280-0222	010-87-9445	A-70280-0262	44													
	46	010-89-7461	A-70280-0023	010-89-7462	A-70280-0063	010-89-7460	A-70280-0103	010-97-7465	A-70280-0143	010-97-7466	A-70280-0183	010-89-7463	A-70280-0223	010-87-9465	A-70280-0263	46													
	48	010-89-7481	A-70280-0024	010-89-7482	A-70280-0064	010-89-7480	A-70280-0104	010-97-7485	A-70280-0144	010-97-7486	A-70280-0184	010-89-7483	A-70280-0224	010-87-9485	A-70280-0264	48													
	50	010-89-7501	A-70280-0025	010-89-7502	A-70280-0065	010-89-7500	A-70280-0105	010-97-7505	A-70280-0145	010-97-7506	A-70280-0185	010-89-7503	A-70280-0225	010-87-9505	A-70280-0265	50													
D	52	010-89-7521	A-70280-0026	010-89-7522	A-70280-0066	010-89-7520	A-70280-0106	010-97-7525	A-70280-0146	010-97-7526	A-70280-0186	010-89-7523	A-70280-0226	010-87-9525	A-70280-0266	52													
	54	010-89-7541	A-70280-0027	010-89-7542	A-70280-0067	010-89-7540	A-70280-0107	010-97-7545	A-70280-0147	010-97-7546	A-70280-0187	010-89-7543	A-70280-0227	010-87-9545	A-70280-0267	54													
	56	010-89-7561	A-70280-0028	010-89-7562	A-70280-0068	010-89-7560	A-70280-0108	010-97-7565	A-70280-0148	010-97-7566	A-70280-0188	010-89-7563	A-70280-0228	010-87-9565	A-70280-0268	56													
	58	010-89-7581	A-70280-0029	010-89-7582	A-70280-0069	010-89-7580	A-70280-0109	010-97-7585	A-70280-0149	010-97-7586	A-70280-0189	010-89-7583	A-70280-0229	010-87-9585	A-70280-0269	58													
	60	010-89-7601	A-70280-0030	010-89-7602	A-70280-0070	010-89-7600	A-70280-0110	010-97-7605	A-70280-0150	010-97-7606	A-70280-0190	010-89-7603	A-70280-0230	010-87-9605	A-70280-0270	60													
	62	010-89-7621	A-70280-0031	010-89-7622	A-70280-0071	010-89-7620	A-70280-0111	010-97-7625	A-70280-0151	010-97-7626	A-70280-0191	010-89-7623	A-70280-0231	010-87-9625	A-70280-0271	62													
	64	010-89-7641	A-70280-0032	010-89-7642	A-70280-0072	010-89-7640	A-70280-0112	010-97-7645	A-70280-0152	010-97-7646	A-70280-0192	010-89-7643	A-70280-0232	010-87-9645	A-70280-0272	64													
	66	010-89-7661	A-70280-0033	010-89-7662	A-70280-0073	010-89-7660	A-70280-0113	010-97-7665	A-70280-0153	010-97-7666	A-70280-0193	010-89-7663	A-70280-0233	010-87-9665	A-70280-0273	66													
C	68	010-89-7681	A-70280-0034	010-89-7682	A-70280-0074	010-89-7680	A-70280-0114	010-97-7685	A-70280-0154	010-97-7686	A-70280-0194	010-89-7683	A-70280-0234	010-87-9685	A-70280-0274	68													
	70	010-89-7701	A-70280-0035	010-89-7702	A-70280-0075	010-89-7700	A-70280-0115	010-97-7705	A-70280-0155	010-97-7706	A-70280-0195	010-89-7703	A-70280-0235	010-87-9705	A-70280-0275	70													
	72	010-89-7721	A-70280-0036	010-89-7722	A-70280-0076	010-89-7720	A-70280-0116	010-97-7725	A-70280-0156	010-97-7726	A-70280-0196	010-89-7723	A-70280-0236	010-87-9725	A-70280-0276	72													
	74	010-89-7741	A-70280-0037	010-89-7742	A-70280-0077	010-89-7740	A-70280-0117	010-97-7745	A-70280-0157	010-97-7746	A-70280-0197	010-89-7743	A-70280-0237	010-87-9745	A-70280-0277	74													
B	76	010-89-7761	A-70280-0038	010-89-7762	A-70280-0078	010-89-7760	A-70280-0118	010-97-7765	A-70280-0158	010-97-7766	A-70280-0198	010-89-7763	A-70280-0238	010-87-9765	A-70280-0278	76													
	78	010-89-7781	A-70280-0039	010-89-7782	A-70280-0079	010-89-7780	A-70280-0119	010-97-7785	A-70280-0159	010-97-7786	A-70280-0199	010-89-7783	A-70280-0239	010-87-9785	A-70280-0279	78													
	80	010-89-7801	A-70280-0040	010-89-7802	A-70280-0080	010-89-7800	A-70280-0120	010-97-7805	A-70280-0160	010-97-7806	A-70280-0200	010-89-7803	A-70280-0240	010-87-9805	A-70280-0280	80													
A	UPDATE DIMENSIONS EC NO: UCP2007-1440 2006/12/18 DRWN:PRI DER CHKD:ADER APPR:F:SM TH 2007/01/10															QUALITY SYMBOLS ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE ---		DESIGN UNITS INCH		THIRD ANGLE PROJECTION			
																		DRAWN BY SMR		DATE 1993/04/19		TITLE SALES ASSY-HIGH TEMP. DUAL ROW WAFER W/BREAK- OFF OPTION, .025 SQ PINS							
																		CHECKED BY		DATE									
																		APPROVED BY SMR		DATE 1993/04/19		MOLEX INCORPORATED							
															ANGULAR ±1/2°		MATERIAL NO.		DOCUMENT NO.		SHEET NO.								
															DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART				SDA								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[10-87-9105](#) [10-87-9125](#) [10-89-7183](#) [10-89-7223](#) [10-87-9205](#)