



Leaded Tantalum Capacitors

TAP Series Specifications




Part Number Determination


TAP475M035SCS				
TAP	475	M	035	SCS
STYLE	CAPACITANCE CODE	TOLERANCE	VOLTAGE	WIRE FORM & PACKAGING
Solid Tantalum Resin Dipped Capacitors	in pF 2 Significant digits = 1 multiplier	K=±10% M=±20%	006=6.3V 010=10V 016=16V 020=20V 025=25V 035=35V 050=50V	CCS=Wire Form C/ Bulk CRW=Wire Form C/Tape&Reel CRS=Wire Form C/Ammo Tape BRW=Wire Form B/Tape&Reel BRS=Wire form B/Ammo Tape SCS=Wire Form S/Bulk SRW=Wire form S/Tape&Reel SRS=Wire Form S/Ammo Tape

Package Dimensions mm(in)

WIRE FORM	C,F,G,H	B,S,D	D
CASE SIZE	H	*H1	
A	8.5 (0.33)	7.0 (0.28)	4.5 (0.18)
B	9.0 (0.35)	7.5 (0.30)	4.5 (0.18)
C	10.0 (0.39)	8.5 (0.33)	5.0 (0.20)
D	10.5 (0.41)	9.0 (0.35)	5.0 (0.20)
E	10.5 (0.41)	9.0 (.035)	5.5 (0.22)
F	11.5 (0.45)	10.0 (0.39)	6.0 (0.24)
G	11.5 (0.45)	10.0 (0.39)	6.5 (0.26)
H	12.0 (0.47)	10.5 (0.41)	7.0 (0.28)
J	13.0 (0.51)	11.5 (0.45)	8.0 (0.31)
K	14.0 (0.55)	12.5 (0.49)	8.5 (0.33)
L	14.0 (0.55)	12.5 (0.49)	9.0 (0.35)
M	14.5 (0.57)	13.0 (0.51)	9.0 (0.35)
N	16.0 (0.63)		9.0 (0.35)
P	17.9 (0.67)		10.0 (0.39)
R	18.5 (0.73)		10.0 (0.39)



Marking



*Polarity
*Capacitance
*Voltage
*AVX Logo